

自主封測 品質把控 售後保障

WEB | WWW.TDSEMIC.COM



電源管理



顯示驅動



二三極管



LDO穩壓器



觸摸芯片



MOS管



運算放大器



存儲芯片



MCU



串口通信

MMBT2907A(2F)

產品規格說明書

SOT-23 Plastic-Encapsulate Transistors

MMBT2907 2F TRANSISTOR (PNP)

FEATURES

Complimentary to MMBT2222

MARKING:2F

SOT-23

1. BASE
2. EMITTER
3. COLLECTOR



MAXIMUM RATINGS (TA=25°C unless otherwise noted)

Symbol (符号)	Parameter (参数名称)	Value (额定值)	Units (单位)
VCBO	Collector-Base Voltage (集电极-基极电压)	60	V
VCEO	Collector-Emitter Voltage (集电极-发射极电压)	60	V
VEBO	Emitter-Base Voltage (发射极-基极电压)	5	V
IC	Collector Current -Continuous (集电极电流)	0.6	A
PC	Collector Power Dissipation (耗散功率)	0.225	W
Tj	Junction Temperature (结温)	150	°C
Tstg	Storage Temperature (储存温度)	-55-150	°C


ELECTRICAL CHARACTERISTICS (Tamb=25°C unless otherwise specified)

Parameter (参数名称)	Symbol (符号)	Test conditions (测试条件)	MIN (最小值)	TYP (典型值)	MAX (最大值)	UNIT (单位)
Collector-base breakdown voltage 集电极-基极击穿电压	V(BR)CBO	IC= -100μA, IE=0	-60			V
Collector-emitter breakdown voltage 集电极-发射极击穿电压	V(BR)CEO	IC= -1mA, IB=0	-60			V
Emitter-base breakdown voltage 发射极-基极击穿电压	V(BR)EBO	IE=-100μA, IC=0	-5			V
Collector cut-off current 集电极-基极截止电流	ICBO	VCB=-50 V, IE=0			-1	μ A
Collector cut-off current 集电极-发射极截止电流	ICEO	VCE=-30V, IB=0			-10	μ A
Emitter cut-off current 发射极-基极截止电流	IEBO	VEB=-5V, IC=0			-1	μ A
DC current gain 直流电流增益	hFE	VCE=-10V, IC= -150mA	100		400	
Collector-emitter saturation voltage 集电极-发射极饱和压降	VCE(sat)	IC=-150mA, IB= -15mA			-0.4	V
Base-emitter saturation voltage 发射极-基极饱和压降	VBE(sat)	IC=-150mA, IB= -15mA			-1.3	V

CLASSIFICATION OF hFE


Range	100-300	300-400		
-------	---------	---------	--	--

Typical Characteristics



I_C , COLLECTOR CURRENT (mA)

“On” Voltage



I_C , COLLECTOR CURRENT (mA)

Current-Gain — Bandwidth Product