

自主封測 品質把控 售後保障

WEB | WWW.TDSEMIC.COM



電源管理



顯示驅動



二三極管



LDO穩壓器



觸摸芯片



MOS管



運算放大器



存儲芯片



MCU



串口通信

DB107S


產品規格說明書

DB107S Voltage Range 50 to 1000 Volts Current 1.0Ampere


Features

- *UL Recognized File
- *Ideal for printed circuit board
- *Reliable low cost construction utilizing molded plastic technique
- *High temperature soldering guaranteed:
250°C/10 seconds/0.375" (9.5mm) lead length at 5lbs.
(2.3kg) tension
- *Small size, simple installation Leads solderable per
MIL-STD-202, Method 208
- *High surge current capability

DB-1



DBS



Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	DB 101(S)	DB 102(S)	DB 103(S)	DB 104(S)	DB 105(S)	DB 106(S)	DB 107(S)	Units
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @T=40°C	1.0							A
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	50							A
Maximum Instantaneous Forward Voltage @1.0A	1.1							V
Maximum DC Reverse Current @TA=25°C At Rated DC Blocking Voltage@TA=125°C	10 500							uA uA
Operating Temperature Range T	-55 to+125							°C
Storage Temperature Range TsTG	-55 to+125							°C

DB107S Voltage Range 50 to 1000

Volts Current 1.0 Ampere

RATINGS AND CHARACTERISTIC CURVES(DB101(S)THRU DB107(S))

