

# SPTECH Product Specification

## SPTECH Silicon NPN Power Transistor

2SC6082

### DESCRIPTION



- Large current capacitance
- High speed switching
- Low saturation voltage
- 100% avalanche tested
- Minimum Lot-to-Lot variations for robust device performance and reliable operation

### APPLICATIONS

- High speed switching applications

### ABSOLUTE MAXIMUM RATINGS( $T_a=25^{\circ}\text{C}$ )

| SYMBOL    | PARAMETER                                                 | VALUE   | UNIT               |
|-----------|-----------------------------------------------------------|---------|--------------------|
| $V_{CBO}$ | Collector-Base Voltage                                    | 60      | V                  |
| $V_{CEO}$ | Collector-Emitter Voltage                                 | 50      | V                  |
| $V_{EBO}$ | Emitter-Base Voltage                                      | 6       | V                  |
| $I_C$     | Collector Current- Continuous                             | 15      | A                  |
| $I_B$     | Base Current- Continuous                                  | 3       | A                  |
| $I_{CP}$  | Collector Current-Pulse                                   | 20      | A                  |
| $P_C$     | Collector Power Dissipation<br>@ $T_a=25^{\circ}\text{C}$ | 2       | W                  |
|           | Collector Power Dissipation<br>@ $T_c=25^{\circ}\text{C}$ | 23      |                    |
| $T_J$     | Junction Temperature                                      | 150     | $^{\circ}\text{C}$ |
| $T_{stg}$ | Storage Temperature Range                                 | -55~150 | $^{\circ}\text{C}$ |



# SPTECH Product Specification

## SPTECH Silicon NPN Power Transistor

2SC6082

### ELECTRICAL CHARACTERISTICS

$T_c=25^{\circ}\text{C}$  unless otherwise specified

| SYMBOL        | PARAMETER                            | CONDITIONS                                                 | MIN | TYP. | MAX | UNIT          |
|---------------|--------------------------------------|------------------------------------------------------------|-----|------|-----|---------------|
| $V_{CE(sat)}$ | Collector-Emitter Saturation Voltage | $I_C=7.5\text{A}; I_B=0.375\text{A}$                       |     |      | 0.4 | V             |
| $V_{BE(sat)}$ | Base-Emitter Saturation Voltage      | $I_C=7.5\text{A}; I_B=0.375\text{A}$                       |     |      | 1.2 | V             |
| $I_{CBO}$     | Collector Cutoff Current             | $V_{CB}=40\text{V}; I_E=0$                                 |     |      | 10  | $\mu\text{A}$ |
| $h_{FE-1}$    | DC Current Gain                      | $I_C=330\text{mA}; V_{CE}=2\text{V}$                       | 200 |      | 560 |               |
| $h_{FE-2}$    | DC Current Gain                      | $I_C=10\text{A}; V_{CE}=2\text{V}$                         | 50  |      |     |               |
| $t_{stg}$     | Storage Time                         | $I_C=5\text{A}, I_{B1}=0.25\text{A}; I_{B2}=-0.25\text{A}$ |     | 560  |     | ns            |
| $t_f$         | Fall Time                            |                                                            |     | 37   |     | ns            |