



Technical drawing of a rectangular metal plate. The drawing shows a top view and a side view. The top view is a rectangle with a width of 1.00 and a length of 1.40. The side view shows a thickness of 2.35. The drawing includes a detail view of a hole with a diameter of $N-0.20 \pm 0.02$. The drawing is labeled with circled numbers 1, 2, and 4.



适用线路板 (PCB LAYOUT)

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.

