

SPTECH Silicon NPN Power Transistor

2SC2751

DESCRIPTION



- Collector-Emitter Sustaining Voltage-
: $V_{CEO(SUS)} = 400V(\text{Min})$
- High Current Capability
- High Power Dissipation

APPLICATIONS

- Designed for high speed, high current switching industrial applications.

ABSOLUTE MAXIMUM RATINGS($T_a=25^{\circ}\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	500	V
V_{CEO}	Collector-Emitter Voltage	400	V
V_{EBO}	Emitter-Base Voltage	7	V
I_C	Collector Current-Continuous	15	A
I_{CM}	Collector Current-Peak	30	A
I_B	Base Current-Continuous	7.5	A
P_C	Collector Power Dissipation @ $T_C=25^{\circ}\text{C}$	120	W
T_J	Junction Temperature	150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	-55~150	$^{\circ}\text{C}$



SPTECH Silicon NPN Power Transistor

2SC2751

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{CEQ(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C=30\text{mA}; I_B=0$	400			V
V_{CBO}	Collector-Emitter Sustaining Voltage	$I_B=1\text{mA}, I_C=0$	450			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=10\text{A}; I_B=2\text{A}$			1.0	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C=10\text{A}; I_B=2\text{A}$			1.5	V
I_{CBO}	Collector Cutoff Current	$V_{CB}=450\text{V}; I_E=0$			100	μA
I_{EBO}	Emitter Cutoff Current	$V_{EB}=5\text{V}; I_C=0$			10	μA
h_{FE-1}	DC Current Gain	$I_C=2\text{A}; V_{CE}=5\text{V}$	15		80	
h_{FE-2}	DC Current Gain	$I_C=5\text{A}; V_{CE}=5\text{V}$	10			
h_{FE-3}	DC Current Gain	$I_C=10\text{A}; V_{CE}=5\text{V}$	7			

Switching Times

t_{on}	Turn-on Time	$I_C=10\text{A}, I_{B1}=-I_{B2}=2\text{A}, V_{CC}\approx 150\text{V}; R_L=15\Omega$			1.0	μs
t_{stg}	Storage Time				2.5	μs
t_f	Fall Time				0.7	μs

◆ h_{FE-1} Classifications

N	R	O	Y
15-30	20-40	30-60	40-80