

DESCRIPTION



- Good Linearity of h_{FE}
- High Collector-Emitter Breakdown Voltage-
 $V_{(BR)CEO} = 160V(\text{Min})$ -2SC3298
 $= 180V(\text{Min})$ -2SC3298A
 $= 200V(\text{Min})$ -2SC3298B
- Complement to Type 2SA1306/A/B

APPLICATIONS

- Power amplifier applications.
- Driver stage amplifier applications.

ABSOLUTE MAXIMUM RATINGS($T_a=25^\circ\text{C}$)

SYMBOL	PARAMETER		VALUE	UNIT
V_{CBO}	Collector-Base Voltage	2SC3298	160	V
		2SC3298A	180	
		2SC3298B	200	
V_{CEO}	Collector-Emitter Voltage	2SC3298	160	V
		2SC3298A	180	
		2SC3298B	200	
V_{EBO}	Emitter-Base Voltage		5	V
I_C	Collector Current-Continuous		1.5	A
I_B	Base Current-Continuous		0.15	A
P_C	Collector Power Dissipation @ $T_C=25^\circ\text{C}$		20	W
T_J	Junction Temperature		150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range		-55~150	$^\circ\text{C}$



SPTECH Silicon NPN Power Transistors

2SC3298/A/B

ELECTRICAL CHARACTERISTICS

 $T_c=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER		CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	2SC3298	$I_C = 10\text{mA}; I_B = 0$	160			V
		2SC3298A		180			
		2SC3298B		200			
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage		$I_C = 500\text{mA}; I_B = 50\text{mA}$			1.5	V
$V_{BE(on)}$	Base-Emitter On Voltage		$I_C = 500\text{mA}; V_{CE} = 5\text{V}$			1.0	V
I_{CBO}	Collector Cutoff Current		$V_{CB} = 160\text{V}; I_E = 0$			1.0	μA
I_{EBO}	Emitter Cutoff Current		$V_{EB} = 5\text{V}; I_C = 0$			1.0	μA
h_{FE}	DC Current Gain		$I_C = 100\text{mA}; V_{CE} = 5\text{V}$	70		240	
f_T	Current-Gain—Bandwidth Product		$I_C = 100\text{mA}; V_{CE} = 10\text{V}$		100		MHz
C_{OB}	Output Capacitance		$I_E = 0; V_{CB} = 10\text{V}; f_{test} = 1.0\text{MHz}$		25		pF

◆ h_{FE} Classifications

O	Y
70-140	120-240