

SPTECH Silicon PNP Power Transistor**2SA1294****DESCRIPTION**



- High Collector-Emitter Breakdown Voltage-
 $V_{(BR)CEO} = -230V(\text{Min})$
- Good Linearity of h_{FE}
- Complement to Type 2SC3263

APPLICATIONS

- Designed for audio and general purpose applications

ABSOLUTE MAXIMUM RATINGS($T_a=25^\circ\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	-230	V
V_{CEO}	Collector-Emitter Voltage	-230	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current-Continuous	-15	A
I_B	Base Current-Continuous	-4	A
P_C	Collector Power Dissipation @ $T_c=25^\circ\text{C}$	130	W
T_J	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range	-55~150	$^\circ\text{C}$



SPTECH Silicon PNP Power Transistor**2SA1294****ELECTRICAL CHARACTERISTICS****T_C=25°C unless otherwise specified**

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
V _{(BR)CEO}	Collector-Emitter Breakdown Voltage	I _C = -25mA ; I _B = 0	-230			V
V _{CE(sat)}	Collector-Emitter Saturation Voltage	I _C = -5.0A; I _B = -0.5A			-2.0	V
I _{CBO}	Collector Cutoff Current	V _{CB} = -230V ; I _E = 0			-100	μ A
I _{EBO}	Emitter Cutoff Current	V _{EB} = -5V; I _C = 0			-100	μ A
h _{FE}	DC Current Gain	I _C = -5A ; V _{CE} = -4V	50		140	
C _{OB}	Output Capacitance	I _E = 0 ; V _{CB} = -10V; f= 1.0MHz		500		pF
f _T	Current-Gain—Bandwidth Product	I _E = 2A ; V _{CE} = -12V		35		MHz

Switching Times

t _{on}	Turn-on Time	I _C = -5A , R _L = 12 Ω , I _{B1} = -I _{B2} = -0.5A, V _{CC} = -60V		0.35		μ s
t _{stg}	Storage Time			1.5		μ s
t _f	Fall Time			0.3		μ s

◆ h_{FE} Classifications

O	Y
50-100	70-140