

SPTECH Silicon NPN Power Transistor

2SC3039

DESCRIPTION



- Collector-Emitter Breakdown Voltage-
: $V_{(BR)CEO} = 400V(\text{Min})$
- Fast Switching Speed
- Wide Area of Safe Operation

APPLICATIONS

- Designed for switching regulator applications.

ABSOLUTE MAXIMUM RATINGS($T_a = 25^\circ\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	500	V
V_{CEO}	Collector-Emitter Voltage	400	V
V_{EBO}	Emitter-Base Voltage	7	V
I_C	Collector Current-Continuous	7	A
I_{CM}	Collector Current-Peak	14	A
I_B	Base Current-Continuous	3	A
P_C	Collector Power Dissipation @ $T_C = 25^\circ\text{C}$	50	W
T_J	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range	-55~150	$^\circ\text{C}$



SPTECH Silicon NPN Power Transistor

2SC3039

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP.	MAX	UNIT
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage	$I_C = 5\text{mA}; R_{BE} = \infty$	400			V
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage	$I_C = 1\text{mA}; I_E = 0$	500			V
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage	$I_E = 1\text{mA}; I_C = 0$	7			V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C = 4\text{A}; I_B = 0.8\text{A}$			1.0	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C = 4\text{A}; I_B = 0.8\text{A}$			1.5	V
I_{CBO}	Collector Cutoff Current	$V_{CB} = 400\text{V}; I_E = 0$			10	μA
I_{EBO}	Emitter Cutoff Current	$V_{EB} = 5\text{V}; I_C = 0$			10	μA
h_{FE-1}	DC Current Gain	$I_C = 0.8\text{A}; V_{CE} = 5\text{V}$	15		50	
h_{FE-2}	DC Current Gain	$I_C = 4\text{A}; V_{CE} = 5\text{V}$	8			
f_T	Current-Gain—Bandwidth Product	$I_C = 0.8\text{A}; V_{CE} = 10\text{V}$		20		MHz
C_{OB}	Output Capacitance	$V_{CB} = 10\text{V}; f_{test} = 1.0\text{MHz}$		80		pF

Switching times

t_{on}	Turn-on Time	$I_C = 5\text{A}, I_{B1} = -I_{B2} = 1\text{A};$ $R_L = 40\Omega; V_{CC} = 200\text{V}$			1.0	μs
t_{stg}	Storage Time				2.5	μs
t_f	Fall Time				1.0	μs

◆ h_{FE-1} Classifications

L	M	N
15-30	20-40	30-50