








P.J-306FA



SCHEMATIC



10	PJ306FA SPRING(卡簧)	SPRING WIRE	1	Ni PLATED
9	PJ306F AXIS GUIDE	PBT	1	PINK/BLUE/GREEN/BLACK
8	PJ306F AXIS GUIDE	BRASS	1	Ni/Au PLATED
7	PJ306 5#SPRING	PBS/SUS	1	Ag PLATED
6	PJ306 4#TERMINAL	BRASS	1	Ag PLATED
5	PJ306 3#TERMINAL	BRASS	1	Ag PLATED
4	PJ306 2#SPRING	PBS	1	Ag PLATED
3	PJ306 1#COVER	BRASS	1	Ag PLATED
2	PJ306 COVER	PBT	1	BLACK
1	PJ306 CASE	PBT	1	BLACK
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED		A1	2018.9.14	修正脚位尺寸公差	GYW	
UP TO 5mm: ± 0.1	ANGULAR $\pm 1^\circ$	A0	2018.4.4	首次发行	GYW	
ABOVE 5mm: ± 0.2		NO	DATE	REVISIONS	BY	APPD
TITLE:PHONE JACK		UNIT : MM		ROHS COMPLIANT	DWN	
MODEL:PJ-306FA		SCALE: 1:1		CHK'D		
HOOYA ELECTRONIC CO. LTD 皓宇电子有限公司		APPD				
		PRO.AGL:			REV :A1	