

SPTECH Silicon NPN Power Transistors

BU122

DESCRIPTION

- Collector-Emitter Sustaining Voltage-
: $V_{CEO(SUS)} = 150V(\text{Min})$

APPLICATIONS



- Designed for horizontal deflection output stage of CTV receivers and high voltage, fast switching and industrial application.

ABSOLUTE MAXIMUM RATINGS($T_a=25^\circ\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Emitter Voltage	150	V
V_{CEO}	Collector-Emitter Voltage	150	V
V_{EBO}	Emitter-Base Voltage	8	V
I_C	Collector Current-Continuous	5	A
I_{CM}	Collector Current-peak	15	A
I_B	Base Current-Continuous	3.0	A
P_C	Collector Power Dissipation @ $T_c=25^\circ\text{C}$	50	W
T_j	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature Range	-65~150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j-c}$	Thermal Resistance, Junction to Case	1.75	$^\circ\text{C/W}$



SPTECH Silicon NPN Power Transistors

BU122

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	MAX	UNIT
$V_{CEO(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C=50\text{mA}$; $I_B=0$	150		V
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage	$I_C=1\text{mA}$; $I_E=0$	150		V
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=8\text{A}$; $I_B=2.5\text{A}$		3.3	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C=8\text{A}$; $I_B=2.5\text{A}$		2.2	V
I_{CBO}	Collector Cutoff Current	$V_{CB}=150\text{V}$; $I_E=0$		0.1	mA
I_{EBO}	Emitter Cutoff Current	$V_{EB}=7\text{V}$; $I_C=0$		0.1	mA
h_{FE}	DC Current Gain	$I_C=1\text{A}$; $V_{CE}=5\text{V}$	25	250	
f_T	Current-Gain—Bandwidth Product	$I_C=1\text{A}$; $V_{CE}=10\text{V}$; $f_{test}=1\text{MHz}$	10		MHz