

SPTECH Silicon PNP Power Transistor

BD534

DESCRIPTION

- DC Current Gain -
: $h_{FE} = 40@ I_C = -0.5A$
- Collector-Emitter Sustaining Voltage-
: $V_{CEO(SUS)} = -45V(\text{Min})$
- Complement to Type BD533

APPLICATIONS



- Designed for use in medium power linear and switching applications.

ABSOLUTE MAXIMUM RATINGS($T_a=25^{\circ}\text{C}$)

SYMBOL	PARAMETER	VALUE	UNIT
V_{CBO}	Collector-Base Voltage	-45	V
V_{CES}	Collector-Emitter Voltage	-45	V
V_{CEO}	Collector-Emitter Voltage	-45	V
V_{EBO}	Emitter-Base Voltage	-5	V
I_C	Collector Current-Continuous	-8	A
I_B	Base Current	-1	A
P_C	Collector Power Dissipation @ $T_C=25^{\circ}\text{C}$	50	W
T_J	Junction Temperature	150	$^{\circ}\text{C}$
T_{stg}	Storage Temperature Range	-65~150	$^{\circ}\text{C}$

THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	MAX	UNIT
$R_{th\ j-c}$	Thermal Resistance, Junction to Case	2.5	$^{\circ}\text{C/W}$
$R_{th\ j-a}$	Thermal Resistance, Junction to Ambient	70	$^{\circ}\text{C/W}$



SPTECH Silicon PNP Power Transistor

BD534

ELECTRICAL CHARACTERISTICS

 $T_C=25^{\circ}\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
$V_{CEQ(SUS)}$	Collector-Emitter Sustaining Voltage	$I_C = -30\text{mA}$; $I_B = 0$	-45			V
$V_{CE(sat)-1}$	Collector-Emitter Saturation Voltage	$I_C = -2\text{A}$; $I_B = -0.2\text{A}$			-0.8	V
$V_{CE(sat)-2}$	Collector-Emitter Saturation Voltage	$I_C = -6\text{A}$; $I_B = -0.6\text{A}$		-0.8		V
$V_{BE(on)}$	Base-Emitter On Voltage	$I_C = -2\text{A}$; $V_{CE} = -2\text{V}$			-1.5	V
I_{CBO}	Collector Cutoff Current	$V_{CB} = -45\text{V}$; $I_E = 0$			-0.1	mA
I_{CES}	Collector Cutoff Current	$V_{CE} = -45\text{V}$; $V_{BE} = 0$			-0.1	mA
I_{EBO}	Emitter Cutoff Current	$V_{EB} = -5\text{V}$; $I_C = 0$			-1.0	mA
h_{FE-1}	DC Current Gain	$I_C = -10\text{mA}$; $V_{CE} = -5\text{V}$	20			
h_{FE-2}	DC Current Gain	$I_C = -0.5\text{A}$; $V_{CE} = -2\text{V}$	40			
h_{FE-3}	DC Current Gain	$I_C = -2\text{A}$; $V_{CE} = -2\text{V}$	25			
f_T	Current-Gain—Bandwidth Product	$I_C = -0.5\text{A}$; $V_{CE} = -1\text{V}$	3.0	12		MHz