

## N-Channel Enhancement Mode Power MOSFET

## Description


The GT013N04TLH uses advanced trench technology to provide excellent  $R_{DS(ON)}$ , low gate charge. It can be used in a wide variety of applications.

## General Features


- $V_{DS}$  40V
- $I_D$  (at  $V_{GS} = 10V$ ) 285A
- $R_{DS(ON)}$  (at  $V_{GS} = 10V$ ) < 1.3m $\Omega$
- 100% Avalanche Tested
- RoHS Compliant

## Application

- Power switch
- DC/DC converters



Schematic diagram



TOLL-8L

## Ordering Information

| Device      | Package | Marking   | Packaging    |
|-------------|---------|-----------|--------------|
| GT013N04TLH | TOLL-8L | GT013N04H | 2000pcs/Reel |

Absolute Maximum Ratings  $T_C = 25^\circ\text{C}$ , unless otherwise noted

| Parameter                                        | Symbol         | Value      | Unit             |
|--------------------------------------------------|----------------|------------|------------------|
| Drain-Source Voltage                             | $V_{DS}$       | 40         | V                |
| Continuous Drain Current                         | $I_D$          | 285        | A                |
|                                                  |                | 180        |                  |
| Pulsed Drain Current (note1)                     | $I_{DM}$       | 1140       | A                |
| Gate-Source Voltage                              | $V_{GS}$       | $\pm 20$   | V                |
| Power Dissipation                                | $P_D$          | 156        | W                |
| Single pulse avalanche energy (note2)            | $E_{AS}$       | 440        | mJ               |
| Operating Junction and Storage Temperature Range | $T_J, T_{stg}$ | -55 To 150 | $^\circ\text{C}$ |

## Thermal Resistance

| Parameter                               | Symbol     | Value | Unit               |
|-----------------------------------------|------------|-------|--------------------|
| Thermal Resistance, Junction-to-Ambient | $R_{thJA}$ | 50    | $^\circ\text{C/W}$ |
| Maximum Junction-to-Case                | $R_{thJC}$ | 0.8   | $^\circ\text{C/W}$ |

**Specifications**  $T_J = 25^\circ\text{C}$ , unless otherwise noted

| Parameter                               | Symbol               | Test Conditions                                                          | Value |      |      | Unit |
|-----------------------------------------|----------------------|--------------------------------------------------------------------------|-------|------|------|------|
|                                         |                      |                                                                          | Min.  | Typ. | Max. |      |
| Static Parameters                       |                      |                                                                          |       |      |      |      |
| Drain-Source Breakdown Voltage          | V <sub>(BR)DSS</sub> | V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA                             | 40    | --   | --   | V    |
| Zero Gate Voltage Drain Current         | I <sub>DSS</sub>     | V <sub>DS</sub> = 40V, V <sub>GS</sub> = 0V                              | --    | --   | 1    | μA   |
| Gate-Source Leakage                     | I <sub>GSS</sub>     | V <sub>GS</sub> = ±20V                                                   | --    | --   | ±100 | nA   |
| Gate-Source Threshold Voltage           | V <sub>GS(th)</sub>  | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA               | 2.0   | 3.0  | 4.0  | V    |
| Drain-Source On-Resistance              | R <sub>DS(on)</sub>  | V <sub>GS</sub> = 10V, I <sub>D</sub> = 50A                              | --    | 1.0  | 1.3  | mΩ   |
| Forward Transconductance                | g <sub>FS</sub>      | V <sub>GS</sub> = 5V, I <sub>D</sub> = 50A                               | --    | 80   | --   | S    |
| Dynamic Parameters                      |                      |                                                                          |       |      |      |      |
| Input Capacitance                       | C <sub>iss</sub>     | V <sub>GS</sub> = 0V,<br>V <sub>DS</sub> = 20V,<br>f = 0.6MHz            | --    | 5400 | --   | pF   |
| Output Capacitance                      | C <sub>oss</sub>     |                                                                          | --    | 3600 | --   |      |
| Reverse Transfer Capacitance            | C <sub>rss</sub>     |                                                                          | --    | 150  | --   |      |
| Total Gate Charge                       | Q <sub>g</sub>       | V <sub>DD</sub> = 20V,<br>I <sub>D</sub> = 50A,<br>V <sub>GS</sub> = 10V | --    | 84   | --   | nC   |
| Gate-Source Charge                      | Q <sub>gs</sub>      |                                                                          | --    | 28   | --   |      |
| Gate-Drain Charge                       | Q <sub>gd</sub>      |                                                                          | --    | 17   | --   |      |
| Turn-on Delay Time                      | t <sub>d(on)</sub>   | V <sub>DD</sub> = 20V,<br>I <sub>D</sub> = 50A,<br>R <sub>G</sub> = 1.6Ω | --    | 13   | --   | ns   |
| Turn-on Rise Time                       | t <sub>r</sub>       |                                                                          | --    | 7    | --   |      |
| Turn-off Delay Time                     | t <sub>d(off)</sub>  |                                                                          | --    | 53   | --   |      |
| Turn-off Fall Time                      | t <sub>f</sub>       |                                                                          | --    | 9    | --   |      |
| Drain-Source Body Diode Characteristics |                      |                                                                          |       |      |      |      |
| Continuous Body Diode Current           | I <sub>S</sub>       | T <sub>C</sub> = 25°C                                                    | --    | --   | 285  | A    |
| Body Diode Voltage                      | V <sub>SD</sub>      | T <sub>J</sub> = 25°C, I <sub>SD</sub> = 50A, V <sub>GS</sub> = 0V       | --    | --   | 1.2  | V    |
| Reverse Recovery Charge                 | Q <sub>rr</sub>      | I <sub>F</sub> = 50A, V <sub>GS</sub> = 0V<br>di/dt=100A/us              | --    | 115  | --   | nC   |
| Reverse Recovery Time                   | T <sub>rr</sub>      |                                                                          | --    | 35   | --   | ns   |

**Notes**


1. Repetitive Rating: Pulse width limited by maximum junction temperature

2. EAS condition :  $T_J = 25^\circ\text{C}$ ,  $V_{DD} = 40V$ ,  $V_{GS} = 10V$ ,  $L = 0.5mH$ ,  $R_G = 25\Omega$

The table shows the minimum avalanche energy, which is 1225mJ when the device is tested until failure

3. Identical low side and high side switch with identical  $R_G$


### Gate Charge Test Circuit



### Switch Time Test Circuit




### EAS Test Circuit




**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted


**Figure 1. Output Characteristics**




**Figure 2. Transfer Characteristics**




**Figure 3. Drain Source On Resistance**




**Figure 4. Gate Charge**



**Figure 5. Capacitance**




**Figure 6. Source-Drain Diode Forward**




**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted


**Figure 7. Drain-Source On-Resistance**




**Figure 8. Safe Operation Area**




**Figure 9. Maximum Continuous Drain Current vs Case Temperature**



**Figure 10. Normalized Maximum Transient Thermal Impedance**



## TOLL-8L Package Information



| SYMBOL | COMMON     |         |       | SYMBOL | COMMON     |         |       |
|--------|------------|---------|-------|--------|------------|---------|-------|
|        | MILLIMETER |         |       |        | MILLIMETER |         |       |
|        | MIN.       | NOMINAL | MAX.  |        | MIN.       | NOMINAL | MAX.  |
| A      | 2.20       | 2.30    | 2.40  | E2     | 0.30       | 0.40    | 0.50  |
| b      | 0.70       | 0.80    | 0.90  | E3     | 8.50       |         |       |
| b1     | 9.70       | 9.80    | 9.90  | E4     | 9.46       |         |       |
| b2     | 0.36       | 0.45    | 0.55  | H      | 11.50      | 11.68   | 11.85 |
| b3     | 0.05       | 0.100   | /     | H1     | 6.55       | 6.65    | 6.75  |
| b4     | 0.30       | 0.40    | 0.50  | K      | 4.08       | 4.18    | 4.28  |
| b5     | 1.10       | 1.20    | 1.30  | L      | 1.60       | 1.90    | 2.10  |
| b6     | 3.00       | 3.10    | 3.20  | L1     | 0.50       | 0.70    | 0.90  |
| c      | 0.40       | 0.50    | 0.60  | L2     | 0.50       | 0.60    | 0.70  |
| D      | 10.28      | 10.38   | 10.55 | L3     | 1.00       | 1.20    | 1.30  |
| D1     | 10.98      | 11.08   | 11.18 | L4     | 0.13       | 0.23    | 0.33  |
| D2     | 3.20       | 3.30    | 3.40  | P      | 2.85       | 3.00    | 3.15  |
| D3     | 7.15       |         |       | θ      | 10° REF    |         |       |
| D4     | 3.59       |         |       | aaa    | 0.20       |         |       |
| D5     | 3.26       |         |       | ccc    | 0.20       |         |       |
| e      | 1.10       | 1.20    | 1.30  | ddd    | 0.25       |         |       |
| E      | 9.80       | 9.90    | 10.00 | eee    | 0.20       |         |       |
| E1     | 7.40       | 7.50    | 7.60  |        |            |         |       |