



Features

- Epitaxial planar die construction
- Built-in biasing resistors (R_1 : 4.7 k Ω R_2 : 4.7 k Ω)
- Also available in lead free version
- RoHS compliant with Halogen-free

Mechanical Data

- Case: SOT-523,
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Ordering Information

Part Number	Package	Shipping Quantity
DTA143EE	SOT-523	3000 pcs / Tape & Reel

Maximum Ratings (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Supply Voltage	V_{CC}	-50	V
Input Voltage	V_I	+10 to -30	V
Output Current	I_O	-100	mA
Collector Current	$I_{C(\text{Max})}$	-100	mA
Power Dissipation	P_D	150	mW
Junction Temperature Range	T_J	-55 ~ +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input Voltage	$V_{I(\text{OFF})}$	$V_{CC} = -5\text{V}, I_O = -100\mu\text{A}$	-0.5	-	-	V
Input Voltage	$V_{I(\text{ON})}$	$V_O = -0.3\text{V}, I_O = -20\text{mA}$	-	-	-3	V
Output Voltage	$V_{O(\text{on})}$	$I_O = -10\text{mA}, I_I = -0.5\text{mA}$	-	-	-0.3	V
Input Current	I_I	$V_I = -5\text{V}$	-	-	-1.8	mA
Output Current	$I_{O(\text{off})}$	$V_{CC} = -50\text{V}, V_I = 0\text{V}$	-	-	-0.5	μA
DC Current Gain	G_I	$V_O = -5\text{V}, I_O = -10\text{mA}$	20	-	-	-
Input Resistor	R_I		3.29	4.7	6.11	k Ω
Resistance ratio	R_2/R_1		0.8	1.0	1.2	-
Gain-Bandwidth Product	f_T	$V_{CE} = -10\text{V}, I_E = -5\text{mA}$ $f = 100\text{MHz}$	-	250	-	MHz

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Input Voltage vs Output Current




Fig 2 Output Current vs Input Voltage




Fig 3 DC Current Gain vs Output Current





Fig 4 Output Voltage vs Output Current

Package Outline Dimensions (unit:mm)

SOT-523



Mounting Pad Layout (unit: mm)

