

1		2		3		4																											
RoHS		<table><tr><td colspan="6">REVISIONS</td></tr><tr><td>REV.</td><td>ECN NO.</td><td>LOCATION</td><td colspan="2">DESCRIPTION</td><td>DATE</td><td>DESIGN</td></tr><tr><td>A0</td><td>N/A</td><td></td><td colspan="2">INITIAL RELEASE</td><td>2024.10.28</td><td></td></tr><tr><td colspan="6"></td></tr></table>						REVISIONS						REV.	ECN NO.	LOCATION	DESCRIPTION		DATE	DESIGN	A0	N/A		INITIAL RELEASE		2024.10.28							
REVISIONS																																	
REV.	ECN NO.	LOCATION	DESCRIPTION		DATE	DESIGN																											
A0	N/A		INITIAL RELEASE		2024.10.28																												
Specifications(规格):																																	
1.Impedance(特性阻抗): 50Ω;																																	
2.Frequency (工作频率): DC~3GHz;																																	
3.VSWR (电压驻波比): 1.50 Max;																																	
4.Insulation resistance(绝缘阻抗): ≥100MΩ;																																	
5.Dielectric withstand voltage (介质耐电压): 800V AC;																																	
6.Mating cycles (耐久性): ≥25 cycles;																																	
7.Retention force latch(保持力): ≥110N;																																	
8.Temperature range(使用温度): -40℃~+105℃;																																	
PART NO.:																																	
XZ X X-K1F-XXXX-K1F-Z Z																																	
① Cable TYPE:																																	
3: RG174																																	
4: 1.5DS																																	
7: Dacar302																																	
8: RG174LL																																	
② Successive number: 1~Z																																	
③ Length (mm): 1000=1000mm																																	
④ Coding A: A~Z																																	
⑤ Coding B (B1~B4): A~Z																																	