




CKI	DIM A	DIM B	DIM C
4	3.00	5.06	8.00
5	4.00	6.06	9.00
6	5.00	7.06	10.00
7	6.00	8.06	11.00
8	7.00	9.06	12.00
9	8.00	10.06	13.00
10	9.00	11.06	14.00
11	10.00	12.06	15.00
12	11.00	13.06	16.00
13	12.00	14.06	17.00
14	13.00	15.06	18.00
15	14.00	16.06	19.00
16	15.00	17.06	20.00
17	16.00	18.06	21.00
18	17.00	19.06	22.00
19	18.00	20.06	23.00
20	19.00	21.06	24.00
21	20.00	22.06	25.00
22	21.00	23.06	26.00
23	22.00	24.06	27.00
24	23.00	25.06	28.00
25	24.00	26.06	29.00
26	25.00	27.06	30.00
27	26.00	28.06	31.00
28	27.00	29.06	32.00
29	28.00	30.06	33.00
30	29.00	31.06	34.00




Technical drawing of a composite plate. The top view shows a rectangular plate with a total width of $(B-0.05)\pm 0.05$. The distance between the centers of the first and last holes is $A\pm 0.05$. The distance between the centers of two adjacent holes is 1.00 ± 0.05 . The diameter of each hole is 0.5 . The thickness of the plate is 3.5 Min. . The side view shows a cross-section of the plate with a total thickness of 0.30 ± 0.0 and a minimum thickness of 4.5 Min. for the bottom layer.

Technical drawing of a rectangular metal plate. The drawing shows a top view and a side view. The top view is a rectangle with a width of 1.60 and a length of 0.85. The side view shows a thickness of 2.20. The plate has a series of 12 holes along its length, with a spacing of $N-0.15 \pm 0.02$ between them. Callout ② points to one of the holes. Callout ④ points to the top edge of the plate. The bottom edge of the plate is dimensioned as 2.38.



2. 温度范围(Temperature range): $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$

成电子有限公司	品 名 TITLE	FPC座
	料 号 PART NO	HC-FPC-1.0-8P-FHH20

		深圳市虹成电子有限公司		品 名 TITLE	FPC座	
				料 号 PART NO	HC-FPC-1.0-8P-FHH20	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1:1			
X. ±.50 .XX ±.10		单 位 UNIT	MM	制 图 DRAW	AhYe	
.X ±.20 .XXX ±.05		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
ANGLES ±1°		版 本 REV	A	批 准 APPROVE	赵亮亮	