

新品 变更

产 品 规 格 书

SPECIFICATION FOR APPROVAL

产品名称
Product Name: 石英晶体谐振器

产品型号
Product Type: SMD3225

标称频率
Nominal Freq: 25.000000 MHz

明德亨料号
MDH P/N: 2.3.3.250002018

客户料号
Customer P/N:

客户承认
Approved By Customer

签章
Signature:

日期
Date:

Date: 2018年8月22日

批准	审核	拟制
Accepted	Checked	Issued
黄屹	乔润国	马赛



烟台明德亨电子科技有限公司
MDH Technology Co., Ltd

ADD: 中国山东烟台开发区黑龙江路6号

No.6 Heilongjiang Road Yantai Development Zone, Shandong, China

TEL: 86-535-6372640

FAX: 86-535-6394876

E-Mail: dynamic@public.ytptt.sd.cn<http://www.mingdeheng.com>

Revision Record

[illegible]

SMD3225 QUARTZ CRYSTAL UNIT		MDH P/N	2. 3. 3. 250002018		
		REV.	01	PAGE	3/10
CONTENT					
N0.	ITEM	PAGE			
1	石英晶体一般规格及特性 Product specification and features	4			
2	石英晶体外观尺寸 Product outline dimension	5			
3	石英晶体内部结构及印字 Product internal structure and marking	6			
4	石英晶体之可靠性 Product reliability	7-9			
5	生产商及产地说明 Manufacturer and origin	10			

SMD3225		QUARTZ CRYSTAL UNIT		MDH P/N		2. 3. 3. 250002018		
				REV.		01	PAGE	4/10
1 石英晶体产品规格及特性 / Product specification and features								
1.1 一般特性 / General characteristics								
标称频率		25.000000		MHz				
Nominal frequency								
振动模式		Fundamental						
Overtone order								
型 号		SMD3225						
Type								
动作温度		-40~85		℃				
Operating temperature								
保存温度		-40~85		℃				
Storage temperature								
1.2 电气特性 / Electric characteristics								
调整频差(+25℃基准)		±10		ppm				
Adjustment tolerance: (at+25℃)								
温度频差		±20		ppm				
Tolerance over the temperature:								
负 载		20.0		pF				
Load capacitance								
测试仪器		S&A 250B						
Measure Instrument								
激励功率		100.0		μw				
Drive level								
等效电阻		30.0		Ω Max				
Equivalent resistance								
分布电容 (C0)		3.0		pF Max				
Shut capacitance								
绝缘阻抗		500 MΩ Min		100VDC±15VDC				
Insulation resistance								
老化率		±2ppm		ppm/First year				
Aging								
1.3 其它特性 / Other characteristics								
SPDB		<-3		dB		(以标称频率为基准)		

SMD3225

QUARTZ CRYSTAL UNIT

MDH P/N

2.3.3.250002018

REV.


01

PAGE


5/10

2.0 外形尺寸、外观 / Outline dimensions、Appearances


2.1 产品外形尺寸(mm) / Product outline dimension(mm)



2.2 载带外形尺寸图 (mm) /Carrier Dimensional Drawing (mm)



2.3 编带盘外形尺寸图(mm) /Reel Dimensional Drawing (mm)




☆图示尺寸及公差 (mm) :


部位	A	T	T1, T2	N	C	D	E	G
尺寸	178	9.0	1.4	60.2	20.2	13.2	2.5	11.5
公差	±2.0	±0.5	±0.2	±0.5	±1.0	±0.5	±0.5	±1.4

SMD3225	QUARTZ CRYSTAL UNIT	MDH P/N	2.3.3.250002018		
		REV.	01	PAGE	6/10


2.4 印字 Marking



3.0 内部构造图 / Product internal structure



封装方式/Seal		激光封装	质量（参考值）		0.0144g
NO.	材料名/Matenal	备注/Notes	NO.	材料/Matenal	备注/Notes
1	金属盖板/LID	Fe—Ni—Co	5	导电胶 /Conductive achese	/
2	陶瓷/Ceramics	黑色/Color black	6	银/Ag	形状例/Form isexample
3	晶片/Crystal (Si02)	晶片 /Crystal Water	7	铬/Cr	形状例/Form isexample
4	引脚 /Pad	镀镍/镀金 Ni plating/Au plating			

SMD3225		QUARTZ CRYSTAL UNIT		MDH P/N		2. 3. 3. 250002018	
				REV.		01	PAGE 8/10
4.1机械性能 / Mechanism characteristics							
B. 1	跌落测试 (Drop Test)						(I)
	Device are dropped from a height of 100 cm onto 20mm thickness stainless plate executing 3 times of random drops.						
B. 2	耐振性 (Resistance of Vibration)						(I)
	Frequency: 10~55Hz, amplitude(total excursion): 1.5mm±15%, 3 direction (X,Y,Z) each 2 hr						
B. 3	耐焊接热 (手工)						(I)
	Resistance to soldering heat (Hand soldering method) 温度: 360±10℃; 时间: 3秒; 次数: 2次; 烙铁功率: 60W/Min Temperature: 370~400℃; Time: 3~4sec; Frequency: 2 times; Soldering iron: 60W/Min						
B. 4	可焊性试验 (Solderability)						(II)
	240±2℃, 3±0.5sec						
B. 5	耐焊接热 (Reflow) Resistance to soldering heat (Reflow)						(I)
	260± 5℃; 10S; 2Times Reflow温度曲线图 						

SMD3225

QUARTZ CRYSTAL UNIT

MDH P/N

2.3.3.250002018

REV.

01

PAGE

10/10

5.0 生产商及产地说明 / Manufacturer and origin

生产商/Manufacturer: 烟台明德亨电子科技有限公司/ MDH Technology Co.,Ltd工厂所在地/Address: 山东省烟台开发区黑龙江路6号No.6 Heilongjiang Road, Yantai Development zone, Shandon包装方式: 纸箱 52cm×37cm×38cm (±1.5cm)Package: Paper carton 52cm×37cm×38cm (±1.5cm)

5.1 包装规格 Package specification

