




| REV. | ECN Number | Description        | Drawn            |
|------|------------|--------------------|------------------|
| 1    | CS17040061 | RELEASE            | ZL 2017. 02. 06  |
| 2    | E18070036  | ADD VACUUM PACKING | XPG 2018. 07. 31 |
| 3    | E22120008  | ADD NATURE COLOR   | LJQ 2024. 04. 15 |

NOTES:

- HOUSING MATERIAL:HIGH TEMPERATURE PLASTICS, UL94V-0.
- CONTACT MATERIAL:COPPER ALLOY.
- OPERATING TEMPERATURE RANGE: -40° C~+105° C
- STORAGE TEMPERATURE RANGE: -40° C~+105° C
- SOLDER STENCIL RECOMMENDING A METAL MORE THAN 0.12~0.15mm THICK.
- Harmful Material Should Comply With The"RoHS"Standard.
- "▽"SIZE FOR CPK;
- PRODUCT NUMBER MATRIX:

Power supply seat  
2.20 Pitch  
T/H, V/T, Two row  
Number of contacts  
08=8pin  
Contact Plating:


WTB  
A P C 6 - 08 X K - X - X  
0:With clip, Black  
1:Without clip, Black  
2:With clip, Nature  
NULL:Low temperature thermoplastic  
F:High temperature thermoplastic  
H:Halogen free  
Packing  
K:Reel

| Definition             | Code          |
|------------------------|---------------|
| ◎ Matte Tin plated     | A             |
| ◎ Gold plated over all |               |
| flash B                | 1u" R 3u" C   |
| 5u" D                  | 10u" E 15u" F |
| 20u" G                 | 25u" H 30u" J |

P/N: APC6-08XK-X-0  
P/N: APC6-08XK-X-2  
P/N: APC6-08XK-X-1

| TOLERANCE UNLESS OTHERWISE SPECIFIED | SCALE 2:1 | ORIGINAL DRAWN: Li jiaqi | DATE 2024. 04. 15 | DWG. NO. 600-0000-0195                 | TITLE PH2. 2-8PIN DIP CONNECTOR CUSTOMER DRAWING | REV. 3    |
|--------------------------------------|-----------|--------------------------|-------------------|----------------------------------------|--------------------------------------------------|-----------|
| X. X ±0.30 X. ° ±3°                  | UNIT mm   | CHECK: Zhao long         | DATE 2024. 04. 15 | PARTS NO. (INTENDED USE) APC6-08XK-X-X |                                                  | SHEET 1/4 |
| X. XX ±0.20 X. X° ±2°                | SIZE A4   | APPROVE: Ady zhou        | DATE 2024. 04. 15 |                                        |                                                  |           |
| X. XXX                               |           |                          |                   |                                        |                                                  |           |







收料方向  
Income expected directio

NOTES

1. 每卷包装数量及每箱装箱数量如下表格。  
Packing q'ty of each reel & carton as below table shown.
  2. 带子引导长度。  
Lead tape length.
- 收料方向  
Income expected direction




3. 上带剥拉力为: 0.1~1.3N(10.2gf~130gf)  
Peeling off force of top tape:0.1~1.3N(10.2gf~130gf)
- 出货运输过程中一定注意:  
This requirement should be applied at shipment:  
卷带在运输过程中不能散开  
Peeling off should not be allowed during transportation.



ShenZhen ShenTai weiXiang Electronics Co., Ltd.

| TOLERANCE UNLESS OTHERWISE SPECIFIED |         |        |      |  | SCALE | ORIGINAL DRAWN: | DATE         | DWG. NO.                 | TITLE                    | REV.  |
|--------------------------------------|---------|--------|------|--|-------|-----------------|--------------|--------------------------|--------------------------|-------|
| X. X                                 | ± 0. 30 | X. °   | ± 3° |  | 2:1   | Li jiaqi        | 2024. 04. 15 | 600-0000-0195            | PH2.2-8PIN DIP CONNECTOR | 3     |
| X. XX                                | ± 0. 20 | X. X°  | ± 2° |  | UNIT  | Zhao long       | 2024. 04. 15 | PARTS NO. (INTENDED USE) | CUSTOMER DRAWING         | SHEET |
| X. XXX                               |         | X. XX° | ± 1° |  | SIZE  | Ady zhou        | 2024. 04. 15 | APC6-08XK-X-X            |                          | 3/4   |



标签黏贴处(朝卷装包材的小定位孔一侧)  
Location of label sticking (label at small positioning hole of the carrier tape side).

② 每卷包装盘缠一圈保护带。  
Each reel use 1 circle protect belt.

保护带 Protect belt

自粘膜  
self-adhesive tape

载带 Carrier tape

收料方向  
Income direction

NOTE:

- 每卷包装数量及每箱装箱数量如下表格。  
Packing q'ty of each reel & carton as below table shown.
- 把1个卷盘和1个干燥剂装入真空袋抽真空包装。  
put 1pc reel and 1pc desiccant into vacuum bag, and then vacuum packing.
- 以上胶带覆盖下包装带经包装机包装。  
Use cover tape to cover and seal up.
- 每个纸箱放2个珍珠棉。  
Every carton use 2pcs EPE.
- 将装满产品的卷盘放入纸箱并以胶带封口。  
Put reels in the carton and use adhesive tape to seal up.
- 产品拆封后请在168小时内使用完，否则会有过炉起泡风险。  
Please use the product in 168h after the product is opened, otherwise, there will be a risk of bubbling.
- 若无法在168小时内使用完的产品，需抽真空包装。  
If you can't use the product in 168h, need to be vacuum packing.

| 产品料号<br>(PRODUCT No.) | 包装数量 (PACKING CAPACITY) |              |            |
|-----------------------|-------------------------|--------------|------------|
|                       | PCS/REEL                | REELS/CARTON | PCS/CARTON |
| APC6-08XK-X-0         | 100                     | 4            | 400        |
| APC6-08XK-X-1         | 100                     | 4            | 400        |
| APC6-08XK-X-2         | 100                     | 4            | 400        |

③



ShenZhen ShenTai weixiang Electronics Co., Ltd.

TOLERANCE UNLESS OTHERWISE SPECIFIED

|        |       |        |     |
|--------|-------|--------|-----|
| X. X   | ±0.30 | X. °   | ±3° |
| X. XX  | ±0.20 | X. X°  | ±2° |
| X. XXX |       | X. XX° | ±1° |

SCALE 2:1

UNIT mm

SIZE A4



ORIGINAL DRAWN: Li jiaqi

CHECK: Zhao long

APPROVE: Ady zhou

DATE 2024.04.15

DATE 2024.04.15

DATE 2024.04.15

DWG. NO.

600-0000-0195

PARTS NO. (INTENDED USE)

APC6-08XK-X-X

TITLE

PH2. 2-8PIN DIP CONNECTOR

CUSTOMER DRAWING

REV.

3

SHEET

4/4