





G

Technical drawing of a mechanical part, likely a bracket or support, showing dimensions and tolerances. The drawing includes the following specifications:


- Overall width: 2.55
- Overall height: 2.20
- Bottom flange thickness: 1.85
- Bottom flange width: 2.15
- Bottom flange hole spacing: $N - 0.25 \pm 0.02$
- Dimension 1: Points to the top surface of the main body.
- Dimension 2: Points to the bottom surface of the main body.



Technical drawing of a PCB layout showing dimensions and labels. The drawing includes a central row of 14 vertical rectangular components, each labeled "NO.1". The components are spaced at 1.00 ± 0.05 units. The total length of the component row is $A \pm 0.05$. The components are flanked by two larger rectangular blocks, each labeled "CONN.". The left "CONN." block has a width of 3.00 and a height of 3.40. The right "CONN." block has a width of 4.30 ± 0.05 and a height of 5.05. The distance between the inner edges of the "CONN." blocks is 2.50. The distance between the outer edges of the "CONN." blocks is 2.05 . The drawing also shows a dashed line indicating a connection point.

适用线路板 (PCB LAYOUT)

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.

 深圳市虹成电子有限公司		品 名 TITLE		FPC座	
		料 号 PART NO		HC-FPC-1.0-20P-CXH25	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X. ±.50 .XX ±.10		单 位 UNIT	MM	制 图 DRAW	AhYe
.X ±.20 .XXX ±.05		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
ANGLES ±1°		版 本 REV	A	批 准 APPROVE	赵亮亮
					