




General tolerances(mm)														0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2°

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/25	/	/
IEC Standard			
Overvoltage Category/Pollution Degree	Ⅲ/3	Ⅲ/2	Ⅱ/2
Rated Voltage(V)/Current(A)	450/32	/	/
Rate Impulse Voltage(kV)	4	/	/
Torque Tightening(N·m/Lb.in)	M4 1.2/12.24		
Wire Range(rigid and flexible)(mm²/AWG)	22~12/0.5~4.0		
Pitch(mm)/Poles	9.50/N=02~26P		
Operating temperature(°C)	-40°~+105°		
Conform to RoHS	Yes		



Note:The A&Z(H) in the name means: A(H) and Z(H).			
3	Screw	Steel	Ni Plated
2	Pin header	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	料号 PART NO.	品名 TITLE	客户料号 CUTM.NO.	版本 REV.	页次 SHEET
				审核 CHECK	Yu	CUSTOMER DRAWING		A	1/1
				核准 APPROVAL	HUANG				
				单位 UNITS	RUAN				
				比例 SCALE	MM				
					1:1				

Bossie (博锡)