

浙江创都电子科技有限公司

规格承认书

SPECIFICATION FOR APPROVAL

客户名称:
CUSTOMER NAME

客户料号:
CUSTOMER NUMBER

产品规格:
PRODUCT NAME

我司型号:
PRODUCT MODEL

我司料号:
PRODUCT NUMBER

承认单位 DEPT	采购部 PURCHASE	品保部 Q C	工程部 R & D	承认章 APPROVAL SIGNET
审核 CHKD				
承认 APPD				

审核结果：
APPROVAL RESULT:

☐合格
O K

☐不合格
N G




确认后请回签一份

说明：
REMRK:



日期 (DATE):

年 (YEAR) / 月 (MONTH) / 日 (DAY)

A	H (高度)
	2.8
	3.0
	3.2
	3.5



电路图表



安装尺寸 (从焊锡面看)



序号	产品名称	材料规格	表面处理 颜色	数量	性能		未注尺寸公差 (mm)		设计	蒋 勇		产品名称: TACT SWITCH	
1	基 座	尼龙PPA	黑色	1	额定规格	DC12V/50mA	.X	±0.20	审 核	叶志龙		产品规格: TS-6645SS4.5×4.5×2.8	
2	盖 板	铁 SP12 t=0.25	镀铜锡	1	接触电阻	≤100mΩ	.XX	±0.10	标准化	胡文阳	图面	A4	浙江创都电子科技有限公司
3	簧 片	不锈钢 SUS301 t=0.25	复 银	1	绝缘电阻	≥100MΩ					单位	MM	
4	按 钮	尼龙PPA	镀 银	1	耐 电 压	AC250V/min					重量		
5	卡 座	黄铜H62 t=0.3	黑色	2	动 作 力	100/180/250g	.XXX	±0.01	批 准	张旭敏	页码	1/1	浙江创都电子科技有限公司
											版次	A/0	

浙江创都电子科技有限公司	日期 DATE	
	文件编号 Document number	
Specification 规格书		
1. 基本说明 General specification 1.1 范围 Scope 此规范含盖单推柄和无推柄的轻触开关要求 This specification covers the requirements for single key switches which have no key top(TACT SWITCHES:MECHANICAL CONTACT). 1.2 使用温度范围 Operating Temperature Range <u>-20</u> to <u>+70</u> °C 正常湿度，标准压力 (normal humidity,normal press.) 1.3 保存温度范围 Storage Temperature Range <u>-25</u> to <u>+85</u> °C 正常湿度，标准压力 (normal humidity,normal press.) 1.4 测试条件 Test Conditions 测试和计量按下列标准条件除非特殊说明： Tests and measurements shall be made in the following standard conditions unless otherwise specified: 标准温度 Normal temperature (temperature <u>5</u> to <u>35</u> °C) 正常湿气 Normal humidity (relative humidity <u>45</u> to <u>85%</u>) 标准压力 Normal pressure (pressure <u>860</u> to <u>1060</u> mbars) 2. 动作类型 TYPE OF ACTUATION <u>轻触返回</u> Tactile feedback 3. 接触形式 CONTACT ARRANGEMENT <u>1</u> 接点 <u>1</u> 回路 <u>1</u> poles <u>1</u> throws 详细接线图在外形图中 (Details of contact arrangement are given in the assembly drawings.) 4. 额定规格 MAXIMUM RATINGS DC <u>12</u> V <u>50</u> mA 5. 外观结构 Appearance and structure 5.1 外观：应无明显收缩、飞边、划伤，镀层均匀，无脱落等现象 Appearance:It should no obvious shrinkin 、upset metal、Scrape、plating path well-distributed and no coming off. 5.2 尺寸：（附外形图）Size:Making (drawing attached) 图纸见第 <u>2</u> 页 5.3 包装方式：Packaging Method(drawing attached) 图纸见第 <u>3</u> 页		
第 4 页 共 11 页		


Specification 规格书


6. 性能 General specification

6.1 电气性能 Electrical properties

项目 Item		测试条件 Test Condition	要求 Requirements
6.1.1	接触电阻 Contact Resistance	用两倍的动作力作静负载施加于按钮的中心, 并用 <u>1</u> 千赫 (kHz) 小电流接触电阻仪测量. Applying static load twice the actuating force to the center of the stem, measurements shall be made with a <u>1</u> kHz small-current contact resistance meter.	小于 <u>100</u> mΩ ≤ <u>100</u> mΩ
6.1.2	绝缘电阻 Insulation Resistance	在端子与端子之间, 端子与外壳之间施加 DC <u>100</u> V/一分钟 Measurements shall be made following application of DC <u>100</u> V potential between terminals and between individual terminals and frame for one minute.	大于 <u>100</u> MΩ ≥ <u>100</u> MΩ
6.1.3	耐 电 压 Dielectric withstanding voltage	在端子与端子之间, 端子与外壳之间施加 AC <u>250</u> V (50HZ-60HZ) AC <u>250</u> V (50Hz or 60Hz) shall be applied between terminals and between individual terminals and frame for one minute.	无击穿、闪烁现象 There shall be no breakdown
6.1.4	抖 动 Bounce	在正常使用中(以每秒 <u>3</u> - <u>4</u> 次周期)轻轻地在手柄中心加力, 在通与断瞬间测试抖动 Lightly striking the center of the stem at a rate encountered in normal use (<u>3</u> to <u>4</u> operations per sec), Bounce shall be tested when "ON" and "OFF"  示波器 Oscillograph  t 为触点抖动时间	<u>10</u> mS 以下

浙江创都电子科技有限公司		日期 DATE	
		文件编号 Document number	
Specification 规格书			
6.2 机械性能 Mechanical properties			
项目 Item		测试条件 Test Condition	要求 Requirements
6.2.1	动作力 Actuating Force	开关的动作方向为垂直放置, 开关向推柄中心逐渐地增加负荷直到推柄停止时所测量的最大负荷 Place the switch such that the direction of switch operation is vertical and then gradually increase the load applied to the center of the stem, the maximum load required for the stem to come to a stop shall be measured	250 ± 50 gf 180 ± 50 gf 100 ± 50 gf
6.2.2	行程 Travel	开关的动作方向为垂直放置开关, 并以双倍动作力的静负荷作用推柄中心, 测量推柄从开始到停止的行程距离 Place the switch such that the direction of switch operation is vertical and then apply a static load twice the actuating force to the center of the stem, the travel distance for the stem to come to a stop shall be measured	250 gf: 0.25 ± 0.05 mm 180 gf: 0.20 ± 0.05 mm 100 gf: 0.20 ± 0.05 mm
6.2.3	返回力 Return Force	开关的动作方向为垂直放置开关, 在已有行程的推柄中心向上减小压力, 推柄回到自由位置时所测量到的力 The sample switch is installed such that the direction of switch operation is vertical and, upon depression of the stem in its center the whole travel distance, the force of the stem to return to its free position shall be measured	250 gf: 80 gf min 180 gf: 60 gf min 100 gf: 40 gf min
6.2.4	静止强度 Static Strength	开关的动作方向为垂直放置开关, 在推柄动作方向施加 <u>1KG</u> 的静负荷, 持续 <u>60</u> 秒 Placing the switch such that the direction of switch operation is vertical, a static load of 3 kgf shall be applied in the direction of stem operation for a period of 60 seconds	无机械的和电气的损伤迹象 There shall be no sign of damage mechanically and electrically

浙江创都电子科技有限公司		日期 DATE	
		文件编号 Document number	
Specification 规格书			
项目 Item		测试条件 Test Condition	要求 Requirements
6.3.4	耐 热 Heat Resistance	样品按下列条件进行耐热试验, 试验后在正常温度和湿度条件下放置 <u>1</u> 小时后测定 Following the test set forth below the sample shall be left in normal temperature and humidity conditions for one hour before measurements are made (1)温 度 Temperature: <u>70 ± 2</u> °C (2)时 间 Time: <u>96</u> 小时 hours	接触电阻 Contact resistance: <u>300 mΩ</u> Max. 绝缘电阻 Insulation resistance: <u>100 MΩ</u> Min 项目 Item 6.1.3、6.1.4 项目 Item 6.2.1~6.2.3
6.3.5	温度循环 Change of Temperature	样品按下列条件进行高低温循环试验, 试验后在正常温度和湿度条件下放置 <u>1</u> 小时后测定 Following ten cycles of high temperature test. The Sample shall be Placed in Normal temperature and humidity Conditions for one hour before measurements are made. During this test, water drops shall be removed  A: <u>+ 85 ± 2</u> °C B: <u>- 25 ± 2</u> °C C: <u>2</u> 小时 D: <u>1</u> 小时 E: <u>2</u> 小时 F: <u>1</u> 小时 周 期: <u>5</u> 次 Cycling: Five cycles	接触电阻 Contact resistance: <u>300 mΩ</u> Max. 绝缘电阻 Insulation resistance: <u>100 MΩ</u> Min 项目 Item 6.1.3、6.1.4 项目 Item 6.2.1~6.2.3
6.3.6	盐雾测试 Salt Spray Test	样品按下列条件进行盐雾试验 The salt spray test shall be conducted at the following conditions: (1)浓 度 Density: 溶液 (<u>5 ± 1</u>) %NaCl(质量百分比) (2)温 度 Temperature: <u>35 ± 2</u> °C (3)时 间 Time: 铁盖 <u>2~4</u> 小时 hours 铜盖 <u>24</u> 小时 hours	金属件无发黄、生锈 No yellowing and rusting of metal parts

浙江创都电子科技有限公司		日期 DATE	
		文件编号 Document number	
Specification 规格书			
项目 Item		测试条件 Test Condition	要求 Requirements
6.3.7	耐 振 动 Vibration Resistance	按下列条件进行抗振动试验 Measurements shall be made following the test set forth below: (1) 频率范围 Range of oscillation: <u>10</u> to <u>55</u> Hz (2) 振幅 Amplitude: 峰-峰 <u>1.5</u> mm(pk-to-pk: <u>1.5</u> mm) (3) 扫描周期 Cycle of sweep: <u>10</u> - <u>55</u> - <u>10</u> Hz 约一分钟内(in one minute, approx.) (4) 扫描方式 Mode of sweep: 对数扫描式恒定扫描(Logarithmically sweep or uniform sweep.) (5) 振动方向 Direction of oscillation: <u>3</u> 个相互垂直方向, 包括推柄行程方向(Three mutually perpendicular directions, including the direction of stem travel.) (6) 每方向 <u>2</u> 小时. 共 <u>6</u> 小时 (<u>2</u> hours each, for a total of <u>6</u> hours.)	项目 Item 6.1 项目 Item 6.2.1、6.2.2
6.3.8	抗 冲 击 Impact Shock Resistance	按下列条件进行冲击试验 Measurements shall be made following the test set forth below: (1) 加速度 Acceleration: <u>80</u> g (2) 试验次数 Cycles of test: 每个方向 <u>3</u> 次, <u>6</u> 个方向共 <u>18</u> 次(<u>3</u> cycles each in <u>6</u> directions, for a total of <u>18</u> cycles) 	项目 Item 6.1 项目 Item 6.2.1、6.2.2

Specification 规格书

7. 焊接条件 Welding conditions

项目 Item	推荐条件 Recommended conditions
7.1 手工焊接 Hand soldering	请按以下条件进行焊接： (1)焊锡温度：$\leq 380\text{ }^{\circ}\text{C}$ (2)连续焊接时间：$\leq 3\text{ S}$ (3)电烙铁的功率：$\leq 60\text{ W}$ Please practice according to bellow conditions: (1)Soldering temperature :$\leq 380\text{ }^{\circ}\text{C}$ (2)Continuous soldering time:$\leq 3\text{ S}$ (3)Capacity of soldering iron:$\leq 60\text{ W}$
7.2 自动焊接 Automatic flow soldering	本产品，请按以下条件进行焊接： This product ,type solder according to the following conditions: 产品表面温度$^{\circ}\text{C}$ surface of product temperature 最高温度260°C 最高三秒 $260^{\circ}\text{C max. 3sec max}$ peak temperature 时间(秒) time(sec) 最多120秒 120sec max. 预热 pre-heating 最多40秒 40s max. 最高3到4分钟 3~4min. max. 注意：以上提及的条件是零部件上 PWB 表面的温度,由于 PWB 的材料、尺寸、厚度等不同,PWB 从开关表面获得的温度也会有很大产不同，因此，千万小心不要让开关表面温度超过 260°C。 Caution: the condition mentioned above is a temperature on the PWB surface on which parts are mounted. There are cases where PWB temperature greatly differs from switch's surface temperature depending on PWB material,size, thickness,etc. The switch's surface temperature shall not allowed to exceed 260°C

浙江创都电子科技有限公司	日期 DATE	
	文件编号 Document number	

Specification 规格书

8. 其他注意事项 Other precautions
- (1) 进行焊接过程中, 不可以用溶剂或类似品清洗开关

Following the soldering process, do not try to clean the switch with a solvent or the like.
- (2) 防止助焊剂从开关的顶端渗入

Safeguard the switch assembly against flux penetration from its topside.
- (3) 交货后保证开关处于封密状态并库存时间 90 天以下。

Please have the products keep in close status and the storage time is 90 days guaranty after delivering the goods at most.