

General Description

The CMSA90DP03 combines advanced trench MOSFET technology with a low resistance package to provide extremely low RDS(ON). This device is ideal for load switch and battery protection applications.

Features

- Low On-Resistance
- 100% avalanche tested
- Small Footprint (5x6 mm) for Compact Design
- RoHS Compliant


Product Summary

BVDSS	R _{DS(on)} max.	ID
-30V	9.6mΩ	-90A

Applications

- High side in DC - DC Buck Converters
- Notebook battery power management
- Load switch in Notebook

DFN-8 5X6 Dual Pin Configuration



Type	Package	Marking
CMSA90DP03	DFN-8 5X6 Dual	CMSA90DP03

Absolute Maximum Ratings (T_A=25 °C Unless Otherwise Noted)

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	-30	V
V _{GS}	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current	-90	A
I _D @T _C =100°C	Continuous Drain Current	-63	A
I _{DM}	Pulsed Drain Current	-360	A
EAS	Single Pulse Avalanche Energy ¹	135	mJ
P _D @T _C =25°C	Total Power Dissipation	80	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	62	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	1.56	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=-250\mu A$	-30	---	---	V
$R_{DS(on)}$	Static Drain-Source On-Resistance	$V_{GS}=-10V$, $I_D=-20A$	---	8.4	9.6	mΩ
		$V_{GS}=-4.5V$, $I_D=-15A$	---	11.2	13	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D = -250\mu A$	-1	---	-2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-24V$, $V_{GS}=0V$	---	---	-1	uA
I_{GSS}	Gate-Source Leakage Current	$V_{GS} = \pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=-10V$, $I_D=-20A$	---	18	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	23	---	Ω
Q_g	Total Gate Charge	$V_{DS}=-24V$, $I_D=-20A$ $V_{GS}=-10V$	---	58	---	nC
Q_{gs}	Gate-Source Charge		---	7	---	
Q_{gd}	Gate-Drain Charge		---	16	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=-15V$, $V_{GEN}=-10V$, $I_D=-10A$ $R_G=4.7\Omega$	---	7	---	ns
T_r	Rise Time		---	14	---	
$T_{d(off)}$	Turn-Off Delay Time		---	86	---	
T_f	Fall Time		---	252	---	
C_{iss}	Input Capacitance	$V_{DS}=-25V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2200	---	pF
C_{oss}	Output Capacitance		---	255	---	
C_{rss}	Reverse Transfer Capacitance		---	190	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V$, Force Current	---	---	-90	A
I_{SM}	Pulsed Source Current		---	---	-360	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V$, $I_S=-20A$, $T_J=25^{\circ}\text{C}$	---	-0.88	-1.3	V

Note :


1.The EAS data shows Max. rating . The test condition is $V_{DD}=-25V$, $V_{GS}=-10V$, $L=0.3\text{mH}$, $I_{AS}=-30A$.

This product has been designed and qualified for the consumer market.


Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.


Typical Characteristics




On-Region Characteristics




transfer characteristics




On-Resistance vs. Drain Current



Gate Charge Characteristics



Capacitance Characteristics






Body Diode Forward Voltage Variation with Source Current and Temperature

Package Dimension

DFN-8 5X6 Dual

Unit :mm



SYMBOL	COMMON			
	MM		INCH	
	MIN.	MAX.	MIN.	MAX.
A	1.03	1.17	0.0406	0.0461
b	0.34	0.48	0.0134	0.0189
c	0.203 BSC		0.0080 BSC	
D	4.80	5.40	0.1890	0.2126
D1	4.80	5.00	0.1890	0.1969
D2	4.11	4.31	0.1620	0.1700
D3	1.60	1.80	0.0629	0.0708
E	5.95	6.15	0.2343	0.2421
E1	5.65	5.85	0.2224	0.2303
E2	3.30	3.50	0.1300	0.1378
E3	1.40	/	0.0551	/
e	1.27 BSC		0.05 BSC	
L	0.05	0.25	0.0019	0.0098
L1	0.38	0.50	0.0150	0.0197
L2	0.38	0.71	0.0150	0.0280
i	/	0.18	/	0.0070
k	0.5	0.7	0.0197	0.0276