




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A2	1	开新模更新模具外观形状	Chen HongJiang	Chen ZhiQiang	2024.07.27

- SPECIFICATIONS
- Current rating: 3A AC, DC
 - Temperature range: -25°C ~ +85°C
 - Insulation Resistance: 1000MΩ Min.
 - Withstanding voltage: 1000V AC/ minute.
 - Contact Resistance: 10mΩ Max.

Material:
Insulator: LCP UL 94V-0
Contact: Brass
Solder Tab: Brass
Plating: Tin plated
Circuits: 02~12P
Mate with:XFCN P2501L series Housing

Ordering Code:
M2501RSF-XX
1 2
1.序列号
2.Pin位数: 02-16P

PIN	尺寸 (mm)		
	A	B	C
02	2.50	7.50	10.00
03	5.00	10.00	12.50
04	7.50	12.50	15.00
05	10.00	15.00	17.50
06	12.50	17.50	20.00
07	15.00	20.00	22.50
08	17.50	22.50	25.00
09	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: M2501RSF-XX		XFCN 兴飞连接器		
TITLE: 2.50mm Crimp Style Connectors		0769-82001899		
		www.xfconn.com		
		DWG NO: /		
APPD	Chen ZhiQiang	VIEW		
CHKD	Liu Wei			
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2024.07.27	NONE	1/1	A2