







RoHS



RECOMMENDED P.C.B LAYOUT

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	NYLON UL94V-0	WHITE / BLACK	1
2	CONTACT	BRASS	THE SURFACE: TIN	N/A
3	STATOR	BRASS	THE SURFACE: TIN	2

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS.

2. PRODUCT PERFORMANCE:

2.1 RATED VOLTAGE(MAX.):100V AC/DC

2.2 RATED CURRENT(MAX.):2.0A AC/DC

2.3 DIELECTRIC STRENGTH:800V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN

2.4 INSULATION RESISTANCE:1000 MΩ MIN. 500VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL

2.5 CONTACT RESISTANCE:20 mΩ MAX.

2.6 OPERATING TEMPERATURE:-25°C to +85°C

3.PART NO. LEGEND: 1WF06-025 0XX-0000X

WATER CODE
002:2PIN




PIN	WATER CODE	NOTES
2P	00001	NYLON BLACK
2P	00002	NYLON WHITE
3P	00001	NYLON BLACK
3P	00002	NYLON WHITE
4P	00001	NYLON BLACK
4P	00002	NYLON WHITE
5P	00001	NYLON BLACK
5P	00002	NYLON WHITE
6P	00001	NYLON BLACK
6P	00002	NYLON WHITE
7P	00001	NYLON WHITE
8P	00001	NYLON WHITE
10P	00001	NYLON WHITE
12P	00001	NYLON WHITE

Circuit No.	Dimensions	
	A	B
02P	2.00	8.00
03P	4.00	10.00
04P	6.00	12.00
05P	8.00	14.00
06P	10.00	16.00
07P	12.00	18.00
08P	14.00	20.00
09P	16.00	22.00
10P	18.00	24.00
11P	20.00	26.00
12P	22.00	28.00
13P	24.00	30.00
14P	26.00	32.00
15P	28.00	34.00
16P	30.00	36.00

HIN-BAN
Electronic Technology



5.0				DRAWING:	GENERAL TOLERANCE .X:=±0.30 .X*::=±2° .XX:=±0.25 .XX*::=±1° .XXX:=±0.15 .XXX*::=±0.5°			
4.0	2022.10.14	Added 12PIN specifications	ShunMingWen	Chen jie				
3.0	2022.03.23	MODIFY PRODUCT NUMBER	ShunMingWen	CHECKED:	UNIT: MM	PROJECTION:	DESCRIPTION: 2.00 mm Pitch Wafer Side Entry SMT Type	
2.0	2016.08.22	All customers increased by logo "CB"	Tian Hai	Tian Hai	SCALE: 1/1		PART NO: 1WF06-0250XX-0000X	REV: 4.0
1.0	2016.08.16	NEW	Tian Hai	APPROVAL:	SHEET: 1/1		OLD CODE: WB2008UR-XXTX-CB	SIZE: A4
NO.	DATE	DESCRIPTION	DRAWING	Cykin			DRAWING NO: UK0306	

RoHS+REACH



PACKING INFORMATION:

PIN	W	F	PCS/REEL	REEL/CARTON	TOTAL	CARTON
02	16.0	7.5	1000PCS	11PCS	11000PCS	350*350*296mm
03~05	24.0	11.5	1000PCS	8PCS	8000PCS	350*350*296mm
06~08	32.0	14.25	1000PCS	7PCS	7000PCS	350*350*296mm
09~13	44.0	20.25	1000PCS	5PCS	5000PCS	350*350*296mm
14	44.0	20.5	1000PCS	5PCS	5000PCS	350*350*296mm
15~16	56.0	26.25	1000PCS	4PCS	4000PCS	350*350*296mm



NOTE:(说明)

1. PEELING OFF FORCE OF COVER TAPE: 0.6-1.0N (盖带剥离力: 0.6-1.0N)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)


(剥离方向如下图所示)

THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT

(这一要求应在装运时适用)

PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.

(运输过程中不允许剥落。)



2. MATERIAL: (材料)

CARRIER TAPE: POLYSTYREN(PS)(载带: PS)

COVER TAPE: TAPE (盖带: TPE)

REEL TAPE: PS(卷盘 PS)

3. PART NUMBER: (料号)

1WF06-0250XX-0000X

5: COLD SEALING(冷封规格)

CHIN-BAN
Electronic Technology

DESCRIPTION: 2.00mm Pitch Wafer Side Entry SMT Type-PACKING

PART NO: F-1WF06-0250XX-0000X

REV: 2.0

PART NO: F-WB2008UR-XXTX-CB

DRAWING NO: UT0097

SIZE: A4

DRAWING:

ShunMingWen

CHECKED:

APPROVAL:

GENERAL TOLERANCE


.X:=±0.50 .X*:=±2°
.XX:=±0.30 .XX*:=±1°
.XXX:=±0.20 .XXX*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1/1

SHEET: 1/1



5.0			
4.0			
3.0			
2.0	22.03.23	调整产品品号信息	ShunMingWen
1.0	16.08.16	NEW	Tianhai
NO.	DATE	DESCRIPTION	APPROVAL