

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

APPROVAL SHEET






CUSTOMER: _____

CUSTOMER P/N: _____ (小批可用管装) (批货推荐卷装)


PART NAME: 1.0mmPitch H=2.5mm SMT 拉拔K型 上接

PART NO. : CAX-AFA07-04SCB-H2.5

MANUFACTURE SIGNATURE			CUSTOMER SIGNATURE
SALES REP.	R&D DEPT.	QA DEPT	
DAET:	DAET:	DAET:	DAET:



RECOMMENDED P.C.B. PATTERN LAYOUT



RECOMMENDED FPC/FFC DIMENSION

Note:

1. Material:

- 1.1 Housing: thermoplastic high temp.UL94V-0; Color: natural.
- 1.2 Latch: thermoplastic high temp.UL94V-0; Color: black.
- 1.3 Terminal: copper alloy.
- 1.4 Fitting Nail: copper alloy.

2. Finish:

- 2.1 Terminal:
Underplating: Au/matt Tin overall.
- 2.2 Fitting Nail:
Underplating: matt Tin overall.

3. Product must comply HF RoHS specification.

4. Product No:

AFA07-S ** E * * - **
CKTS CONTACTS TYPE REMARKS
E:Upper HF:Halogen free
PLATING
1:Gold flash 1u"
2:Gold flash 2u"
3:Gold flash 3u"
B:Bright-Tin 80-150u"
C:Matte-Tin 80-150u"
PACKING
A:Tape&Reel
C:Tube

CKTS	DIM A	DIM B	DIM C	DIM D
4	3.00	5.10	9.05	11.00
5	4.00	6.10	10.05	12.00
6	5.00	7.10	11.05	13.00
7	6.00	8.10	12.05	14.00
8	7.00	9.10	13.05	15.00
9	8.00	10.10	14.05	16.00
10	9.00	11.10	15.05	17.00
11	10.00	12.10	16.05	18.00
12	11.00	13.10	17.05	19.00
13	12.00	14.10	18.05	20.00
14	13.00	15.10	19.05	21.00
15	14.00	16.10	20.05	22.00
16	15.00	17.10	21.05	23.00
17	16.00	18.10	22.05	24.00
18	17.00	19.10	23.05	25.00
19	18.00	20.10	24.05	26.00
20	19.00	21.10	25.05	27.00
21	20.00	22.10	26.05	28.00
22	21.00	23.10	27.05	29.00
23	22.00	24.10	28.05	30.00
24	23.00	25.10	29.05	31.00
25	24.00	26.10	30.05	32.00
26	25.00	27.10	31.05	33.00
27	26.00	28.10	32.05	34.00
28	27.00	29.10	33.05	35.00
29	28.00	30.10	34.05	36.00
30	29.00	31.10	35.05	37.00

CUSTOMER DRAWING

Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.25 0° ±5°	Unit(单位): MM
0.00 ±0.15 0°0 ±3°	Scale(比例): 1:1
0.000 ±0.10 0°00 ±1°	Project View (投影视角)
Rev 版本	Page(页数): 1 OF 1
Rev 版本	Rev(版本): A

浙江创都电子科技有限公司


ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

Product Name(产品名称):
1.0Pitch H=2.5 FPC/FFC ZIF R/A TypeK1 Upper SMT CONN

Product No(产品料号):
CAX-AFA07-04SCB-H2.5

Designer(设计):
Checked(审核):
Approved(核准):

Rev 版本	Change Description 变更内容	Date 日期	Revisor 制/修订人
A	初版发行	2011/03/23	



CLASSIFICATION DIMENSION(尺寸类别):	
FAI(首次检验): ☉To ☉	
■"MARK IS MAJOR DIM(重点尺寸标示) ☉"MARK IS CRITICAL DIM(pk&pC标示)	
Tolerance Unspecified (未注公差)	Size(图幅): A4
0.0 ±0.10 0° ±3°	Unit(单位): MM
0.00 ±0.05 0° 0° ±2°	Scale(比例): 1 : 1
0.000 ±0.02 0° 0° ±1°	
Project View (投影视角)	Page(页数): 10 OF 10
	Rev(版本号): 1.0

DNE00013-1		2011/04/09	
Designer(设计):		Checked(审核):	Approved(核准):

1.0	初版发行	2011/04/09	
Rev 版本	Change Description 变 更 内 容	Date 日期	Revisor 制/修订人

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

产 品 规 格 书 PRODUCT SPECIFICATION

【1】适用范围 SCOPE

本规格书适用于 1.0mm Pitch H=2.5 FPC/FFC 拉拔卧式 K 型 SMT 型连接器系列。

This specification covers the 1.0mm Pitch H=2.5 FPC/FFC ZIF R/A TypeK SMT Connectors series.

【2】外观尺寸 CONNECTOR DIMENSIONS

请参照图面

See attached drawings.

【3】材质 MATERIAL

绝缘胶体 Housing: LCP

颜色 Color:自然色 Natural.

耐燃等级 (UL94V-0) Flammability Rating (UL94V-0).

后盖 Latch: LCP

颜色 Color:黑色 Black.

耐燃等级 (UL94V-0) Flammability Rating (UL94V-0).

端子 Terminal: 磷青铜 Phosphor Bronze.

焊片 Fitting Nail: 磷青铜 Phosphor Bronze.

【4】建议 P.C.B LAYOUT 图 ACCOMMODATED P.C.B LAYOUT

请参照图面

See attached drawings.

【5】等级 RATING

项 目 ITEM	规 格 SPECIFICATIONS
最大容许电压 Operating Voltage (Max.)	50V AC
最大容许电流 Current Rating (Max.)	0.5A DC
使用温度范围 Operating Temperature range	*-55° C ~ +85° C
使用湿度范围 Operating humidity range	相对湿度90%以下 Relative humidity 90% max.
保存温度范围 Storage temperature range	-40° C ~ +50° C
保存湿度范围 Storage humidity range	相对湿度90%以下 Relative humidity 90% max.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

*:包含电流通过所产生的上升温度 Including terminal temperature rise.

【6】性能 PERFORMANCE

6.1 电气特性 ELECTRICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
接触阻抗 Contact Resistance	将样品与适合之FPC/FFC连接, 测试电压20mV, 限电流100mA下进行阻抗测试。(EIA-364-23) Mate applicable FPC/FFC and measure by dry circuit, 20mV Max, 100mA. (EIA-364-23)	40 mΩ最大. 40 mΩ Max.
绝缘阻抗 Insulation Resistance	将样品与适合之FPC/FFC连接, 提供相邻端子间测试电压500V DC进行绝缘阻抗测试(EIA-364-21) Mate applicable FPC/FFC and apply 500V DC between adjacent terminal or ground. (EIA-364-21)	500 MΩ最小. 500 MΩ Min.
耐电压 Dielectric Strength	将样品与适合之FPC/FFC连接, 相邻端子间需可承受250V AC(rms) 1分钟。(EIA-364-20) Mate applicable FPC/FFC , apply 250V AC(rms) for 1 minute between adjacent terminal or ground. (EIA-364-20)	目视外观无任何损坏异状 No Breakdown

6.2 机械特性 MECHANICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
FPC保持力 FPC Retention Force	将盖子盖上, 与FPC/FFC连接, 以操作速度每分钟位移25±3mm进行FPC/FFC保持力测试。(EIA-364-13) Insert the Latch, pull the FPC at a rate of 25±3mm per minute. (EIA-364-13)	Pos. x 0.40N最小 Pos. x 0.40N Min.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

端子保持力 Terminal Retention Force	端子与Housing组装后,以操作速度每分钟位移 $25\pm 3\text{mm}$ 将端子拔出Housing,进行端子保持力测试。 (EIA-364-29) Apply axial pull out force at the rate of $25\pm 3\text{ mm/minute}$ on the terminal assembled in the housing. (EIA-364-29)	3.0N最小. 3.0N Min.
项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
焊片保持力 Fitting Nail Retention Force	焊片与Housing组装后,以操作速度每分钟位移 $25\pm 3\text{mm}$ 将焊片拔出Housing,进行焊片保持力测试。 (EIA-364-29) Apply axial pull out force at the rate of $25\pm 3\text{ mm/minute}$ on the Fitting Nail assembled in the housing. (EIA-364-29)	1.0N最小. 1.0N Min

6.3 环境特性及其它性能 ENVIRONMENTAL PERFORMANCE AND OTHERS

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐久性 Durability	将盖子与FPC/FFC反复连接,以每分钟小于10 Cycles连续操作20次。 (EIA-364-09) Insert and withdraw actuator up to 20 cycles at the speed rate of less than 10 cycles/minute. (EIA-364-09)	接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
温度上升 Temperature Rise	量测通过FPC/FFC最大容许电流时,样品接触点之温升。 (EIA-364-70 Method2) Mate applicable FPC/FFC and measure the temperature rise of contact when the maximum AC rated current is passed. (EIA-364-70 Method 2)	温升 Temperature Rise	30° C最大. 30° C Max.

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

耐振性 Vibration	通过DC电流100mA，位移相对距离1.5mm，振动周期10~ 55~ 10 Hz在1分钟内，持续2小时，方向在X, Y, Z轴做测试。(EIA-364-28 Condition I) Mate connectors and subject to the following vibration conditions, for period of 2 hours in each of 3 mutually perpendicular axes, passing DC 100mA during the test. Amplitude : 1.5mm P-P Frequency : 10~ 55~ 10 Hz in 1 minute. Duration : 2 hours in each of X, Y, Z axes. (EIA-364-28 Condition I)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ最大. 60mΩ Max.
		瞬间断电 Discontinuity	1 μ sec最大 1 μ sec Max.
项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐冲击性 Shock	将样品与适合之FPC/FFC连接，通过DC 100 mA测试条件，连续测试3次。在X、Y、Z 3轴6个垂直方向施于重力加速度490m/s2 {50G} 冲击。 (EIA-364-27, Test condition A) Mate applicable FPC/FFC and subject to the following shock conditions. 3 times of shocks shall be applied for each 6 directions along 3 mutually perpendicular axes, passing DC 100 mA current during the test. (Total of 18 shocks) Peak value : 490m/s2 {50G} (EIA-364-27, Test condition A)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
		瞬间断电 Discontinuity	1 μ sec 最大 1 μ sec Max.
耐热性 Heat Resistance	将样品与适合之FPC/FFC连接，置于环境温度85±2° C测试时间96小时，再置放于室温下1~ 2小时。 (EIA-364-17) Mate applicable FPC/FFC and expose	外观 Appearance	目视外观无任何损坏异状 NoDamage

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

	to $85\pm 2^{\circ}\text{C}$ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-17)	接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
耐寒性 Cold Resistance	将样品与适合之FPC/FFC连接, 置于环境温度 $-40\pm 2^{\circ}\text{C}$, 测试时间96小时, 再置放于室温下1~ 2小时。 (EIA-364-59) Mate applicable FPC/FFC and expose to $-40\pm 2^{\circ}\text{C}$ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-59)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT	
耐湿性 Humidity	将样品与适合之FPC/FFC连接, 置于环境温度 $40\pm 2^{\circ}\text{C}$, 相对湿度90~ 95%, 测试时间96小时, 再置放于室温下1~ 2小时。(EIA-364-31) Mate applicable FPC/FFC and expose to $40\pm 2^{\circ}\text{C}$, relative humidity 90 to 95% for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. (EIA-364-31)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60m Ω 最大. 60m Ω Max.
		耐电压 Dielectric Strength	需能符合耐电压测试 No Breakdown
		绝缘阻抗 Insulation Resistance	20 M Ω 最小. 20 M Ω Min

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

热冲击 Thermal Shock	将样品与适合之FPC/FFC连接, 承受5 cycles冷热冲击后放置于室温下1~ 2 小时。1 cycle time如下 a) $-55\pm 3^{\circ}\text{C}$ 30分钟 b) $+85\pm 3^{\circ}\text{C}$ 30分钟 (EIA-364-32) Mate applicable FPC/FFC and subject to the following conditions for 5 cycles. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. 1 cycle a) $-55\pm 3^{\circ}\text{C}$ 30minutes b) $+85\pm 3^{\circ}\text{C}$ 30minutes (EIA-364-32)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
盐水喷雾 Salt Spray	将样品与适合之FPC/FFC连接, 使用 $5\pm 1\%$ 浓度盐水, 测试温度 $35\pm 2^{\circ}\text{C}$, 镀金: 1~ 2u", 测试时间 24 ± 4 小时, 镀金: 3u" 及以上, 测试时间 48 ± 4 小时, 后于室温下使用清水冲洗后再干燥。(EIA-364-26) Mate applicable FPC/FFC and expose to the following salt mist conditions. Upon completion of the exposure period, salt deposits shall be removed by a gentle wash or dip in running water, after which the specified measurements shall be performed. NaCl solution Concentration : $5 \pm 1\%$ Gold plating: 1~ 2u " Spray time : 24 ± 4 hours Gold plating: 3u "and above Spray time : 48 ± 4 hours Ambient temperature : $35 \pm 2^{\circ}\text{C}$ (EIA-364-26)	外观 Appearance	目视外观无任何损坏异状 NoDamage
		接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
项目	测试条件	规格	

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A


ITEM	TEST CONDITION	REQUIRMENT	
焊锡性 Solderability	锡温 $245\pm5^{\circ}\text{C}$, 将导电端子浸入锡炉液面至Housing距离锡面0.1mm位置, 焊锡时间 3 ± 0.5 秒。(EIA-364-52) Tip of solder tails and fitting nails into the molten solder (held at $245\pm5^{\circ}\text{C}$) up to 0.1mm from the bottom of the housing for 3 ± 0.5 seconds. (EIA-364-52)	润湿性 Solder Wetting	润湿面积95%以上, 并不得有漏焊针孔现象 95% of immersed area must show no voids, pin holes.
焊锡耐热性 Resistance to Soldering Heat	使用红外线回焊时请参考第7 When reflowing Refer to paragraph 7. 使用烙铁手焊时须可符合下述焊锡条件。(EIA-364-56) Soldering iron method 0.2mm from terminal tip and fitting nail tip. Soldering time : 5 seconds Max. Solder temperature : $370\sim 400^{\circ}\text{C}$. (EIA-364-56)	外观 Appearance	目视外观无任何损坏异状 NoDamage

浙江创都电子科技有限公司

ZHE JIANG CHUANG DU ELECTRONICS CO.,LTD

REV. A

【7】红外线回焊温度曲线 INFRARED REFLOW CONDITION



温度条件TEMPERATURE CONDITION GRAPH
(基板表面温度) (TEMPERATURE ON BOARD PATTERN SIDE)