








RoHS

Circuit 1



3P及以上
底部有凸筋

2P
底部无凸筋



NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	INSULATOR	LCP (UL94V-0)	Natural	1
2	CONTACTS	COPPER ALLOY	Tin-Plated	N
3	SOLDER TAP	COPPER ALLOY	Tin-Plated	2

NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS.
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):50V AC/DC
2.2. RATED CURRENT(MAX.):1.0A AC/DC
2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
2.4 INSULATION RESISTANCE:500 MΩ MIN. 500VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL
2.5 CONTACT RESISTANCE:20 mΩ MAX.
2.6 OPERATING TEMPERATURE:-25°C to +85°C
3.PART NO. LEGEND:

1WF05-115XXX-00001

00001:Water code
See the table below
005: 5PIN

PIN	DIM A	DIM B	DIM C
2P	6.00	3.60	1.50
3P	7.50	5.10	3.00
4P	9.00	6.60	4.50
5P	10.50	8.10	6.00
6P	12.00	9.60	7.50
7P	13.50	11.10	9.00
8P	15.00	12.60	10.50
9P	16.50	14.10	12.00
10P	18.00	15.60	13.50
11P	19.50	17.10	15.00
12P	21.00	18.60	16.50
13P	22.50	20.10	18.00
14P	24.00	21.60	19.50
15P	25.50	23.10	21.00
16P	27.00	24.60	22.50

规格	新品号
2P	1WF05-115002-00001
3P	1WF05-115003-00001
4P	1WF05-115004-00001
5P	1WF05-115005-00001
6P	1WF05-115006-00001
7P	1WF05-115007-00001
8P	1WF05-115008-00001
10P	1WF05-115010-00001
12P	1WF05-115012-00001
13P	1WF05-115013-00001

DRAWING:

ShunMingWen

CHECKED:

Tian hai

APPROVAL:

Cykin

GENERAL TOLERANCE

.X:=±0.30

.X*:=±2°

.XX:=±0.20

.XX*:=±1°

.XXX:=±0.10


.XXX*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1/1

SHEET: 1/1



CHIN-BAN
Electronic Technology

DESCRIPTION:

1.5PITCH 90° WAFER SMT TYPE CONN

PART NO: 1WF05-115XXX-0000X

REV: 3.0

DRAWING NO: UK0446

SIZE: A4

5.0

4.0

3.0

2.0

1.0

NO.

1

2

3

4



5

6

7

8


RoHS



产品标签 (1PCS/REEL)
条形码 (1PCS/REEL)
此位置背面
(保护带) PROTECTION TAPE



1000PCS/REEL
(1000pcs/卷)

N PCS REELS
(N pcs/卷)



PACKING INFORMATION:

PART NAME	W	PCS/REEL	REEL/CARTON	TOTAL	CARTON
1WF05-115002-00001	16.0	1000PCS	11PCS	11000PCS	350*350*296mm
1WF05-115003-00001	16.0	1000PCS	11PCS	11000PCS	350*350*296mm
1WF05-115004-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF05-115005-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF05-115006-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF05-115007-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF05-115008-00001	24.0	1000PCS	8PCS	8000PCS	350*350*296mm
1WF05-115010-00001	32.0	1000PCS	6PCS	6000PCS	350*350*296mm
1WF05-115012-00001	32.0	1000PCS	6PCS	6000PCS	350*350*296mm
1WF05-115013-00001	44.0	1000PCS	5PCS	5000PCS	350*350*296mm




NOTE:(说明)

1. PEELING OFF FORCE OF COVER TAPE: 0.6-1.0N (盖带剥离力: 0.6-1.0N)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)


(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT

(这一要求应在装运时适用)
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.
(运输过程中不允许剥落。)



2. MATERIAL: (材料)

CARRIER TAPE: POLYSTYREN(PS) (载带: PS)
COVER TAPE: TAPE (COLD-SEAL) 盖带: TPE (冷封)
REEL TAPE: PS (卷盘 PS)

G	5.0	22.04.02	更新图框LOGO信息	ShunMingWen	DRAWING:	GENERAL TOLERANCE				G
	4.0	21.10.27	新增13PIN规格	ShunMingWen	ShunMingWen	.X:=±0.50 .X*: =±2° .XX:=±0.30 .XX*: =±1° .XXX:=±0.20 .XXX*: =±0.5°				
	3.0	21.04.27	新增7PIN规格	ShunMingWen		CHECKED:				
H	2.0	21.03.29	调整产品包材使用要求	ShunMingWen	Tian hai	UNIT: MM	PROJECTION:	DESCRIPTION:		H
	1.0	20.11.05	NEW	ShunMingWen	APPROVAL:	SCALE: 1/1		1.5PITCH 卧式WAFER—卷装—包装图		
								PART NO: F—1WF05—115XXX—0000X	REV: 5.0	
								DRAWING NO: UT0218	SIZE: A4	
	NO.	DATE	DESCRIPTION	DRAWING	Cykin	SHEET: 1/1				