


Features

- 500 Watts Peak Pulse Power per Line ($t_p = 8/20\mu s$)
- Replacement for MLV (0805)
- Protects one I/O or power line
- Low Clamping Voltage
- Working Voltage: 5 V
- Low Leakage Current



IEC COMPATIBILITY (EN61000-4)

- IEC 61000-4-2 (ESD) $\pm 30kV$ (air), $\pm 30kV$ (contact)
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 28A (8/20 μs)


Mechanical Characteristics

- JEDEC SOD-323 package
- Molding compound flammability rating: UL 94V-0
- Marking : Marking Code
- Packaging : Tape and Reel per EIA 481
- RoHS Compliant

Applications

- Laptop Computers
- Cellular Phones
- Digital Cameras
- Personal Digital Assistants (PDAs)

Schematic & PIN Configuration




SOD-323 (Top View)

Absolute Maximum Rating			
Rating	Symbol	Value	Units
Peak Pulse Power ($t_p=8/20\mu s$)	P_{PP}	500	Watts
Peak Pulse Current ($t_p=8/20\mu s$)	I_{PP}	28	A
Operating Temperature	T_J	-55 to + 125	°C
Storage Temperature	T_{STG}	-55 to +150	°C

Electrical Parameters (T=25°C)


Symbol	Parameter
I_{PP}	Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F




Electrical Characteristics

Parameter	Symbol	Conditions	Minimum	Typical	Maximum	Units
Reverse Stand-Off Voltage	V_{RWM}				5.0	V
Reverse Breakdown Voltage	V_{BR}	$I_T=1mA$	6.0		8.5	V
Reverse Leakage Current	I_R	$V_{RWM}=5V, T=25°C$			1.0	μA
Peak Pulse Current	I_{PP}	$t_p=8/20\mu s$			28	A
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$			9.0	V
Clamping Voltage	V_C	$I_{PP}=28A, t_p=8/20\mu s$			17	V
Junction Capacitance	C_j	$V_R=0V, f=1MHz$		180		pF


Typical Characteristics




Non-repetitive peak pulse power vs. Pulse time




Power derating vs. Ambient temperature




Clamping voltage vs. Peak pulse current



Capacitance vs. Reverse voltage




8/20μs waveform per IEC61000-4-5




Contact discharge current waveform per IEC61000-4-2

Outline Drawing – SOD-323



Part Numbering System



Device	Package	Shipping	MarKing	Parameter
ST5VFD322	SOD-323	3000/Tape&Reel	05 *	05 = Product Code * = Device Code