



Product Specification

XEL357x

4-Pin SOP Phototransistor Optocouplers

WEB | www.xinboleic.com



Descriptions

The XEL357x series contains an infrared emitting diode, optically coupled to a phototransistor detector. The devices in a 4-pin small outline SOP package.

Features

- AC Input Response
- Current Transfer Ratio in Selected Groups
 - XEL357: 50–600%
 - XEL357A: 80–160%
 - XEL357B: 130–260%
 - XEL357C: 200–400%
 - XEL357D: 300–600%
- Minimum BV_{CEO} of 70 V Guaranteed
- High isolation voltage between input and output ($V_{iso}=3750V$ rms)
- This Device is Pb–Free
- Adopting SOP-4 package



SOP-4

Applications

- Power Supply Regulators
- Digital Logic Inputs
- Microprocessor Inputs

Ordering Information

Product Model	Package Type	Marking	Packing	Packing Qty	CTR Value*
XEL357-TAG	SOP-4-2.54mm	357	Tape	3000Pcs/Reel	50-600%
XEL357A-TAG	SOP-4-2.54mm	357A	Tape	3000Pcs/Reel	80-160%
XEL357B-TAG	SOP-4-2.54mm	357B	Tape	3000Pcs/Reel	130-260%
XEL357C-TAG	SOP-4-2.54mm	357C	Tape	3000Pcs/Reel	200-400%
XEL357D-TAG	SOP-4-2.54mm	357D	Tape	3000Pcs/Reel	300-600%

*Notes: $I_F=5mA$, $V_{CE}=5V$, $T_A=25^{\circ}C$


Product Model

XEL357X-YG

Note

- X = CTR Rank(A, B, C, D or none)
- Y = Tape and reel option (TA, TB or none)
- G = Halogen free


Block Diagram



Pin Configurations

1. Anode
2. Cathode
3. Emitter
4. Collector

Naming Rule



- 1.XBLW LOGO
- 2.CTR Rank
- 3.Year Code, Example : 2023=23
- 4.Work Week Ranging from '01' to '53'
- 5.Internal Code

ABSOLUTE MAXIMUM RATINGS $T_A = 25^\circ\text{C}$ unless otherwise specified.

Symbol	Parameter	Value	Unit
--------	-----------	-------	------

TOTAL DEVICE

T_{STG}	Storage Temperature	-55 to +150	$^\circ\text{C}$
T_{OPR}	Operating Temperature	-55 to +110	
T_J	Junction Temperature	-55 to +125	
T_{SOL}	Lead Solder Temperature	260 for 10 s	
θ_{JC}	Junction-to-Case Thermal Resistance	210	$^\circ\text{C}/\text{W}$
P_{TOT}	Total Device Power Dissipation	200	mW

Symbol	Parameter	Value	Unit
--------	-----------	-------	------

EMITTER

I_F	Continuous Forward Current	50	mA
V_R	Reverse Voltage	6	V
P_D	Power Dissipation	70	mW
	Derate Above 100°C	1.7	mW/ $^\circ\text{C}$

DETECTOR

V_{CEO}	Collector-Emitter Voltage	70	V
V_{ECO}	Emitter-Collector Voltage	6	
I_C	Continuous Collector Current	50	mA
P_C	Collector Power Dissipation	150	mW
	Derate Above 90°C	2.9	mW/ $^\circ\text{C}$

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ELECTRICAL CHARACTERISTICS $T_A = 25^\circ\text{C}$ unless otherwise specified.

INDIVIDUAL COMPONENT CHARACTERISTICS

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

Emmitter

V_F	Forward Voltage	$I_F = 20\text{ mA}$	—	1.2	1.4	V
I_R	Reverse Current	$V_R = 4.0\text{ V}$			10	μA
C_t	Terminal Capacitance	$V = 0, f = 1\text{ kHz}$		30	250	pF

Detector

I_{CEO}	Collector Dark Current	$V_{CE} = 20\text{ V}, I_F = 0$	—		100	nA
BV_{CEO}	Collector-Emitter Breakdown Voltage	$I_C = 0.1\text{ mA}, I_F = 0$	70	—		V
BV_{ECO}	Emitter-Collector Breakdown Voltage	$I_E = 10\text{ }\mu\text{A}, I_F = 0$	6	—	—	

DC TRANSFER CHARACTERISTICS

Symbol	Parameter	Device	Test Conditions	Min	Typ	Max	Unit
CTR	Current Transfer Ratio (Note 1)	XEL357	$I_F = 5 \text{ mA}$, $V_{CE} = 5 \text{ V}$	50	–	600	%
		XEL357A		80		160	
		XEL357B		130	–	260	
		XEL357C		200	–	400	
		XEL357D		300		600	
$V_{CE(SAT)}$	Collector–Emitter Saturation Voltage	XEL357 Series	$I_F = 20 \text{ mA}$, $I_C = 1 \text{ mA}$	–	0.1	0.2	V

ELECTRICAL CHARACTERISTICS TA = 25°C unless otherwise specified. (continued)

AC TRANSFER CHARACTERISTICS

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
f_C	Cut–Off Frequency	$V_{CE} = 5 \text{ V}$, $I_C = 2 \text{ mA}$, $R_L = 100 \Omega$, -3 dB	15	80	–	kHz
t_r	Response Time (Rise)	$V_{CE} = 2 \text{ V}$, $I_C = 2 \text{ mA}$, $R_L = 100 \Omega$ (Note 2)	–	4	18	μs
t_f	Response Time (Fall)		–	3	18	

ISOLATION CHARACTERISTICS

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
V_{ISO}	Input–Output Isolation Voltage (Note 3)	$f = 60 \text{ Hz}$, $t = 1 \text{ min}$, $I_{I-O} \leq 2 \mu\text{A}$	5000			V_{ACRMS}
R_{ISO}	Isolation Resistance	$V_{I-O} = 500 \text{ V}_{DC}$	5×10^{10}	1×10^{11}	–	Ω
C_{ISO}	Isolation Capacitance	$V_{I-O} = 0$, $f = 1 \text{ MHz}$	–	0.6	1.0	pf

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Current Transfer Ratio (CTR) = $I_C / I_F \times 100\%$
2. For test circuit setup and waveforms, refer to page 6 to 8 .
3. For this test, Pins 1 and 2 are common, and Pins 3 and 4 are common.

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTICS CURVES

$T_A = 25^\circ\text{C}$ unless otherwise specified.




Figure 1 . Collector Power Dissipation vs. Ambient Temperature




Figure 2 . Collector-Emitter Saturation Voltage vs.




Figure 3 . Forward Current vs. Forward Voltage




Figure 4 . Current Transfer Ratio vs. Forward Current




Figure 5 . Collector Current vs. Collector-Emitter Voltage







Figure 6. Relative Current Transfer Ratio vs. Ambient Temperature




T_A , Ambient Temperature ($^{\circ}C$)
Figure 7 . Collector-Emitter Saturation Voltage vs. Ambient Temperature




T_A , Ambient Temperature ($^{\circ}C$)
Figure 8 . Led Power Dissipation vs. Ambient Temperature



R_L , Load Resistance ($k\Omega$)
Figure 9 . Response Time vs. Load Resistance




f , Frequency (kHz)
Figure 10. Frequency Response



T_A , Ambient Temperature ($^{\circ}C$)
Figure 11. Collector Dark Current vs. Ambient Temperature

REFLOW PROFILE




Time (s)
Figure 12.
Reflow Profile

REFLOW PROFILE



Profile Feature	Pb-Free Assembly Profile
Temperature Min. (T_{smin})	150 °C
Temperature Max. (T_{smax})	200 °C
Time (t_S) from (T_{smin} to T_{smax})	60–120 s
Ramp-up Rate (t_L to t_P)	3 °C/s max.
Liquidous Temperature (T_L)	217 °C
Time (t_L) Maintained Above (T_L)	60–150 s
Peak Body Package Temperature	260 °C +0 °C / -5 °C
Time (t_P) within 5 °C of 260 °C	30 s
Ramp-down Rate (T_P to T_L)	6 °C/s max.
Time 25°C to Peak Temperature	8 min max.

Tape & Reel Packing Specifications

Option TA



Option TB




ITEM	DIM(mm)
W	16±0.20
A ₀	4.4±0.10
B ₀	7.60±0.10
K ₀	2.40±0.10
P ₁	8.00±0.10
F	7.50±0.10
E	1.75±0.10
D ₀ /D ₁	1.50±0.10
P ₀	4.00±0.10
P ₂	2.00±0.10
T	0.30±0.03

Package Dimension

- SOP-4-2.54mm

SIZE SYMBOL	Dimensions In Millimeters	SIZE SYMBOL	Dimensions In Inches
	DIM(mm)		DIM(in)
A	MAX2.0	A	0.0787
L	5.2 ± 0.2	L	0.205 ± 0.00787
e	2.54 ± 0.02	e	0.1 ± 0.000787
b	0.4 ± 0.1	b	0.0157 ± 0.00394
c	0.2	c	0.0078
D	4.0 ± 0.2	D	0.0157 ± 0.00787
E	4.4 ± 0.05	E	0.173 ± 0.00197
E1	7.0 ± 0.3	E1	0.276 ± 0.0118



Statement:

- XBLW reserves the right to modify the product manual without prior notice! Before placing an order, customers need to confirm whether the obtained information is the latest version and verify the completeness of the relevant information.
- Any semiconductor product may malfunction under specified conditions. When using XBLW products for system design and overall manufacturing, the buyer is responsible for complying with safety standards and taking appropriate safety measures to avoid risks that may cause personal injury or property damage.
- XBLW products have not been licensed for life support, military, and aerospace applications, and therefore XBLW is not responsible for any consequences arising from the use of this product in these areas.
- If any or all XBLW products (including technical data, services) described or contained in this document are subject to any applicable local export control laws and regulations, they may not be exported without an export license from the relevant authorities in accordance with such laws.
- The specifications of any and all XBLW products described or contained in this document specify the performance, characteristics, and functionality of said products in their standalone state, but do not guarantee the performance, characteristics, and functionality of said products installed in Customer's products or equipment. In order to verify symptoms and conditions that cannot be evaluated in a standalone device, the Customer should ultimately evaluate and test the device installed in the Customer's product device.
- XBLW documentation is only allowed to be copied without any alteration of the content and with the relevant authorization. XBLW assumes no responsibility or liability for altered documents.
- XBLW is committed to becoming the preferred semiconductor brand for customers, and XBLW will strive to provide customers with better performance and better quality products.