




SMD PULSE TRANSFORMER


Meets IEEE 802.3ab Standards.
Designed For 1G BASE-T Applications, Surface Mount Type.
Operating Temperature Range: -40 °C to +85°C.
RoHS Compliant.

Part Number	Electrical Specifications @25°C						
	Turns Ratio (±5%)	OCL(uH Min) @100KHz, 0.1V With 8mA DC Bias	CWW(pF Max) @100KHz, 0.1V	DCR (Ω Max)	Insertion Loss (dB Max)	Return Loss (dB Min)	HI-POT (Vrms)
LT4532B-201MGN T6	1CT:1CT	200	45	4.5	-1.2@0.5-100MHz 0.2-0.002*f ^{1.4} @100-125MHz	-16@1-40MHz -10+20*Log(F/80) @40-100MHz	1500

MECHANICAL





SCHEMATICS



Unless otherwise specified all tolerances are: ±0.25 in mm

TAPING AND PACKING



Quantity (pcs):
2400 PCS PER REEL
10 REELS PER CARTON
24000 PCS PER CARTON