



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

- a.HOUSING:PP BLACK
b.SPRING:SPRING WIRE(Ni-PLATING)
c.TERMINAL:BRASS

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.DIELECTRIC VOLTAGE: 270V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-18650-B1AJ020-150

线长(MM)

电池盒

电池型号



SMT 180° TYPE

PLATING:

A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:

1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK



NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL	4	BRASS	Ni-Plating
2	SPRING	4	SPRING WIRE, Ø0.70MM	Ni-Plating
1	HOUSING	1	PP	BLACK

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2023-11-16
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2023-11-16
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2023-11-16
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW: ④ ③
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: 电池盒BH-18650-4J (26#线长150mm剥皮上锡3mm)	
				PART NO.: BH-18650-B1AJ020-150	
				DRAW NO.:WD-CP-0358	