


1. Quad Port T1/E1 with 8 Transformers, 1500 Vrms
2. Matched to leading transceiver ICs.
3. Crosstalk -65dB or Better
4. Operating temperature range: 0 °C to +70 °C
5. Reflow Condition: Maximum reflow temperature is 240 °C ~245 °C, time is 20 ~40 sec. (Refer to IPC/JEDEC J-STD 020C standard)




DIMENSIONS & SCHEMATICS



Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.25}$

Dimensions: Inches
mm


Note: 1. Dimension: inches/mm 2. Unless otherwise specified, tolerances are: $\pm 0.15\text{mm}$



TECHNICAL SPECIFICATIONS

OCL :	1.2mH Min.@ 100KHz 0.1V
Leakage Inductance:	0.7 μH Max @ 100KHz 0.1V
Cw/w:	35pF Max@ 100KHz 0.1V
DCR:	0.70 Ω Max.
Turns Ratio ($\pm 2\%$):	TX:1:2 RX:1:2
Primary Pins:	TX:1-2, 6-7, 11-12, 16-17 RX:3-4, 8-9, 13-14, 18-19

PACKING SPECIFICATION



1. units/reel: 175PCS
2. reel/carton: 4PCS
3. units/carton 700PCS

EXPORT CARTON: 367(L)x337(W)x235(H)