


Features ➤ Super Low Gate Charge ➤ Green Device Available ➤ Excellent CdvV/dt effect decline ➤ Advanced high cell density Trench technology ➤ 100% EAS Guaranteed	Bvdss	Rdson	ID
	-60V	46mΩ	-20A
	Application ➤ PWM applications ➤ Load Switch ➤ Power management		




Package



Marking and pin assignment



TO252-3L top view



Schematic diagram

Package Marking and Ordering Information

Device Marking	Device	Device Package	Quantity
20P06	20P06	TO252-3L	2500

Absolute Maximum Ratings (T_A=25°C unless otherwise specified noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V _{DS}	-60	V
Gate-Source Voltage	V _{GS}	±20	V
Continuous Drain Current, V _{GS} @-10V ¹	I _D @T _C =25°C	-20	A
	I _D @T _C =100°C	-12	A
Pulsed Drain Current ²	I _{DM}	-30	A
Single Pulse Avalanche Energy ³	EAS	18.5	mJ
Avalanche Current	I _{AS}	-13.1	A
Total Power Dissipation ⁴	P _D	2	W
Storage Temperature Range	T _{STG}	-55 ~ 150	°C
Operating Junction Temperature Range	T _J	-55 ~ 150	°C



Thermal Resistance Ratings

Parameter	Symbol	Typ.	Max.	Unit
Thermal Resistance from Junction to Ambient ¹	$R_{\theta JA}$	--	63	°C/W
Thermal Resistance from Junction to Case ¹	$R_{\theta JC}$	--	5	°C/W

Ordering Information

Ordering Number	Package	Pin Assignment			Packing
Halogen Free		G	D	S	
HL20P06	TO252-3L	1	2	3	Tape Reel

Electrical Characteristics ($T_J=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=-250\mu A$	-60	-	-	V
Drain-Source Leakage Current	I_{DSS}	$V_{DS}=-30V, V_{GS}=0V$	-	-	-1	μA
Gate-body Leakage current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu A$	-1.2	-1.7	-2.5	V
Drain-Source On-Resistance ²	$R_{DS(ON)}$	$V_{GS}=-10V, I_D=-10A$	-	47	57	m Ω
		$V_{GS}=-4.5V, I_D=-6A$	-	55	66	m Ω
Forward Transconductance	g_{fs}	$V_{DS}=-5V, I_D=-15A$	-	12	-	S
Input Capacitance	C_{iss}	$V_{DS}=-15V, V_{GS}=0V,$ $f=1\text{MHz}$	-	580	-	pF
Output Capacitance	C_{oss}		-	98	-	
Reverse Transfer Capacitance	C_{rss}		-	84	-	
Total Gate Charge	Q_g	$V_{GS}=-4.5V, I_D=-15A,$ $V_{DS}=-15V$	-	6	-	nC
Gate-Source Charge	Q_{gs}		-	3	-	
Gate-Drain Charge	Q_{gd}		-	1.75	-	
Turn-on Delay Time	$t_{d(on)}$	$V_{DD}=-15V, R_G=3.3\Omega,$ $I_D=-15A, V_{GS}=-10V$	-	2.5	-	nS
Rise Time	t_r		-	8.5	-	
Turn-Off Delay Time	$t_{d(off)}$		-	33.5	-	
Fall Time	t_f		-	6	-	
Continuous Source Current ^{1,5}	I_S	$V_G=V_D=0V, \text{Force Current}$	-	-	-20	A
Pulsed Source Current ^{2,5}	I_{SM}		-	-	-30	A
Diode Forward Voltage ²	V_{SD}	$V_{GS}=0V, I_S=-15A$	-	-	-1.2	V
Reverse Recovery Time	t_{rr}	$I_F=-15A, dI/dt=-100A/\mu s$	-	6	-	nC
Reverse Recovery Charge	Q_{rr}		-	1.5	-	

Notes:

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed, pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
3. The EAS data shows Max. rating. The test condition is $V_{DD}=-25V, V_{GS}=-10V, L=0.1mH, I_{AS}=-19A$
4. The power dissipation is limited by 150°C junction temperature.
5. The data is theoretically the same as I_D and I_{DM} , in real applications, should be limited by total power dissipation.

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 On-Resistance v.s Gate-Source




Fig.3 Forward Characteristics Of Reverse




Fig.4 Gate Charge Characteristics




Fig.5 Normalized $V_{GS(th)}$ vs. T_J




Fig.6 Normalized $R_{DS(on)}$ vs. T_J




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform






Fig.11 Unclamped Inductive Switching Waveform

Package Mechanical Data TO252-3L



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.10		2.50	0.083		0.098
A2	0		0.10	0		0.004
B	0.66		0.86	0.026		0.034
B2	5.18		5.48	0.202		0.216
C	0.40		0.60	0.016		0.024
C2	0.44		0.58	0.017		0.023
D	5.90		6.30	0.232		0.248
D1	5.30REF			0.209REF		
E	6.40		6.80	0.252		0.268
E1	4.63			0.182		
G	4.47		4.67	0.176		0.184
H	9.50		10.70	0.374		0.421
L	1.09		1.21	0.043		0.048
L2	1.35		1.65	0.053		0.065
V1		7°			7°	
V2	0°		6°	0°		6°



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
W	15.90	16.00	16.10	0.626	0.630	0.634
E	1.65	1.75	1.85	0.065	0.069	0.073
F	7.40	7.50	7.60	0.291	0.295	0.299
D0	1.40	1.50	1.60	0.055	0.059	0.063
D1	1.40	1.50	1.60	0.055	0.059	0.063
P0	3.90	4.00	4.10	0.154	0.157	0.161
P1	7.90	8.00	8.10	0.311	0.315	0.319
P2	1.90	2.00	2.10	0.075	0.079	0.083
A0	6.85	6.90	7.00	0.270	0.271	0.276
B0	10.45	10.50	10.60	0.411	0.413	0.417
K0	2.68	2.78	2.88	0.105	0.109	0.113
T	0.24		0.27	0.009		0.011
t1	0.10			0.004		
10P0	39.80	40.00	40.20	1.567	1.575	1.583



Important Notice and Disclaimer

HL Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

HL Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does HL Microelectronics assume any liability for application assistance or customer product design.

HL Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of HL Microelectronics.

HL Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of HL Microelectronics.