




Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.







Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Part No.	Code No.	Number of contact	Dimension of connector, PCB mounting pattern, stencil pattern and FFC/FPC								Dimension of drawing for packing					
			A	B	C	D	E	F	G	H	J	K	L	M	N	P
FH65-4S-0.5SH	————	4	3.8	1.5	2.57	3.18	2.8	3.83	2.5	2.87	4.0	7.5	16.0	—	21.4	17.4
FH65-6S-0.5SH	————	6	4.8	2.5	3.57	4.18	3.8	4.83	3.5	3.87	5.0	7.5	16.0	—	21.4	17.4
FH65-8S-0.5SH	CL580-4703-0-00	8	5.8	3.5	4.57	5.18	4.8	5.83	4.5	4.87	6.0	7.5	16.0	—	21.4	17.4
FH65-10S-0.5SH	CL580-4704-0-00	10	6.8	4.5	5.57	6.18	5.8	6.83	5.5	5.87	7.0	11.5	24.0	—	29.4	25.4
FH65-12S-0.5SH	CL580-4708-0-00	12	7.8	5.5	6.57	7.18	6.8	7.83	6.5	6.87	8.0	11.5	24.0	—	29.4	25.4
FH65-14S-0.5SH	————	14	8.8	6.5	7.57	8.18	7.8	8.83	7.5	7.87	9.0	11.5	24.0	—	29.4	25.4
FH65-15S-0.5SH	CL580-4701-0-00	15	9.3	7.0	8.07	8.68	8.3	9.33	8.0	8.37	9.5	11.5	24.0	—	29.4	25.4
FH65-16S-0.5SH	————	16	9.8	7.5	8.57	9.18	8.8	9.83	8.5	8.87	10.0	11.5	24.0	—	29.4	25.4
FH65-18S-0.5SH	————	18	10.8	8.5	9.57	10.18	9.8	10.83	9.5	9.87	11.0	11.5	24.0	—	29.4	25.4
FH65-20S-0.5SH	————	20	11.8	9.5	10.57	11.18	10.8	11.83	10.5	10.87	12.0	11.5	24.0	—	29.4	25.4
FH65-22S-0.5SH	————	22	12.8	10.5	11.57	12.18	11.8	12.83	11.5	11.87	13.0	11.5	24.0	—	29.4	25.4
FH65-24S-0.5SH	————	24	13.8	11.5	12.57	13.18	12.8	13.83	12.5	12.87	14.0	11.5	24.0	—	29.4	25.4
FH65-26S-0.5SH	————	26	14.8	12.5	13.57	14.18	13.8	14.83	13.5	13.87	15.0	14.2	32.0	28.4	37.4	33.4
FH65-28S-0.5SH	————	28	15.8	13.5	14.57	15.18	14.8	15.83	14.5	14.87	16.0	14.2	32.0	28.4	37.4	33.4
FH65-30S-0.5SH	————	30	16.8	14.5	15.57	16.18	15.8	16.83	15.5	15.87	17.0	14.2	32.0	28.4	37.4	33.4
FH65-32S-0.5SH	————	32	17.8	15.5	16.57	17.18	16.8	17.83	16.5	16.87	18.0	14.2	32.0	28.4	37.4	33.4
FH65-34S-0.5SH	CL580-4700-0-00	34	18.8	16.5	17.57	18.18	17.8	18.83	17.5	17.87	19.0	20.2	44.0	40.4	49.4	45.4
FH65-36S-0.5SH	————	36	19.8	17.5	18.57	19.18	18.8	19.83	18.5	18.87	20.0	20.2	44.0	40.4	49.4	45.4
FH65-40S-0.5SH	————	40	21.8	19.5	20.57	21.18	20.8	21.83	20.5	20.87	22.0	20.2	44.0	40.4	49.4	45.4
FH65-45S-0.5SH	————	45	24.3	22.0	23.07	23.68	23.3	24.33	23.0	23.37	24.5	20.2	44.0	40.4	49.4	45.4
FH65-50S-0.5SH	————	50	26.8	24.5	25.57	26.18	25.8	26.83	25.5	25.87	27.0	20.2	44.0	40.4	49.4	45.4
FH65-60S-0.5SH	————	60	31.8	29.5	30.57	31.18	30.8	31.83	30.5	30.87	32.0	26.2	56.0	52.4	61.4	57.4
FH65-64S-0.5SH	————	64	33.8	31.5	32.57	33.18	32.8	33.83	32.5	32.87	34.0	26.2	56.0	52.4	61.4	57.4
FH65-68S-0.5SH	————	68	35.8	33.5	34.57	35.18	34.8	35.83	34.5	34.87	36.0	26.2	56.0	52.4	61.4	57.4


※Contact positions without code numbers are currently under planning.  
Please contact Hirose for detailed information about product variation.

<b>HRS</b>	DRAWING NO.	EDC-371661-00-00	
	PART NO.	FH65- * * S-0. 5SH	
	CODE NO.	CL580	<div><div>3</div><div>4</div><div>9</div></div>


Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

This connector features small and thin, requiring delicate and careful handling.  
To prevent connector/FPC/FFC breakage and contact failure (mating failure, FPC/FFC pattern breakage, etc),  
read through the instructions shown below and handle the connector properly.  
Each values indicating here are for reference and may differ from standard value.

#### [Connector Part Nomenclature]



(Top view)



(Front view)

#### [Operation and Precautions]

##### 1. Initial condition

The connector is delivered with the actuator closed.

##### [Caution]

-Do not insert FPC/FFC or operate actuator before mounting.

##### 2. How to unlock (Before inserting FPC/FFC)

The actuator rotates on its axis as shown below.

Slowly flip up the actuator to release the lock. (example 1)

##### [Caution]

-Open the actuator by carefully lifting it at the center. (example 2)

-Do not lift the actuator at one end only. (example 3)

-The actuator must be operated by hand only.


Do not insert any tools or fingernails into the connector. (example 4,5)

-The actuator rotates 120 degrees max.


Do not try to rotate the actuator further towards the opening direction or apply any extra force to the actuator while it is fully open. (example 6)

-Do not apply extra force to the connector while rotating the actuator as the illustration shows. (example 7)


-Do not attempt to dislodge the actuator. (example 8,9)



(Contact view)




Example 2




Open the actuator at the center

- Correct operation -




Example 3



Do not operate the actuator at one end only.


- Incorrect operation -

Example 4




- Incorrect operation -

Example 5




- Incorrect operation -

Example 6



- Incorrect operation -

Example 7




- Incorrect operation -




Failure from the actuator pushed in

Example 8



- Incorrect operation -

Example 9



- Incorrect operation -

△<INSTRUCTION MANUAL (1)>

HRS

DRAWING NO.	EDC-371661-00-00
PART NO.	FH65-**S-0.5SH
CODE NO.	CL580

3/5/9

Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

### 3. How to insert FPC/FFC


This connector has contact point on the bottom, insert the FPC/FFC with the exposed conductors face down.  
This connector has metal fittings, insert the FPC/FFC at about 20 degree angle to the PCB mounting surface. (example 10)

#### [Caution]


- Do not insert the FPC/FFC with the conductor surface face up.
- Insert the FPC/FFC properly to the very end.
- Do not insert the FPC/FFC at an angle. (example 11)
- Insert the FPC/FFC with the actuator opened. (example 12)
- Do not twist the FPC/FFC to up and down, right and left or an angle. (example 13)

Example 10


Metal fitting for positioning FPC/FFC




Example 11



Example 12



Example 13




### 4. FPC/FFC insertion check

Metal fittings guide the FPC/FFC tabs to the correct position.  
Make sure that the FPC/FFC tabs are located in correct position as shown in the figure below after FPC/FFC insertion. (example 14)


#### [Caution]

- Do not insert the FPC/FFC at an angle and/or stop it before insertion is completed. (example 15, 16)





Example 14



Example 15



Example 16



△ <INSTRUCTION MANUAL (2)>

HRS

DRAWING NO.	EDC-371661-00-00
PART NO.	FH65-**S-0.5SH
CODE NO.	CL580

3/6/9

Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

## 5. How to lock


The actuator rotates on its axis as shown below.

Apply load to rotate the actuator after inserting the FPC/FFC. (example 17)

[Caution]


- Close the actuator by carefully operating it at the center. (example 18)
- Do not operate the actuator at one end only. (example 19)
- The actuator must be operated by hand only. Do not insert any tools or fingernails into the connector.
- Do not try to rotate the actuator further towards the opening direction while it is fully open.
- Do not attempt to dislodge the actuator.
- After the actuator is closed, the actuator should be parallel to the PCB mounting surface.

Example 17




- Correct operation -

Example 18



- Correct operation -

Example 19



- Incorrect operation -

## 6. Mating confirmation of the FPC/FFC


Visually confirm the position of the FPC/FFC TAB after closing the actuator. (example 20)

[Caution]

- Do not insert the FPC/FFC halfway and/or at an angle before the insertion is completed. (example 21, 22)

Example 20


FPC/FFC TAB will fit into the space between metal fitting and housing if it is inserted correctly.



- Correct operation -

Example 21


FPC/FFC TAB will not fit into the space between metal fitting and housing if it is inserted incorrectly. (halfway insertion)



- Incorrect operation -

Example 22

FPC/FFC TAB will not fit into the space between metal fitting and housing if it is inserted incorrectly. (inserted with an angle)



- Incorrect operation -


## 7. How to unlock

Slowly flip up the actuator to release the lock. (example 23)

[Caution]


- Open the actuator by carefully lifting it at the center. (example 24)
- Do not lift the actuator at one end only. (example 25)
- The actuator must be operated by hand only. Do not insert any tools or fingernails into the connector.
- The actuator rotates 120 degrees max. Do not try to rotate the actuator further towards the opening direction or apply any extra force to the actuator while it is fully open. (example 26)
- Do not attempt to dislodge the actuator. (example 27)

Example 23




- Correct operation -

Example 24




- Correct operation -

Example 25




- Incorrect operation -

Example 26



- Incorrect operation -

Example 27



- Incorrect operation -

△<INSTRUCTION MANUAL(3)>

HRS

DRAWING NO.	EDC-371661-00-00
PART NO.	FH65-**S-0.5SH
CODE NO.	CL580

3/7/9


## 8. How to remove FPC/FFC

The space between metal fitting and housing on both side of the connector is for guiding the FPC/FFC into the right position while insertion.  
After rotating the actuator to the fully open position carefully withdraw the FPC/FFC at about 20 degree angle to the PCB mounting surface. (example 28)

### [Caution]

- For FPC/FFC removal, do not pull out the FPC/FFC horizontally.
- Do not withdraw the FPC/FFC at extreme(inclined towards vertical) angle.
- Do not attempt to pull the FPC/FFC without unlocking the actuator. (example 30)


Example 28



- Correct operation -


Example 29

Deformation of the contact upper arm




- Incorrect operation -

Example 30




- Incorrect operation -


Example 31




Example 33



Example 32



Example 34



## [Instructions for mounting on the PCB]

Follow the instructions shown below when mounting on the PCB.

### [Caution]

- Refer to recommended layouts on the page 1 for PCB and stencil pattern.
- Using neither narrower land pattern or wider stencil pattern than recommendation may end up with excessive amount of solder/flux climbing on contact. Please inspect the size of solder fillet and flux climbing height of the mounted connector while using different land/stencil pattern from our recommendation.
- Larger pattern than the recommended stencil dimension could cause solder wicking and/or flux penetration.
- Clearance between the mounting surface of the connector contact leads and the bottom of the housing is very small. Solder resist/silk screening applied underneath the connector may interfere with the connector. This may lead to soldering defect/insufficient fillet formation. Please verify your solder resist/silk screening design carefully before implementing the design.
- Apply reflow temperature profile within the specified conditions. For specific applications, the recommended temperature may vary depending on type/volume/thickness of solder paste and size/thickness of PCB. Please consult with your solder paste and equipment manufacturer for specific recommendations.
- Please try to minimize the warpage of the PCB. Soldering failure could still occur due to the PCB warpage even if the coplanarity of the connector is under 0.1mm.
- If the connector is mounting on FPC/FFC, please make sure to put a stiffener on the backside of the FPC/FFC. Recommended stiffener: Glass epoxy material with thickness of 0.3mm MIN.
- Do not apply 1 N or greater external force on the connector when unreeling or handling the connector before mounting. Excessive mechanical stress may damage the connector before mounting.

## [Precautions for component layout]

While the FPC/FFC is under tension due to the connecting configuration, extra stress may be applied to the connector.  
As a result, conduction failure may occur due to the extra stress.  
In order to prevent such kind of conduction failure, please read through the following parts before making circuits/mechanism design.

### [Caution]

- Avoid applying forces to/pulling the FPC/FFC along/perpendicular to the direction of FPC/FFC insertion. (example 31)
- Avoid pushing/pulling the FPC/FFC upwards/downwards.
- If the FPC/FFC has to be curled/bended in your cabling design, please keep enough degree of freedom in your design to keep the FPC/FFC tension free. In this regard, the stiffener is parallel to the PCB. (example 32)
- If the FPC/FFC has to be curled/bended in your cabling design, do not curl/bend the FPC/FFC area near the connector. This may lead to conduction failure or FPC/FFC breakage. (example 33)
- It is recommended to keep the FPC/FFC fixed to avoid applying stress through the FPC/FFC to the connector.
- Do not mount other components underneath the FPC/FFC stiffener which may interfere with the connection. (example 34)
- Follow the recommended FPC/FFC design. Please consult with the FPC/FFC manufacturer about FPC/FFC bending performance and wire breakage strength while making design.
- Keep sufficient operating space for FPC/FFC insertion during layout design in order to avoid incorrect FPC/FFC insertion. Please keep enough FPC/FFC length and component layout space for assembly during design process. FPC/FFC with too short length may make the assembly difficult.
- Keep enough space for the rotation of the actuator during PCB and component layout design.
- Please consult with our sales representative if you are using FPC/FFC with different configuration from our recommendation.

△<INSTRUCTION MANUAL (4)>

HRS

DRAWING NO.	EDC-371661-00-00
PART NO.	FH65-**S-0.5SH
CODE NO.	CL580

3/8/9



Jun.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


# [Instructions for PCB handling after mounting the connector]

Follow the instructions shown below when mounting on the PCB.


## [Caution]

- Splitting a large PCB into several pieces
  - Installing mounting screw on PCB
- During the assembly processes described above, care should be taken so as not to give any stresses of deflection or twisting to the PCB. Stresses applied on PCB may damage the connector as well.
- The warpage of a 100 mm wide PCB should remain within 1 mm. (example 35)
- The warpage of PCB may apply excessive stress on the connector and damage the connector.
- Please perform conduction check with caution. Conductivity probe may damage the connector contacts. (example 36)
  - Attachment of foreign particles with the connector contact may lead to conduction failure. In this particular case, the conduction failure may be fixed by re-inserting the FPC/FFC.

Example 35



Example 36



# [Instructions on manual soldering]

Follow the instructions shown below when soldering the connector manually during repair work, etc.

## [Caution]


- Do not perform manual soldering with the FPC/FFC inserted into the connector.
  - Do not heat the connector excessively. Be very careful not to let the soldering iron touch any parts other than connector leads. Otherwise, the connector may be deformed or melt.
  - Do not supply excessive solder (or flux).
- If excessive solder (or flux) is supplied on the contact lead, solder or flux may adhere to the contact point or rotating parts of the actuator, resulting in conduction or rotation failure of the actuator. Supplying excessive solder to the metal fittings may hinder actuator rotation, resulting in breakage of the connector.

## [Recommended reflow temperature profile]

The temperatures mentioned above refer to the PCB surface temperature near the connector contact leads. For specific applications the recommendation temperature may vary depending on type/volume/thickness of solder paste and size/thickness of PCB. Please consult with your solder paste and equipment manufacturer for specific recommendations.

Reflow method: IR reflow

Number of reflow cycles: 2 cycles MAX.



△ < Recommended reflow temperature profile >

**HRS**

DRAWING NO.	EDC-371661-00-00
PART NO.	FH65- * * S-0.5SH
CODE NO.	CL580

3/9