





May.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



RECOMMENDED PCB PATTERN

NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM


NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
60~120s

2. TEMPERATURE FOR SOLDERING IRON
: 280~300°C WITHIN 2s

3. CO-PLANARITY SHALL BE 0.1mm MAX.

4. RECOMMENDED PCB THICKNESS IS 1.6mm.

5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



2	BRASS	TIN PLATED T=0.64	4	BRASS	TIN PLATED T=0.4
1	PPS	BLACK	3	BRASS	TIN PLATED T=0.64
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
	HIROSE ELECTRIC CO., LTD.	APPROVED : AR. SHIRAI	16. 07. 27	DRAWING NO.	EDC-360215-00-00
		CHECKED : HS. OZAWA	16. 07. 27	PART NO.	GT25H2-40DP-2.2V
		DESIGNED : TK. SHISHIKURA	16. 07. 27	CODE NO.	CL775-0085-3-00
		DRAWN : TK. SHISHIKURA	16. 07. 27		