



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

COMMON MODE CHOKE

PART NO:

MWBA1206D系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/5	

CUSTOMER APPROVE

DDY® 德立电子&铭易轩

东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD.

地址: 广东省东莞市大朗镇景泰路20号VV大厦

工厂地址: 广东省惠州市博罗县洲际工业园梅园三路

电话: 13640935893 , 15970768093

网址: <http://www.dgmingyixuan.com>



MODIFY RECORD 变更履历


[illegible]



SPECIFICATION FOR APPROVAL


CUSTOMER:		REV. NO.	A0
PART NO:	MWBA1206D系列	PAGE NO:	2/8
CUST. PART NO:		DATE:	2025/5/5

1. SHAPE & DIMENSION (UNIT:mm)



A	B	C	E	D1	D2	F	G	I	H
3.2 ±0.2	1.6 ±0.2	1.9 ±0.1	0.2 Typ.	0.70 Typ.	0.60 Typ.	3.50 Typ.	1.90 Typ.	0.40 Typ.	1.70 Typ.

2. SCHEMATIC



3. PART NUMBERING SYSTEM

MWBA	1206	D	900	P	T	-	HF
①	②	③	④	⑤	⑥		⑦

- ① PRODUCT SYMBOL (产品代号)
- ② DIMENSIONS (规格尺寸)
- ③ TYPE (类型)
- ④ IMPEDANCE (阻抗)
- ⑤ TOLERANCE (公差) : P±25%; N±30%
- ⑥ PACKAGING (包装方式) : T-编带盘装; B-散装
- ⑦ E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV. NO.	A0
PART NO:	MWBA1206D系列	PAGE NO:	3/8
CUST. PART NO:		DATE:	2025/5/5

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	Z	Freq	Rdc	Irms	Rated Voltage	Insulation Resistance
		(Ω)	(MHz)	(Ω)Max.	(mA)Max.	Volts	(MΩ) Min.
1	MWBA1206D900PT-HF	90	100	0.30	370	50	10
2	MWBA1206D121PT-HF	120	100	0.30	350	50	10
3	MWBA1206D161PT-HF	160	100	0.40	340	50	10
4	MWBA1206D221PT-HF	220	100	0.45	300	50	10
5	MWBA1206D261PT-HF	260	100	0.50	310	50	10
6	MWBA1206D361PT-HF	360	100	0.60	300	50	10
7	MWBA1206D601PT-HF	600	100	0.80	260	50	10
8	MWBA1206D801PT-HF	800	100	0.90	240	50	10
9	MWBA1206D102PT-HF	1000	100	1.00	230	50	10
10	MWBA1206D142PT-HF	1400	100	1.00	220	50	10
11	MWBA1206D202PT-HF	2000	100	1.20	200	50	10
12	MWBA1206D222PT-HF	2200	100	1.20	200	50	10

Test remarks

- (1). All test data is referenced to 25 °C ambient.
- (2). Irms: Rating DC current: Temperature rise(ΔT) is 40°C approximately at Irms.

5. GENERAL SPECIFICATION

- (1). Operating temp.: -40°C ~ +125°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.


注意：
此物料不涉及汽车或相关产品方面的应用，否则，由此引起的一切品质和责任问题，我司将概不承担。

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平

CUSTOMER:		REV. NO.	A0
PART NO:	MWBA1206D系列	PAGE NO:	4/8
CUST. PART NO:		DATE:	2025/5/5

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max.)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering



Note:

Use a 20 watt soldering iron with tip diameter of 1.0mm

Limit soldering time to 3 sec.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平




SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWBA1206D系列	PAGE NO:	5/8
CUST. PART NO:		DATE:	2025/5/5

7. PACKAGE SPECIFICATION


TAPING DRAWINGS



REEL DIMENSIONS(UNIT:mm)

	A	B	C	N	G
CF-8	178±2.0	22±2.0	13.0±1.0	60±1.0	8


LEADER AND BLANK PORTION



(3). Packaging Quantity

Type	1206
Quantity	2000

PEELLING OFF FORCE:0.05 to 0.7N in the direction show below.



APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平




SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWBA1206D系列	PAGE NO:	6/8
CUST. PART NO:		DATE:	2025/5/5

8.Package Specifications

Inside Box And Outside Carton



卷轴数量	内盒包装数量	外箱包装数量
每卷:2000 PCS	每盒四盘，共8000 PCS	小箱6盒，共48000 PCS
		中箱8盒，共64000 PCS
		大箱10盒，共80000 PCS
	内盒包装尺寸	外箱包装尺寸
	20.3*19.3*5.5cm	小箱，40.6*23*19.7cm
		中箱，41*22*26cm
		大箱，41*22*33cm


APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWBA1206D系列	PAGE NO:	7/8
CUST. PART NO:		DATE:	2025/5/5

9. ELECTRICAL CHARACTERISTIC CURVE









APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWBA1206D系列	PAGE NO:	8/8
CUST. PART NO:		DATE:	2025/5/5

9. ELECTRICAL CHARACTERISTIC CURVE



APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平