







NOTE1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.

2. () IS REFERENCE DIMENSION.

3. MATING DF59-3P-2C, DF59-3P-2SP ARE APPLIED.

4. REFER TO THE DF59 SERIES MATING/UNMATING OPERATION INSTRUCTION MANUAL(ETAD-H0496) FOR THE OPERATING OF THE PRODUCT.

5. UL(FILE NO. E52653).
C-UL(FILE NO. E52653) APPROVED PRODUCT.



2	PHOSPHOR BRONZE	CONTACT AREA : GOLD PLATING 0.2μm MIN LEAD AREA : TIN PLATING 1μm MIN UNDER PLATING : NICKEL PLATING 0.5μm MIN	6	PS	REEL , BLACK
1	LCP	UL94V-0,BEIGE	5	POLYESTER	CLEAR(COVER TAPE)
			4	PS	CLEAR(EMBOSSED CARRIER TAPE)
			3	PHOSPHOR BRONZE	SURFACE : TIN PLATING 1μm MIN UNDER PLATING : NICKEL PLATING 0.5μm MIN
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5 : 1	COUNT 5	DESCRIPTION OF REVISIONS DIS-H-006828	DESIGNED MI. SAKIMURA
			CHECKED HK. UMEHARA		
			DATE 12. 04. 20		
			DRAWING NO. EDC3-330589-01		
			PART NO. DF59-3S-2V(51)		
			CODE NO. CL667-0002-3-51		
			1/2		

HRS HIROSE ELECTRIC CO., LTD.

APPROVED : KI. AKIYAMA 10. 09. 28
CHECKED : OM. MIYAMOTO 10. 09. 27
DESIGNED : KT. ISHII 10. 09. 27
DRAWN : KT. ISHII 10. 09. 27

DRAWING NO. EDC3-330589-01
PART NO. DF59-3S-2V(51)
CODE NO. CL667-0002-3-51

