

N-Channel Enhancement Mode Power MOSFET

Description


The GT020N10Q uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge. It can be used in a wide variety of applications.

General Features


- V_{DS} 100V
- I_D (at $V_{GS} = 10V$) 250A
- $R_{DS(ON)}$ (at $V_{GS} = 10V$) < 2.5m Ω
- 100% Avalanche Tested
- RoHS Compliant

Application

- Power switch
- DC/DC converters



Schematic diagram



TO-247

Ordering Information

Device	Package	Marking	Packaging
GT020N10Q	TO-247	GT020N10	30pcs/Tube

Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	100	V
Continuous Drain Current	I_D	250	A
		158	
Pulsed Drain Current (note1)	I_{DM}	1000	A
Gate-Source Voltage	V_{GS}	± 20	V
Power Dissipation	P_D	280	W
Single pulse avalanche energy (note2)	E_{AS}	812	mJ
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 To 150	$^\circ\text{C}$

Thermal Resistance

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Ambient	R_{thJA}	40	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Case	R_{thJC}	0.45	$^\circ\text{C/W}$

Specifications $T_J = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Parameters						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = 250μA	100	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 100V, V _{GS} = 0V	--	--	1	μA
Gate-Source Leakage	I _{GSS}	V _{GS} = ±20V	--	--	±100	nA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	2.3	2.8	3.7	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 80A	--	2.1	2.5	mΩ
Forward Transconductance	g _{FS}	V _{GS} = 5V, I _D = 80A	--	94	--	S
Dynamic Parameters						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = 50V, f = 0.8MHz	--	10600	--	pF
Output Capacitance	C _{oss}		--	1370	--	
Reverse Transfer Capacitance	C _{rss}		--	370	--	
Total Gate Charge	Q _g	V _{DD} = 50V, I _D = 80A, V _{GS} = 10V	--	160	--	nC
Gate-Source Charge	Q _{gs}		--	53	--	
Gate-Drain Charge	Q _{gd}		--	60	--	
Turn-on Delay Time	t _{d(on)}	V _{DD} = 50V, I _D = 80A, R _G = 6Ω	--	57	--	ns
Turn-on Rise Time	t _r		--	124	--	
Turn-off Delay Time	t _{d(off)}		--	116	--	
Turn-off Fall Time	t _f		--	47	--	
Drain-Source Body Diode Characteristics						
Continuous Body Diode Current	I _S	T _C = 25°C	--	--	250	A
Body Diode Voltage	V _{SD}	T _J = 25°C, I _{SD} = 80A, V _{GS} = 0V	--	--	1.2	V
Reverse Recovery Charge	Q _{rr}	I _F = 80A, V _{GS} = 0V di/dt=100A/us	--	139	--	nC
Reverse Recovery Time	T _{rr}		--	64	--	ns

Notes

1. Repetitive Rating: Pulse width limited by maximum junction temperature
2. EAS condition : $T_J = 25^\circ\text{C}$, $V_{DD} = 50V$, $V_{GS} = 10V$, $L = 0.5mH$, $R_g = 25\Omega$


The table shows the minimum avalanche energy, which is 2256mJ when the device is tested until failure

3. Identical low side and high side switch with identical R_G



Gate Charge Test Circuit



Switch Time Test Circuit



EAS Test Circuit



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Drain Source On Resistance




Figure 4. Gate Charge




Figure 5. Capacitance





Figure 6. Source-Drain Diode Forward



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Drain-Source On-Resistance




Figure 8. Safe Operation Area




Figure 9. Maximum Continuous Drain Current vs Case Temperature










Figure 10. Normalized Maximum Transient Thermal Impedance



TO-247 Package Information



VIEW A-A



SECTION C-C, D-D, E-E

SYMBOLS	DIMENSIONS			
	mm		inch	
	MIN.	MAX.	MIN.	MAX.
A	4.85	5.15	0.191	0.203
A1	2.25	2.55	0.088	0.100
A2	1.85	2.15	0.073	0.085
B	1.04	1.33	0.041	0.052
B1	1.90	2.35	0.075	0.093
B2	1.90	2.15	0.075	0.085
B3	2.90	3.35	0.114	0.132
B4	2.90	3.15	0.114	0.124
c	0.55	0.68	0.022	0.027
D	20.8	21.10	0.819	0.831
D1	16.25	17.65	0.640	0.695
D2	0.95	1.35	0.037	0.053
E	15.70	16.10	0.618	0.634
E1	13.50	14.20	0.531	0.559
E2	3.80	5.00	0.150	0.197
E3	1.00	2.6	0.039	0.102
e	5.46BSC		0.215BSC	
L	19.80	20.3	0.779	0.799
L1	4.00	4.50	0.157	0.177
phi P	3.50	3.70	0.138	0.145
phi P1	—	7.19	—	0.291
Q	5.40	6.00	0.212	0.236
S	6.2BSC		0.244BSC	