



承認書

SPECIFICATION FOR APPROVAL

CUSTOMER:

DESCRIPTION:

WIRE WOUND CHIP INDUCTOR

PART NO:

MWI1812UC系列

CUST. PART NO:

REV. NO.

A0

DRAWING		
PREPARED	CHECKED	APPROVED
邹声平	卢嘉良	曾凡强
DATE:	2025/5/5	

CUSTOMER APPROVE

 德立电子&铭易轩

东莞市铭易轩电子科技有限公司

DongGuan Ming Yixuan Electronic Technology Co., LTD.

地址: 广东省东莞市大朗镇景泰路20号VV大厦

工厂地址: 广东省惠州市博罗县洲际工业园梅园三路

电话: 13640935893 , 15970768093

网址: <http://www.dgmingyixuan.com>



[illegible]



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV. NO.	A0
PART NO:	MWI1812UC系列	PAGE NO:	2/7
CUST. PART NO:		DATE:	2025/5/5


1. SHAPE & DIMENSION (UNIT:mm)



Recommended patterns

L	W	T	E	F	D
4.95 Max.	3.85 Max.	3.43 Max.	1.14 Typ.	3.05 Typ.	3.0 Typ.

2. SCHEMATIC



3. PART NUMBERING SYSTEM

MWI	1812	UC	R10	J	S	T	-	HF
1	2	3	4	5	6	7		8

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 INDUCTANCE (电感量)
- 5 TOLERANCE (公差) : G $\pm$ 2%; J $\pm$ 5%; K $\pm$ 10%; M $\pm$ 20%
- 6 TERMINAL (端电极材料): G-金端头; S-锡端头;
- 7 PACKAGING (包装方式): T-编带盘装; B-散装
- 8 E.P. (环保): LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV. NO.	A0
PART NO:	MWI1812UC系列	PAGE NO:	3/7
CUST. PART NO:		DATE:	2025/5/5

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	Inductance	Test Freq	Q	SRF	Rdc	Irms	Tolerance
		(μH)	(MHz)	Min.	(MHz)Min.	(Ω) Max.	(mA)Max.	
1	MWI1812UCR10□ST-HF	0.10	7.9	60@50MHZ	400	0.60	480	J,K,M
2	MWI1812UCR12□ST-HF	0.12	25	50@25MHZ	900	0.10	480	J,K,M
3	MWI1812UCR15□ST-HF	0.15	25	50@25MHZ	700	0.12	480	J,K,M
4	MWI1812UCR18□ST-HF	0.18	25	50@25MHZ	700	0.13	480	J,K,M
5	MWI1812UCR22□ST-HF	0.22	25	50@25MHZ	500	0.14	480	J,K,M
6	MWI1812UCR27□ST-HF	0.27	25	50@25MHZ	500	0.15	480	J,K,M
7	MWI1812UCR33□ST-HF	0.33	7.9	60@50MHZ	400	0.70	480	J,K,M
8	MWI1812UCR39□ST-HF	0.39	7.9	60@50MHZ	400	0.80	480	J,K,M
9	MWI1812UCR75□ST-HF	0.75	7.9	60@50MHZ	350	0.65	750	J,K,M
10	MWI1812UC1R0□ST-HF	1.00	7.9	60@50MHZ	250	1.20	480	J,K,M
11	MWI1812UC1R5□ST-HF	1.50	7.9	60@50MHZ	210	1.60	430	J,K,M
12	MWI1812UC2R2□ST-HF	2.20	7.9	35@50MHZ	150	2.20	340	J,K,M
13	MWI1812UC2R7□ST-HF	2.70	7.9	55@50MHZ	150	3.20	300	J,K,M
14	MWI1812UC3R3□ST-HF	3.30	7.9	55@50MHZ	130	3.80	270	J,K,M
15	MWI1812UC3R9□ST-HF	3.90	7.9	55@50MHZ	120	5.00	240	J,K,M
16	MWI1812UC4R7□ST-HF	4.70	7.9	25@50MHZ	90	5.40	230	J,K,M
17	MWI1812UC5R6□ST-HF	5.60	7.9	45@50MHZ	90	5.70	220	J,K,M
18	MWI1812UC6R8□ST-HF	6.80	7.9	30@50MHZ	80	6.60	210	J,K,M
19	MWI1812UC8R2□ST-HF	8.20	7.9	20@50MHZ	70	7.00	200	J,K,M
20	MWI1812UC100□ST-HF	10.00	7.9	15@50MHZ	50	7.70	190	J,K,M
21	MWI1812UC120□ST-HF	12.00	2.5	30@10MHZ	50	8.70	180	J,K,M
22	MWI1812UC150□ST-HF	15.00	2.5	30@10MHZ	30	9.60	170	J,K,M
23	MWI1812UC180□ST-HF	18.00	2.5	25@10MHZ	30	10.50	160	J,K,M
24	MWI1812UC220□ST-HF	22.00	2.5	25@10MHZ	20	11.50	155	J,K,M

□:表示产品公差

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平



SPECIFICATION FOR APPROVAL

CUSTOMER:		REV. NO.	A0
PART NO:	MWI1812UC系列	PAGE NO:	4/7
CUST. PART NO:		DATE:	2025/5/5

4. ELECTRICAL CHARACTERISTICS

No.	Part Number	Inductance	Test Freq	Q	SRF	Rdc	Irms	Tolerance
		(μH)	(MHz)	Min.	(MHz)Min.	(Ω) Max.	(mA)Max.	
25	MWI1812UC270□ST-HF	27.00	2.5	25@10MHZ	20	12.50	150	J,K,M
26	MWI1812UC330□ST-HF	33.00	2.5	10@10MHZ	10	13.50	145	J,K,M

□:表示产品公差

Test remarks

- (1). All test data is referenced to 25 °C ambient.
- (2). Irms: DC current that causes the temperature rise ($\Delta T \leq 40^{\circ}\text{C}$) from 25°C ambient.

5. GENERAL SPECIFICATION

- (1). Operating temp.: -40°C ~ +125°C (Including self-generated heat).
- (2). Storage temp.: -10°C ~ +40°C R.H.:60% Max.
- (3). Moisture sensitivity level (MSL) 1
- (4). Recommended products should be used within 12 months from the date of delivery
- (5). The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平




SPECIFICATION FOR APPROVAL

CUSTOMER:		REV. NO.	A0
PART NO:	MWII812UC系列	PAGE NO:	5/7
CUST. PART NO:		DATE:	2025/5/5

6. SOLDERING CONDITIONS

Figure 1. Re-flow Soldering (Lead Free)



Note:


Preheat circuit and products to 150°C

260°C tip temperature (Max)

Reflow times: no more than 2 times

Solder paste thickness: the best 0.08mm is ,but max is 0.1mm

Figure 2. Hand Soldering



Note:

Use a 20 watt soldering iron with tip diameter of 1.0mm

Limit soldering time to 3 sec.

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平





SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWI1812UC系列	PAGE NO:	6/7
CUST. PART NO:		DATE:	2025/5/5

7. PACKAGING(unit: mm)

Type	1812
Quantity	500


TAPING DRAWINGS




REEL DIMENSIONS(UNIT:mm)

	A	B	C	N	G
CF-12	178±2.0	22±2.0	12.5±1.0	57±1.0	12

LEADER AND BLANK PORTION



PEELLING OFF FORCE:0.05 to 0.7N in the direction show below.



APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平






SPECIFICATION FOR APPROVAL

CUSTOMER:		REV NO:	A0
PART NO:	MWII812UC系列	PAGE NO:	7/7
CUST. PART NO:		DATE:	2025/5/5

8. Package Specifications

■Inside Box And Outside Carton



卷轴数量	→	内盒包装数量	→	外箱包装数量
每卷:500PCS		每盒四盘，共2000 PCS		小箱6盒，共12000 PCS
				中箱8盒，共16000 PCS
				大箱10盒，共20000 PCS
		内盒包装尺寸	→	外箱包装尺寸
		20.3*19.3*5.5cm		小箱，40.6*23*19.7cm
				中箱，41*22*26cm
				大箱，41*22*33cm

APPROVED	CHECKED	PREPARED
曾凡强	卢嘉良	邹声平