


Amphenol FCI
© 2016 AFCI



PRODUCT NUMBER
69167-XXXXXXHLF

LEAD FREE OPTION
NOTE 1, 2, 7
PACKAGE OPTION
BLANK : BAG
R : TAPE AND REEL (NO CAP)
V : TAPE AND REEL (WITH CAP)
POLARIZATION
NOTE 10
NO. OF POS.
SEE TABLE
PIN PLATING
BASE P/N



.025/.64 □ PIN
⌀ .020/0.51 (M) A (S) B (S)
AT TIP
BOTH ENDS

NOTE 5
DETAIL J
SCALE 16/1



Mat'l. code NOTES 1 & 2				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection inch/mm	product family			
ltr	ecm no	dr	date	tolerances unless otherwise specified			title			
T	ELX-N-011896	JZ	05/31/12	angles	linear	scale 1:1	FRICITION LATCH HEADER SINGLE ROW VERTICAL			
U	ELX-N-20592	J.H	03/30/15							
V	ELX-N-37212	M.Z	05/29/20	0°±2°			dwg no			
W	ELX-N-44959	M.X	06/06/22	dr	M.CLOUSER	11/27/90				
X	ELX-N-49432	TY	10/10/23	enr	C.TREXTLER	11/27/90	69167			
Y	ELX-N-52600	MZ	08/22/24	chr	C.TREXTLER	11/27/90				
				appd	C.TREXTLER	11/27/90	type Product Customer Drawing			
sheet	revision	Y	Y	Y						
index	sheet	1	2	3						

PIN PLATING CODES	
XXXXX-1YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-2YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-3YY	50u"/1.27u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-4YY	
XXXXX-4YYHLF	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 9)
XXXXX-7YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-8YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni

