

MLVS 0402 Lead Free Series Specification

Product Name	Multilayer Varistor
Series	MLVS Lead Free Series
Size	EIA 0402



MLVS 0402 Lead Free Series Engineering Specification

1. Scope



- (1) SMD type zinc oxide based ceramic chip
- (2) Lead free plating termination provided good solderability characteristic
- (3) Insulator over coat keeps excellent low and stable leakage current
- (4) Quick response time (<1ns)
- (5) Low clamping voltage
- (6) High transient current capability
- (7) Compact size for EIA 0402

Applications



Applications for Mother Board and Notebook, Cellular Phone, PDA, handheld device, DSC, DV, Scanner, and Set-Top Box etc.

Suitable for Push-Button, Power Line and Low Frequency single line over voltage protect.

2. Explanation of Part Number



3. Construction & Dimension



Unit: mm	0402
L	0.96±0.12
W	0.48±0.07
T	0.50±0.10
C	0.25±0.15

4. Part ratings and characteristics:

4.1. Rating(25±5°C)

	Working voltage		Varistor voltage	Clamping Voltage	Capacitance	Peak current	Transient energy
Symbol	V_{RMS}	V_{DC}	V_V	V_C	C_p	i_{max}	W_{max}
Units	Volts	Volts (Max.)	Volts	Volts (Max.)	pF (Typical)	Amps (Max.)	Joules (Max.)
Test Condition		$< 10 \mu A$	1mA DC	1A 8/20 μs	1MHz	8/20 μs	10/1000 μs
MLVS 0402 L04	4	5.5	8 ~ 18	24	270	20	0.05
MLVS 0402 L04M	4	5.5	6.4 ~ 9.6	26	270	20	0.05
MLVS 0402 L04P	4	5.5	7.2 ~ 10.8	26	270	20	0.05
MLVS 0402 L07	7	9	11.5 ~ 21.5	41	130	20	0.05
MLVS 0402 L14	14	18	23 ~ 33	54	85	20	0.05
MLVS 0402 L15	15	20	Min 35	100	10	5	-
MLVS 0402 L17	17	20	32 ~ 42	70	35	20	0.05
MLVS 0402 L19	19	24	32 ~ 42	70	35	20	0.05
MLVS 0402 LE05	-	17	21.6~32.4	66	15		
MLVS 0402 LE06	-	5	28 ~ 38	72	7	-	-
MLVS 0402 LE08	-	12	25 ~ 40	110	7	-	-
MLVS 0402 LE10	-	12	45 ~ 65	150	3.5	-	-
MLVS 0402 LE11	-	18	45 ~ 65	150	3.5	-	-
MLVS 0402 LE12	-	26	45 ~ 65	145	4	-	-
MLVS 0402 LE17		36	45 ~ 65	150	3.5		

V_{RMS} – Maximum AC operating voltage the varistor can maintain and not exceed 10 μ A leakage current

V_{DC} – Maximum DC operating voltage the varistor can maintain and not exceed 10 μ A leakage current

V_V – Voltage across the device measured at 1mA DC current.

EquiValent to V_b , “Breakdown Voltage”.

C_p – Device capacitance measured with zero volt bias 1Vrms at 1MHz.

V_C – Maximum peak voltage across the varistor measured at 8/20 μ s waveform and 1A pulse current

i_{max} – Maximum peak current which may be applied with 8/20 μ s waveform without device failure

W_{max} – Maximum energy that may be dissipated with the 10/1000 μ s waveform without device failure.

5. General electrical specifications

5.1. General technical data

Operating temperature	-40 ... +85°C
Storage temperature (on board)	-40... +85°C
Response time	<1 ns
Solderability	245±5°C, 5+0/-0.5sec
Solder leach resistance	260±5°C, 10 ±1sec

5.2. Environmental Specifications

Characteristics	Specifications	Test condition
Bias humidity	$\Delta V_V / V_V \leq \pm 10\%$	90%RH, 40°C, Working voltage, 1000 hours
Thermal shock	$\Delta V_V / V_V \leq \pm 10\%$	-40°C to 85°C, 30 min. Cycle, 5 cycles
Full load voltage	$\Delta V_V / V_V \leq \pm 10\%$	Working voltage, 85°C, 1000 hours

5.3. Storage Condition with package


Storage Time: 12 months max

Storage Temperature : 5 to 40°C

Relative Humidity: to 65 %


6. Taping Package and Label Marking

6.1. Carrier tape dimensions



Type	A	B	W	E	F	P0	P1	P2	D0	T
0402	0.59 ±0.03	1.12 ±0.03	8.0 ±0.1	1.75 ±0.05	3.5 ±0.05	4.0 ±0.1	2.0 ±0.05	2.0 ±0.05	1.55 ±0.05	0.60 ±0.03

6.2. Taping reel dimensions



6.3 Taping specifications

There shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the head of taping.

6.4 Label Marking

The label specified as follows shall be put on the side of reel.

- (1) Part No.
- (2) Quantity
- (3) Lot No.

*Part No. And Quantity shall be marked on outer packaging.

6.5 Quantity of products in the taping package

- (1) Standard quantity : 10,000pcs/Reel for MLVS 0402 Lead Free Series
- (2) Shipping quantity is a multiple of standard quantity.


7. Precautions for Handling

7.1. Solder cream in reflow soldering

Refer to the recommendable land pattern as printing mask pattern for solder cream.

(1) Print solder in a thickness of 150 to 200 μm .

(2) Dimensions: millimeters (inches)



7.2. Precaution for handling of substrate

Do not exceed to bend the board after soldering this product extremely.

(Reference examples)

- Mounting place must be as far as possible from the position, which is close to the break line of board, or on the line of large holes of board.
- Do not bend extremely the board, in mounting another components.
If necessary, use back-up pin (support pin) to prevent from bending extremely.
- Do not break the board by hand. We recommend using the machine or the jig to break it.


7.3. Precaution for soldering

Note that rapid heating, rapid cooling or local heating will easily damage this product.

Do not give heat shock over 100°C in the process of soldering. We recommend taking preheating and gradual cooling.

7.4. Recommendable reflow soldering

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (T _{smax} to T _p)	3° C/second max.
Preheat <ul style="list-style-type: none"> – Temperature Min (T_{smin}) – Temperature Max (T_{smax}) – Time (t_{smin} to t_{smax}) 	150 °C 200 °C 60-180 seconds
Time maintained above: <ul style="list-style-type: none"> – Temperature (T_L) – Time (t_L) 	217 °C 60-150 seconds
Peak/Classification Temperature (T _p)	260 °C
Time within 5 °C of actual Peak Temperature (t _p)	20-40 seconds
Ramp-Down Rate	6 °C/second max.
Time 25 °C to Peak Temperature	8 minutes max.



*According to J-STD-020C

7.5. Soldering gun procedure

Note the follows, in case of using solder gun for replacement.

- (1) The tip temperature must be less than 280°C for the period within 3 seconds by using soldering gun less than 30 W.
- (2) The soldering gun tip shall not touch this product directly.

7.6. Soldering volume

Note that excess of soldering volume will easily get crack the body of this product.