

|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

客戶名稱

Customer

:

客戶編碼

Customer P/N

:

產品系列

Series

:

贴片共模电感

Common mode choke

產品編碼

Supply P/N

:

PCAQ1211H-501T14

發版號

Version

:

A2.0

承認日期

Endorsement Date

:

2025-5-13

備註

Note

:

|                                                                     |       |
|---------------------------------------------------------------------|-------|
| 譜羅德電子科技（深圳）有限公司<br>PuLuoDe Electronic Technology (Shenzhen) Co. LTD |       |
| 製作<br>APPROVED                                                      | Ben   |
| 審查<br>CHECKED                                                       | Yuki  |
| 确认<br>PREPARED                                                      | Peter |

\*烦请贵司在正式订单下达前确认回签本承诺书，否则敝司默认贵司认可本承诺书内的参数与条款，并以此参数生产交货

Please confirm and sign this acknowledgement letter before placing the formal order, otherwise PROD will acquiesce that your company recognizes the parameters and terms in this acknowledgement letter, and will produce and deliver according to these parameters.

客戶承認

Customer Approval

客戶簽章



修訂記錄  
REVISION RECORD






|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

| Version | REVISION ITEM | BEFORE REVISION | AFTER REVISION | DATE      |
|---------|---------------|-----------------|----------------|-----------|
| A2.0    | First Version |                 |                | 2025-5-13 |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |
|         |               |                 |                |           |

|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

封裝尺寸  
Dimension (mm)

推薦的焊盤尺寸  
Recommaned Land Pattern



| 系列<br>Series | 封裝尺寸<br>Dimension |          |        |          |         |        |         | 焊盤尺寸<br>Land Pattern |     |     |     |
|--------------|-------------------|----------|--------|----------|---------|--------|---------|----------------------|-----|-----|-----|
|              | A                 | B        | C      | D        | E       | F      | G       | a                    | b   | c   | d   |
| 1211         | 12.0±0.5          | 10.8±0.5 | 6.5MAX | 2.7 ±0.5 | 2.5±0.5 | 7.0Typ | 2.5 Typ | 3.5                  | 3.2 | 9.5 | 5.2 |

### 編碼解釋

Code interpretation

**PCAQ**

類別碼

Category code

**1211**

尺寸系列

Dimension

**H**

系列碼

Series Code

**XXX**

阻抗值

Impedance

**T14**

額定電流

Rated Current

### 電氣參數

Electrical Characteristics

| 產品編碼<br>P/N      | @ 25 °C Ambient Temperture |     |     |             |                         |
|------------------|----------------------------|-----|-----|-------------|-------------------------|
|                  | 阻抗值<br>(Z)                 |     | DCR | 絕緣性<br>(IR) | 額定電流<br>(Rated Current) |
|                  | Ω                          |     | mΩ  | MΩ          | A                       |
|                  | Min                        | Typ | Max | Min         | Max                     |
| PCAQ1211H-501T14 | 250                        | 500 | 3   | 10          | 14                      |


- ◎ 規格參數基於環境溫度25℃取得  
All test Data is referenced to 25℃ ambient
- ◎ 電感工作環境溫度：-40℃ ~ 125℃  
Operating temperature range -40 °C to +125 °C
- ◎ 加載額定電流會使電感溫度上升大約 40℃ (電感初始溫度+上升溫度=電感最終溫度)  
Typical Heat Rating DC Current would cause an approximately ΔT of 40℃
- ◎ 務必考慮最終的產品設計，元器件佈局，線路板走線，以及使用環境過程中，電感最終溫度不得超過125℃  
The operating temperature of inductance do not exceed 125℃
- ◎ 使用電感時，請查閱第7頁注意事項  
The announcements is on page7



|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

## 電路結構

## Connections




◎ 電感內置兩組線圈

Inductor Contents Two (2) Set(s) of Coil

## 特性曲線

## Performance Curves



## 材料清單

## Material List

| NO. | 材料<br>ITEM | 材質規格<br>Material | 製造商<br>Manufacturer   | UL NO.  |
|-----|------------|------------------|-----------------------|---------|
| 1   | 磁芯/Core    | S8H              | SINCORES (或等同廠商規格)    | N.A     |
| 2   | 漆包線/Wire   | P180             | ELEKTRISOLA (或等同廠商規格) | E258243 |
| 3   | 蓋子/Cover   | LCP              | TY (或等同廠商規格)          | N.A     |
| 4   | 胶水/Glue    | E500AH           | ASIASEAL (或等同廠商規格)    | N.A     |
| 5   | 锡条/Sn      | 107              | CITY (或等同廠商規格)        | N.A     |



|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

### 机械可靠性测试

### Mechanical Reliability

| 實驗名稱<br>ITEM           | 試驗要求<br>Specification & Requirement                                        | 試驗方法<br>Method Used                                                                                         |
|------------------------|----------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|
| 可焊性實驗<br>Solderability | The surface of terminal/pin tested shall be covered with new solder by 95% | Solder heat proof:<br>Preheating: 180 ±10℃ 90 seconds<br>Soldering: 255 ±5℃ for 3 ±1 sec                    |
| 機械衝擊<br>Shock          | Inductance change within ± 5% Without mechanical damage                    | Drop down with 981m/s2 (100G) shock<br>Attitude upon a rubber block method shock testing machinem, 3 tests. |
| 振動實驗<br>Vibration      | Inductance change within ± 5% Without mechanical damage                    | Vibration frequency:<br>10Hz to 55Hz to 10Hz 60 seconds cycle<br>Vibration time: 2 hours                    |

### 老化测试

### Aging Reliability

| 實驗名稱<br>ITEM                 | 試驗要求<br>Specification & Requirement                     | 試驗方法<br>Method Used                                                                            |
|------------------------------|---------------------------------------------------------|------------------------------------------------------------------------------------------------|
| 冷熱衝擊<br>Thermal Shock        | Inductance change within ± 5% Without mechanical damage | -40℃, (30 mins) -> room temp. (5 mins) -> 125℃, (30 mins) -> room temp. (5 mins)<br>100 cycles |
| 耐熱性<br>Heat Resistance       | Inductance change within ± 5% Without mechanical damage | Apply IDC current @ 85℃ ambient<br>Duration: 1000 hrs                                          |
| 耐濕性<br>Humidity Resistance   | Inductance change within ± 5% Without mechanical damage | Apply IDC current @ 60℃ ambient<br>Humidity: 90~95%<br>Duration: 1000 hrs                      |
| 低溫存儲實驗<br>Low Temp. Storing  | Inductance change within ± 5% Without mechanical damage | Storing Temp.<br>-40 ±2 ℃ for total 1,000 +4/-0 hours                                          |
| 高溫存儲實驗<br>High Temp. Storing | Inductance change within ± 5% Without mechanical damage | Storing Temp.<br>125 ±2 ℃ for total 1,000 +4/-0 hours                                          |



包裝方式  
PACKING FOR SMD




|                |                  |                         |                                      |
|----------------|------------------|-------------------------|--------------------------------------|
| 產品編碼<br>P/N    | PCAQ1211H-501T14 | 測試設備<br>TEST INSTRUMENT | Keysight:E4991B<br>Chroma:16502 3302 |
| 產品系列<br>Series | 贴片共模电感           | 測試頻率<br>TEST FREQUENCY  | 100MHZ / 0.1V                        |

載帶卷盤尺寸：(mm)

Packing Dimension

|           |     |     |      |    |    |    |           |
|-----------|-----|-----|------|----|----|----|-----------|
| MPQ       | A   | B   | C    | W  | P  | Po | L         |
| 500pcs/卷盤 | 330 | 100 | 24.5 | 24 | 20 | 4  | 200mm Min |




載帶剝離力：

Typical Pulling Force

對上蓋帶施加力：20g~120g內即可與下載帶剝離

Tape Peeling off force: 20g~120g




裝箱數量：

Package Quantity


500pcs/卷盤

500pcs/Reel




1000pcs/每盒

1000pcs/ Middle box



3000pcs/每箱

3000pcs/ Outer box



◎ 實際出貨過程，依據客戶需求狀況的不同，包裝數量會有變化，最終的包裝數量請參照實際出貨包裝

In the actual delivery process, the package quantity will change according to the different customer demands. Please refer to the actual shipment quantity for the final package quantity





## 注意事项

使用本产品时，请注意以下事项

- ◎ 产品保存期限为12个月，保存条件：温度5~40℃，湿度10~75%RH以内，超过保存期限可能会使元器件电极发生氧化，存储标准可参照：IEC\_61760-2-2021  
This components storage life is 12 months, Storage Temperature: TEMP. 5~40℃; RH10~75%. Please use this components within the warranty period. refer standard to: IEC\_61760-2-2021
- ◎ 请勿在极端环境下使用和保存（高盐，强酸，强碱，强辐射等）。  
Do not use this component in special environments, such as high salt content, strong acid, strong alkali, strong corrosion and other special environments.
- ◎ 元器件焊接前，请进行预热，预热与焊接温度之间温差建议控制在150℃以内；焊接标准参考：EN61760-1:2006  
Please preheat the product before welding; it is recommended to control the preheating temperature and welding temperature within 150℃. refer standard to: EN61760-1:2006
- ◎ 元器件焊接后需重新拆卸焊接修正时，请遵循规格书规定的条件范围；过高的加热温度以及反复的拆卸可能会导致元器件失效。  
When repairing this component, the temperature used for disassembly should not exceed the datasheet limit and do not disassemble it frequently to prevent damage to the component.
- ◎ 请勿用清洗剂、丙酮等腐蚀性液体接触该元器件，这可能会侵蚀元器件本体以至于失效。  
Do not use acetone or other corrosive liquids to contact this component or it will cause it to fail.
- ◎ 元器件焊接到线路板后，请注意不可因线路板整体变形或局部变形而施加给电感剩余应力，这可能会导致元器件脱落、破损失效。  
When this component is soldered to the circuit board, you need to pay attention to the stress applied to it by the PCB, which may cause it to fall off or damaged fail.
- ◎ 元器件通电后温度会随电流的增大而上升，设计时请务必考虑留有余量。  
Self heating (Rated Current or Irms) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.
- ◎ 过高的静电会损坏该元器件，请注意静电防护。  
Too high static electricity will cause permanent damage to the product, please pay attention to electrostatic protection.
- ◎ 本元器件作为磁性产品，设计时请务必考虑周边元器件与本产品可能产生的耦合效应影响。  
This magnetic component needs to be considered for coupling effects in the application.
- ◎ 谱罗德并不能完全掌握或熟悉客户的特定应用以及要求，贵司有责任和义务验证此元器件以及元器件规格书中的描述是否满足于贵司的设计要求；需要指出是：即使按照现有的技术标准操作，该元器件依然有几率在典型寿命结束前发生故障，谱罗德强烈建议贵司对于该元器件在一些典型的严苛应用中，例如安规产品，工业产品、医疗产品、车载产品、航空/航天等产品应用，对于该元器件可能存在的失效情况做适当的冗余设计，以此避免该元器件在失效时造成严重后果；特别提醒：对于特定的应用对象谱罗德强烈要求贵司同谱罗德取得书面的许可，否则谱罗德不承担元器件失效带来的任何责任，特定对象包括且不限于：车用，航空航天，安规产品，军用以及贵司对元器件有严苛要求的产品。

PROD cannot fully understand and be familiar with customers' specific applications and requirements. Your company has the responsibility and obligation to verify whether the components and the description in the component specification meet your design requirements. Special reminder: Even if operated in accordance with existing technical standards, this component still has a chance of failure before the end of its typical life. PROD strongly recommends that your company make appropriate redundant designs for possible failure situations of this component in some typical harsh applications, such as safety products, industrial products, medical products, automotive products, aviation/aerospace products, etc., so as to avoid serious consequences when the component fails.

**PROD Requirements:** For specific application item, PROD strongly requires your (or company) to obtain written permission from PROD, otherwise PROD will not bear any responsibility for component failure. Specific item list include but are not limited to: automotive, aerospace, safety products, military and products that your company has strict requirements on components.

Page 7 / 7



譜羅德電子科技（深圳）有限公司

PuLuoDe Electronic Technology (Shenzhen) Co., LTD

深圳市寶安區石岩三聯工業區B棟311

更多规格请访问谱罗德官方网站下载或者  
扫描二维码通过微信小程序获取

<http://www.prodtech.cn/>

