

A				B		C		D		E		F		G		
1	性能参数															1
	1. Heating current: Ui: AC250V, lth: 3A 发热电流: Ui: AC250V, lth: 3A							13. Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C								
	2. Rated current:2A/DC36V 额定电流:2A/DC36V							14. Compression torque: ≤ 3N 按压扭力: ≤3N								
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min							15. Electrical life: 100000 cycles 电气寿命: 100000 cycles								
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ							16. mechanical: 5000000cycles 机械寿命: 5000000cycles								
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ							17. Operation method:Self compound 操作方式: 自复式								
	6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10							18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N								
	7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10							19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下								
	8. welding temperature: 320 °C± 20 °C 焊接温度: 320 °C± 20 °C							20. LED lamp lifespan: 40000h LED寿命: 40000h								
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration							21. LED color: Red LED颜色: 红色								
2																2
3																3
4																4
5																5

A		B		C		D		E		F		G	
材质参数													
9		luminous zone 发光区		PC 塑料		1							
8		LEDpin LED脚		Brass 黄铜		1				Silvering 镀银			
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		Base 基座		PBT		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		SUS 不锈钢		1							
1		Key 按键		SUS 不锈钢		1							
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91205P224RS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													