

1. Description

The SMxxC Series is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.


3. Applications

- Cell Phone Handsets and Accessories
- Microprocessor based equipment
- Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers

2. Features

- 350 Watts Peak Pulse Power per (8/20μs)
- IEC61000-4-2 (ESD) ±15kV (air), ±8kV (contact)
- IEC61000-4-4 (EFT) 40A (5/50ns)
- Protects two bidirectional line
- Low clamping voltage
- Low leakage current
- Working voltages : 3V, 5V, 8V, 12V, 15V, 18V, 20V, 24V, 36V

4. Pinning information



SOT-23



5. Absolute Maximum Ratings

Parameter	Symbol	Value	Units
ESD per IEC 61000-4-2 (Air)	V_{ESD}	± 15	kV
ESD per IEC 61000-4-2 (Contact)		± 8	kV
Peak Pulse Power($t_p=8/20\mu s$ waveform)	P_{PP}	350	W
Junction Temperature	T_{OPT}	-55 to 150	°C
Storage Temperature	T_{STG}	-55 to 150	°C
Lead Solder Temperature – Maximum (10 Second Duration)	T_L	260 (10 sec.)	°C

Notes: The above data are for reference only.









6.Electrical Characteristics(T_A=25°C)

PART NUMBER	V _{RWM}	V _B	I _T	V _{C@1A}	V _C		I _R	C _T
	(V)	(V)	(mA)	(V)	(V)		(μA)	(pF)
	(max.)	(min.)		(max.)	(max.)	(@A)	(max.)	(max.)
SM03C	3.3	4	1	7.5	16	20	40	450
SM05C	5	6	1	9.8	18	17	10	200
SM08C	8	8.5	1	13.4	24	15	2	120
SM12C	12	13.3	1	19	32	11	1	75
SM15C	15	16.7	1	24	38	10	1	68
SM18C	18	20.0	1	29	45	9	1	57
SM20C	20	22.3	1	35	50	8	1	52
SM24C	24	26.7	1	43	52	7	1	50
SM36C	36	40	1	60	75	4.5	1	35




7. Typical characteristic

	
Figure 1: 8/20µs Waveform per IEC61000-4-5	Figure 2: Contact Discharge Current Waveform per IEC 61000-4-2)
	
Figure 3: Voltage vs Capacitance	Figure 4: Voltage vs Capacitance
	
Figure 5: Clamping Voltage vs Peak Pulse Current	Figure 6: Clamping Voltage vs Peak Pulse Current



8.SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	B	b_p	C	D	E	H_E	A1	L_p
Min	0.95	1.78	0.35	0.08	2.70	1.20	2.20	0.013	0.20
Max	1.40	2.04	0.50	0.19	3.10	1.65	3.00	0.100	0.50



9.Ordering information



yww: Batch Code

Order Code	Marking	Package	Base QTY	Delivery Mode
UMW SM03C	03C	SOT-23	3000	Tape and reel
UMW SM05C	05C	SOT-23	3000	Tape and reel
UMW SM08C	08C	SOT-23	3000	Tape and reel
UMW SM12C	12C	SOT-23	3000	Tape and reel
UMW SM15C	15C	SOT-23	3000	Tape and reel
UMW SM18C	18C	SOT-23	3000	Tape and reel
UMW SM20C	20C	SOT-23	3000	Tape and reel
UMW SM24C	24C	SOT-23	3000	Tape and reel
UMW SM36C	36C	SOT-23	3000	Tape and reel



10.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.