





A4			
A3			
A2			
A1			
REV	DATE	REVISION DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
ROCPU TECHNOLOGY CO.,LTD			

MODEL NO: TP91201P2S
Https: www.rocpu.tw

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G				
1	性能参数										
	1. Heating current: Ui: AC250V, lth: 3A 发热电流: Ui: AC250V, lth: 3A			13. Compression torque: ≤ 3N 按压扭力: ≤3N							
	2. Rated current:2A/DC36V 额定电流:2A/DC36V			14. Electrical life: 500000 cycles 电气寿命: 500000 cycles							
	3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			15. mechanical: 500000cycles 机械寿命: 500000cycles							
	4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			16. Operation method:Self compound 操作方式: 自复式							
2	5. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10			17. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	6. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10										
	7. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃										
	8. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration										
	9. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	10. Protection level:IP65 防护等级:IP65										
3	11. Explosion prevention level: IK08 防暴等级: IK08										
	12. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃										
4											
5	A4			 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91201P2S
	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	X					
				ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

	A	B	C	D	E	F	G
1	材质参数						
	10						
	9						
2	8						
	7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金		
	6	Contact material 接触材质	Silvering 镀银	1			
3	5	Base 基座	PBT	1			
	4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍		
	3	Oring O型圈	Silica gel 硅胶	1			
4	2	Housing 外壳	SUS 不锈钢	1			
	1	Key 按键	SUS 不锈钢	1			
	NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注		

A4				 台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91201P2S	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https:	www.rocpu.tw
A1						X.X	± 0.15	ROCPU TECHNOLOGY CO.,LTD					
						X	± 0.25						
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
A				B	C		D	E		F		G	