

SOT-23 Surface Mount Schottky Barrier Rectifier

Features

- V_R 70V
- $I_{F(AV)}$ 0.07A
- High Current Capability
- Low Forward Voltage Drop
- Extremely Fast Switching Speed

Applications

These Schottky barrier diodes are designed for high speed switching applications, circuit protection, and voltage clamping.


Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Cathode line denotes the cathode end


Function Diagram

Reverse Voltage
70 V
Forward Current
0.07 Ampere


SOT-23




Marking:
BAS70:73
BAS70-04:74
BAS70-05:75
BAS70-06:76




BAS70




BAS70-04



BAS70-05



BAS70-06







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Maximum repetitive peak reverse voltage	V_{RRM}	V	70
Maximum RMS voltage	V_{RMS}	V	49
Maximum DC blocking voltage	V_{DC}	V	70
Maximum average forward rectified current	$I_{F(AV)}$	mA	70
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I_{FSM}	mA	100
Power Dissipation	P_D	mW	200
Junction Temperature	T_j	°C	-55 ~+125
Storage temperature range	T_{STG}	°C	-55 ~+125
Typical thermal resistance	$R_{\theta JA}$	°C /W	500

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	Min	Typ	Max
Maximum forward voltage	$I_F = 1.0\text{mA}$	V_F	mV	—	—	410
	$I_F = 15\text{mA}$			—	—	1000
Maximum reverse current	$V_R = 50\text{V}$	I_R	μA	—	—	0.2
Capacitance between terminals	$V_R = 1.0\text{V}, f = 1\text{MHz}$	C_T	pF	—	2.0	—
Reverse breakdown voltage	$I_R = 10\mu\text{A}$	V_R	V	—	—	70
Maximum reverse recovery time	$I_F = I_R = 10\text{mA}, I_{(\text{REC})} = 1.0\text{mA}$	t_{rr}	ns	—	—	5.0

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



BAS70 THRU BAS70-06

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.008	3000	45000	180000	7"

● Package Outline Dimensions (SOT-23)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.75	0.85	0.030	0.033
K	0.85	0.95	0.033	0.037
M	1.95	2.05	0.077	0.081
N	1.85	1.95	0.073	0.077