



Single color electrical schematic diagram
单色电气原理图



Installation View
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP92214P124GS

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

A		B		C		D		E		F		G	
1	性能参数												1
	1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A												
	2. Rated current:3A/DC36V 额定电流:3A/DC36V												
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min												
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ												
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ												
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10												
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10												
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	9. Protection level:IP67 防护等级:IP67												
2	10. Explosion prevention level: IK10 防暴等级: IK10												2
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	12. Compression torque: ≤ 6N 按压扭力: ≤ 6N												
	13. Electrical life: 100000 cycles 电气寿命: 100000 cycles												
	14. mechanical: 500000cycles 机械寿命: 500000cycles												
	15. Operation method:Self-locking 操作方式: 自锁式												
	16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下												
	17. LED lamp lifespan: 40000h LED寿命: 40000h												
	18. LED color: Green LED颜色: 绿色												
	19. LED Lamp Voltage: 24V LED灯电压: 24V												
3	20. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N												3
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 1NO1NCSwitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线(NO) 黄线(NC)												
	2.2 2NO2NC switch function wire: green black wire C, blue black wire NO, yellow white wire NC 2NO2NC开关功能线材: 绿黑线C、蓝黑线NO、黄白线NC												
	2.3 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极												
	5												
	4												
	5												
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													
5													

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑胶		1							
9	LEDpin LED引脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED底座			PC 塑胶		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			SUS 不锈钢		1							
1	Key 按键			SUS 不锈钢		1							
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92214P124GS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													