



1.Features

- For surface mounted applications
- Low-profile package
- Optimized for LAN protection applications
- Ideal for ESD protection of data lines in accordance with IEC 61000-4-2 (IEC 801-2)
- Ideal for EFT protection of data lines in accordance with IEC 61000-4-4 (IEC 801-4)
- ESD-protection acc. IEC 61000-4-2
 - ± 30 kV contact discharge
 - ± 30 kV air discharge
- Low incremental surge resistance, excellent clamping capability
- 200 W peak pulse power capability with a 10/1000 μ s waveform, repetition rate (duty cycle): 0.01 %
- “Low-Noise” technology - very fast response time
- High temperature soldering guaranteed: 260 °C/10 s at terminals
- e3 - Sn
- AEC-Q101 qualified

2.Pinning information



SOD-123FL



3. Absolute Maximum Ratings ($T_{amb}=25^{\circ}\text{C}$, unless otherwise specified)

Parameter	Symbol	Conditions	Value	Units
Peak pulse current	I_{PPM}	$t_p=10/1000\ \mu\text{s}$ waveform	see "Electrical Characteristics"	A
Peak pulse power	P_{PP}	$t_p=10/1000\ \mu\text{s}$ waveform	200	W
Peak forward surge current	I_{FSM}	8.3 ms single half sine-wave	50	A
ESD immunity	V_{ESD}	Contact discharge acc.IEC61000-4-2;10 pulses	± 30	kV
		Air discharge acc.IEC61000-4-2;10 pulses	± 30	kV
Junction Temperature	T_J	Junction temperature	-55 to 150	$^{\circ}\text{C}$
Storage temperature	T_{STG}		-55 to 150	$^{\circ}\text{C}$



4. Electrical Characteristics ($T_A=25^{\circ}\text{C}$)

Type		Marking		V_{RMW}	Breakdown Voltage		Test Current	Reverse Leakage	Max. Clamp Voltage	Peak Pulse Current
					$V_{\text{BR}} @ I_{\text{T}}$		I_{T}	$I_{\text{R}} @ V_{\text{RMW}}$	$V_{\text{C}} @ I_{\text{PP}}$	I_{PP}
					Min	Max				
Uni	Bi	Uni	Bi	V	V	V	mA	μA	V	A
SMF5.0A	SMF5.0CA	AE	NE	5	6.4	7	10	400	9.2	21.7
SMF6.0A	SMF6.0CA	AG	NG	6	6.67	7.37	10	400	10.3	19.4
SMF6.5A	SMF6.5CA	AK	NK	6.5	7.22	7.98	10	250	11.2	17.9
SMF7.0A	SMF7.0CA	AM	NM	7	8.33	8.6	10	100	12	16.7
SMF7.5A	SMF7.5CA	AP	NP	7.5	8.89	9.21	1	50	12.9	15.5
SMF8.0A	SMF8.0CA	AR	NR	8	9.44	9.83	1	25	13.6	14.7
SMF8.5A	SMF8.5CA	AT	NT	8.5	10	10.4	1	10	14.4	13.9
SMF9.0A	SMF9.0CA	AV	NV	9	11.1	11.1	1	5	15.4	13
SMF10A	SMF10CA	AX	NX	10	12.2	12.3	1	2.5	17	11.8
SMF11A	SMF11CA	AZ	NZ	11	13.3	13.5	1	2.5	18.2	11
SMF12A	SMF12CA	BE	OE	12	14.4	14.7	1	2.5	19.9	10.1
SMF13A	SMF13CA	BG	OG	13	15.6	15.9	1	1	21.5	9.3
SMF14A	SMF14CA	BK	OK	14	16.7	17.2	1	1	23.2	8.6
SMF15A	SMF15CA	BM	OM	15	17.8	18.5	1	1	24.4	8.2
SMF16A	SMF16CA	BP	OP	16	18.9	19.7	1	1	26	7.7
SMF17A	SMF17CA	BR	OR	17	20	20.9	1	1	27.6	7.2
SMF18A	SMF18CA	BT	OT	18	22.2	22.1	1	1	29.2	6.8
SMF20A	SMF20CA	BV	OV	20	24.4	24.5	1	1	32.4	6.2
SMF22A	SMF22CA	BX	OX	22	26.7	26.9	1	1	35.5	5.6
SMF24A	SMF24CA	BZ	OZ	24	28.9	29.5	1	1	38.9	5.1
SMF26A	SMF26CA	CE	PE	26	31.1	31.9	1	1	42.1	4.8
SMF28A	SMF28CA	CG	PG	28	33.3	34.4	1	1	45.4	4.4



Type		Marking		V_{RMW}	Breakdown Voltage		Test Current	Reverse Leakage	Max. Clamp Voltage	Peak Pulse Current
					$V_{BR} @ I_T$		I_T	$I_R @ V_{RMW}$	$V_C @ I_{PP}$	I_{PP}
					Min	Max				
Uni	Bi	Uni	Bi	V	V	V	mA	μA	V	A
SMF30A	SMF30CA	CK	PK	30	33.3	36.8	1	1	48.4	4.1
SMF33A	SMF33CA	CM	PM	33	36.7	40.6	1	1	53.3	3.8
SMF36A	SMF36CA	CP	PP	36	40	44.2	1	1	58.1	3.4
SMF40A	SMF40CA	CR	PR	40	44.4	49.1	1	1	64.5	3.1
SMF43A	SMF43CA	CT	PT	43	47.8	52.8	1	1	69.4	2.9
SMF45A	SMF45CA	CV	PV	45	50	55.3	1	1	72.7	2.8
SMF48A	SMF48CA	CX	PX	48	53.3	58.9	1	1	77.4	2.6
SMF51A	SMF51CA	CZ	PZ	51	56.7	62.7	1	1	82.4	2.4
SMF54A	SMF54CA	DE	PA	54	60	66.3	1	1	87.1	2.3
SMF58A	SMF58CA	DG	PC	58	64.4	71.2	1	1	93.6	2.1
SMF60A	SMF60CA	DK	CDK	60	66.7	73.7	1	1	96.8	1.8
SMF64A	SMF64CA	DM	CDM	64	71.1	78.6	1	1	103	1.7
SMF70A	SMF70CA	DP	CDP	70	77.8	86	1	1	113	1.5
SMF75A	SMF75CA	DR	CDR	75	83.3	92.1	1	1	121	1.4
SMF78A	SMF78CA	DT	CDT	78	86.7	95.8	1	1	126	1.4
SMF85A	SMF85CA	DV	CDV	85	94.4	104	1	1	137	1.3
SMF90A	SMF90CA	DX	CDX	90	100	111	1	1	146	1.2
SMF100A	SMF100CA	DZ	CDZ	100	111	123	1	1	162	1.1
SMF110A	SMF110CA	EE	CEE	110	122	135	1	1	177	1
SMF120A	SMF120CA	EG	CEG	120	133	147	1	1	193	0.9
SMF130A	SMF130CA	EK	CEK	130	144	159	1	1	209	0.8
SMF150A	SMF150CA	EM	CEM	150	167	185	1	1	243	0.7
SMF160A	SMF160CA	EP	CEP	160	178	197	1	1	259	0.7
SMF170A	SMF170CA	ER	CER	170	189	209	1	1	275	0.6



Type		Marking		V_{RMW}	Breakdown Voltage		Test Current	Reverse Leakage	Max. Clamp Voltage	Peak Pulse Current
					$V_{BR} @ I_T$		I_T	$I_R @ V_{RMW}$	$V_C @ I_{PP}$	I_{PP}
					Min	Max				
Uni	Bi	Uni	Bi	V	V	V	mA	μA	V	A
SMF180A	SMF180CA	ET	CET	180	201	222	1	1	292	0.5
SMF190A	SMF190CA	EV	CEV	190	211	232	1	1	308	0.5
SMF200A	SMF200CA	EX	CEX	200	224	247	1	1	324	0.5
SMF220A	SMF220CA	E22	CE22	220	246	272	1	1	356	0.5
SMF250A	SMF250CA	E25	CE25	250	279	309	1	1	405	0.5
SMF300A	SMF300CA	E30	CE30	300	335	371	1	1	486	0.45
SMF350A	SMF350CA	E35	CE35	350	391	432	1	1	567	0.4
SMF400A	SMF400CA	E40	CE40	400	447	494	1	1	648	0.35
SMF440A	SMF440CA	E44	CE44	440	492	543	1	1	713	0.3



5. Typical characteristic




Figure 1: Pulse Derating Curve




Figure 2: Maximum Non-Repetitive Surge Current




Figure 3: Steady State Power Derating Curve




Figure 4: Peak Pulse Power Rating Curve




Figure 5: Pulse Waveform





Figure 6: Typical Junction Capacitance



6.SOD123-FL Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	b	C	D	E	F	L
Min	0.6	1.55	2.5	0.8	0.05	0.5	3.5
Max	1.0	1.95	2.9	1.2	0.25	1.1	3.9



7.Ordering information



Order Code	Package	Base QTY	Delivery Mode
UMW SMFxxA	SOD123-FL	3000	Tape and reel
UMW SMFxxCA	SOD123-FL	3000	Tape and reel



8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.