








PCB. Welding diagram
PCB.焊接图



Circuit diagram
电路图



SPECIFICATION

规范

Rating: 100mA.12V DC

额定值: 100mA.12V DC

Insulation resistance: ≤100MΩ

绝缘电阻: ≤100MΩ

Dielectric strength: 250V 50HZ 1 min

抗电强度: 250V 50HZ 1 min

Contact resistance: ≤100mΩ max

接触电阻: ≤100mΩ max

Travel: 0.25±0.1mm

行程: 0.25±0.1mm

Lifetime: 100000 times

寿命: 100000 times

Operating force: 260±40gf

操作力: 260±40gf

5	Cover plate 盖板	SUS	1	Iron 铁盖
4	Stem 按钮	PA6T	1	Black 黑色
3	Shrapnel 弹片	SUS	1	SUS 不锈钢
2	Base 基座	PA6T	1	Black 黑色
1	Pin 引脚	Brass 黄铜	1	Agplating
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP16812650

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission