






Circuit diagram
电路图



Welding diagram
焊接图

SPECIFICATION

规范
Rating: 50mA.12V DC
额定值: 50mA.12V DC
Insulation resistance: ≤100MΩ
绝缘电阻: ≤100MΩ
Dielectric strength: 250V 50HZ 1 min
抗电强度: 250V 50HZ 1 min

Contact resistance: ≤100mΩ max
接触电阻: ≤100mΩ max
Travel: 0.25±0.1mm
行程: 0.25±0.1mm
Lifetime: 100000 times
寿命: 100000 times
Operating force: 260±40gf
操作力: 260±40gf

5	Stem 按钮	PA6T	1	Black 黑色
4	Cover plate 盖板	SUS	1	Iron 铁盖
3	Shrapnel 弹片	SUS	1	SUS 不锈钢
2	Pin 引脚	Brass	1	Agplating
1	Base 基座	PA6T	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP16722643
DATE	2019	APPROVAL B	Https: www.rocpcu.tw
ROCPU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			