

SOT-89 Plastic-Encapsulate Transistors


Features

- Complementary to 2SC2873
- Power dissipation of 500mW
- High stability and high reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C


Mechanical Data

- Case: SOT-89
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Collector-Base Voltage
VCBO -50V
Collector Current
-2.0 Ampere



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Collector-Base Voltage	V_{CBO}	V	-50
Collector-Emitter Voltage	V_{CEO}		-50
Emitter-Base Voltage	V_{EBO}		-5.0
Collector Current	I_C	A	-2.0
Collector Power Dissipation	P_C	mW	500
Storage temperature	T_{stg}	°C	-55 ~+150
Junction temperature	T_j	°C	-55 ~+150
Typical Thermal Resistance	$R_{\theta J-A}$	°C /W	250

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Max
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	V	$I_C = -100\mu A, I_E = 0$	-50	—
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$		$I_C = -10mA, I_B = 0$	-50	—
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$		$I_E = -100\mu A, I_C = 0$	-5.0	—
Collector-Base cut-off current	I_{CBO}	nA	$V_{CB} = -50V, I_E = 0$	—	-100
Emitter-Base cut-off current	I_{EBO}		$V_{EB} = -5.0V, I_C = 0$	—	-100
DC Current Gain	$h_{FE(1)}$	—	$I_C = -500mA, V_{CE} = -2.0V$	70	240
	$h_{FE(2)}$		$I_C = -2A, V_{CE} = -2.0V$	20	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	V	$I_C = -1A, I_B = -50mA$	—	-0.5
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	V	$I_C = -1A, I_B = -50mA$	—	-1.2

● Classification Of h_{FE}

RANK	O	Y
Range	70-140	120-240





● Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	Max
Transition frequency	f_T	$I_C=-0.5A, V_{CE}=-2V$	MHz	100	—



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-89	R1	0.055	1000	7000	21000	7"


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-89)



● Suggested Pad Layout

