


叠层片式铁氧体磁珠—PZ 系列

Multilayer Chip Ferrite Bead – PZ Series



工作温度
Operating Temp

- ◆ -55°C ~ +125°C

特征
Features

- ◆ 内部印有银电极的叠层结构，铁氧体屏蔽无串扰
- ◆ 具有较大的额定电流，允许的最大电流为 6A
- ◆ 在较宽的频率范围内具有优良的 EMI 抑制效果
- ◆ 三种铁氧体材料、阻抗范围宽，适用于不同的电子线路
- ◆ Internal silver printed layers and magnetic shielded structures to minimize crosstalk
- ◆ Large withstand current (allowable current: up to 6A)
- ◆ Can be used in a wide range of frequency to suppress EMI
- ◆ Three types material and wide range of impedance values for various applications

用途
Applications


- ◆ 电脑及周边设备，电源适配器、LCD TV 等音视频设备，通讯设备，办公自动化等电子设备的电源线或大电流信号线的噪声抑制
- ◆ Noise suppression for power line or large current signal of electric equipments such as computers and peripheral devices, power adapter, LCD TVs, communication equipments, OA equipments, etc.

产品型号
Product Identification

1	2	3	4	5	6	7	8
PZ	3216	U	121	-3R0	T	F	(A99)

1	2	3
分类 Type	外形尺寸 (L×W) (mm) External Dimensions (L×W) (mm)	材料代号 Material Code
PZ	0603 [0201] 0.6×0.3 1005 [0402] 1.0×0.5 1608 [0603] 1.6×0.8 2012 [0805] 2.0×1.25 3216 [1206] 3.2×1.6 4516 [1806] 4.5×1.6	D, E, U
4	5	6
公称阻抗值 Nominal Impedance	额定电流值 Rated Current	内部代码 Internal Code
Example Nominal Value	R60 0.6A 2R5 2.5A 3R0 3.0A	A99
6	7	8
包装 Packing	无有害物质产品 Hazardous Substance Free Products	
T 编带 Tape & Reel	F	

外观尺寸
Shape and Dimensions



Unit: mm [inch]

Type	L	W	T	a
PZ0603 [0201]	0.6±0.05 [.024±.002]	0.3±0.05 [.012±.002]	0.3±0.05 [.012±.002]	0.15±0.05 [.006±.002]
PZ1005 [0402]	1.0±0.15 [.039±.006]	0.5±0.15 [.020±.006]	0.5±0.15 [.020±.006]	0.25±0.1 [.010±.004]
PZ1608 [0603]	1.6±0.15 [.063±.006]	0.8±0.15 [.031±.006]	0.8±0.15 [.031±.006]	0.3±0.2 [.012±.008]
PZ2012 [0805]	2.0 (+0.3, -0.1) [.079 (+.012, -.004)]	1.25±0.2 [.049±.008]	0.85±0.2 [.033±.008]	0.5±0.3 [.020±.012]
PZ3216 [1206]	3.2±0.2 [.126±.008]	1.6±0.2 [.063±.008]	0.85±0.2 [.033±.008] 1.1±0.2 [.043±.008]	0.5±0.3 [.020±.012]
PZ4516 [1806]	4.5±0.2 [.178±.008]	1.6±0.2 [.063±.008]	1.6±0.2 [.063±.008]	0.5±0.3 [.020±.012]

规格特性

Specifications

PZ0603 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ0603D600-R50TF	60±25%	100	0.18	500	0.3±0.05 [.012±.002]
PZ0603D800-R50TF	80±25%	100	0.20	500	
PZ0603D121-R45TF	120±25%	100	0.25	450	
PZ0603D241-R35TF	240±25%	100	0.41	350	
PZ0603D601-R25TF	600±25%	100	1.00	250	
PZ0603D102-R20TF	1000±25%	100	1.40	200	
PZ0603U100-1R0TF	5~15	100	0.05	1000	
PZ0603U800-R50TF	80±25%	100	0.18	500	
PZ0603U121-R45TF	120±25%	100	0.23	450	
PZ0603U241-R35TF	240±25%	100	0.38	350	

PZ1005 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ1005D100-1R0TF	0~30	100	0.05	1000	0.5±0.15 [.020±.006]
PZ1005E100-1R8TF	0~15	100	0.02	1800	
PZ1005E700-R80TF	70±25%	100	0.10	800	
PZ1005E121-R70TF	120±25%	100	0.13	700	
PZ1005E221-R60TF	220±25%	100	0.18	600	
PZ1005E601-R45TF	600±25%	100	0.34	450	
PZ1005U700-1R2TF	70±25%	100	0.10	1200	
PZ1005U121-1R0TF	120±25%	100	0.12	1000	
PZ1005U221-R80TF	220±25%	100	0.18	800	
PZ1005U601-R45TF	600±25%	100	0.34	450	

PZ1608 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ1608D300-3R0TF	30±25%	100	0.03	3000	0.8±0.15 [.031±.006]
PZ1608D600-2R0TF	60±25%	100	0.08	2000	
PZ1608D750-1R0TF	75±25%	100	0.15	1000	
PZ1608D121-1R0TF	120±25%	100	0.20	1000	
PZ1608D221-1R0TF	220±25%	100	0.20	1000	
PZ1608D601-R50TF	600±25%	100	0.35	500	
PZ1608E600-1R4TF	60±25%	100	0.10	1400	
PZ1608U100-3R0TF	0~15	100	0.02	3000	
PZ1608U300-3R0TF	30±25%	100	0.03	3000	
PZ1608U600-2R5TF	60±25%	100	0.04	2500	
PZ1608U101-2R0TF	100±25%	100	0.05	2000	
PZ1608U121-2R0TF	120±25%	100	0.05	2000	
PZ1608U221-1R4TF	220±25%	100	0.10	1400	
PZ1608U331-1R2TF	330±25%	100	0.14	1200	
PZ1608U391-1R0TF	390±25%	100	0.14	1000	
PZ1608U471-1R0TF	470±25%	100	0.20	1000	

规格特性 Specifications

PZ2012 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ2012D390-4R0TF	39 $\pm$ 25%	100	0.02	4000	0.85 $\pm$ 0.2 [.033 $\pm$.008]
PZ2012D800-3R0TF	80 $\pm$ 25%	100	0.04	3000	
PZ2012D121-2R5TF	120 $\pm$ 25%	100	0.06	2500	
PZ2012D221-1R5TF	220 $\pm$ 25%	100	0.08	1500	
PZ2012D301-1R5TF	300 $\pm$ 25%	100	0.12	1500	
PZ2012D471-R80TF	470 $\pm$ 25%	100	0.25	800	
PZ2012D601-R80TF	600 $\pm$ 25%	100	0.25	800	
PZ2012U300-3R0TF	30 $\pm$ 25%	100	0.02	3000	
PZ2012U300-4R0TF	30 $\pm$ 25%	100	0.015	4000	
PZ2012U600-3R0TF	60 $\pm$ 25%	100	0.025	3000	
PZ2012U121-2R5TF	120 $\pm$ 25%	100	0.04	2500	
PZ2012U221-2R0TF	220 $\pm$ 25%	100	0.07	2000	
PZ2012U301-1R5TF	300 $\pm$ 25%	100	0.10	1500	
PZ2012U421-1R0TF	420 $\pm$ 25%	100	0.20	1000	
PZ2012U601-R80TF	600 $\pm$ 25%	100	0.25	800	

PZ3216 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ3216D190-6R0TF	19 $\pm$ 25%	100	0.010	6000	0.85 $\pm$ 0.2 [.033 $\pm$.008]
PZ3216D600-4R0TF	60 $\pm$ 25%	100	0.02	4000	
PZ3216U300-6R0TF	30 $\pm$ 25%	100	0.01	6000	
PZ3216U600-4R0TF	60 $\pm$ 25%	100	0.025	4000	
PZ3216U221-2R0TF	220 $\pm$ 25%	100	0.08	2000	
PZ3216U301-2R0TF	300 $\pm$ 25%	100	0.10	2000	
PZ3216U391-2R0TF	390 $\pm$ 25%	100	0.07	2000	
PZ3216U601-1R5TF	600 $\pm$ 25%	100	0.10	1500	
PZ3216U102-R50TF	1000 $\pm$ 25%	100	0.30	500	
PZ3216D000-4R0TFA99	0~10	100	0.02	4000	1.1 $\pm$ 0.2 [.043 $\pm$.008]
PZ3216D050-6R0TFA99	0~15	100	0.01	6000	
PZ3216D100-6R0TFA99	0~20	100	0.01	6000	
PZ3216D190-2R0TFA99	19 $\pm$ 25%	100	0.05	2000	
PZ3216D310-3R0TFA99	31 $\pm$ 25%	100	0.045	3000	
PZ3216D380-5R0TFA99	38 $\pm$ 25%	100	0.015	5000	
PZ3216D500-4R0TFA99	50 $\pm$ 25%	100	0.02	4000	
PZ3216D600-2R5TFA99	60 $\pm$ 25%	100	0.025	2500	
PZ3216D700-3R0TFA99	70 $\pm$ 25%	100	0.03	3000	
PZ3216D800-3R0TFA99	80 $\pm$ 25%	100	0.03	3000	
PZ3216D900-2R0TFA99	90 $\pm$ 25%	100	0.08	2000	
PZ3216D101-3R0TFA99	100 $\pm$ 25%	100	0.03	3000	
PZ3216D121-3R0TFA99	120 $\pm$ 25%	100	0.03	3000	
PZ3216D151-3R0TFA99	150 $\pm$ 25%	100	0.03	3000	
PZ3216D391-2R5TFA99	390 $\pm$ 25%	100	0.05	2500	
PZ3216D501-2R0TFA99	500 $\pm$ 25%	100	0.07	2000	
PZ3216D601-2R0TFA99	600 $\pm$ 25%	100	0.07	2000	
PZ3216U310-6R0TFA99	31 $\pm$ 25%	100	0.01	6000	
PZ3216U500-4R0TFA99	50 $\pm$ 25%	100	0.02	4000	
PZ3216U600-1R5TFA99	60 $\pm$ 25%	100	0.03	1500	
PZ3216U121-3R0TFA99	120 $\pm$ 25%	100	0.03	3000	
PZ3216U102-1R0TFA99	1000 $\pm$ 25%	100	0.30	1000	

规格特性 Specifications

PZ3216 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ3216U501-2R0TFA99	500 $\pm$ 25%	100	0.07	2000	1.6 $\pm$ 0.2 [.063 $\pm$.008]

注：当产品的I_r增加时，PZ3216系列的厚度可能会增加到1.1 $\pm$ 0.2mm。

Note: The thickness of PZ3216 series may be increased to 1.1 $\pm$ 0.2mm when the I_r of product increased.

PZ4516 TYPE

型号 Part Number	阻抗 Impedance	阻抗的测试频率 Z Test Frequency	直流电阻 Max. DC Resistance	额定电流 Max. Rated Current	厚度 Thickness
单位 Units	Ω	MHz	Ω	mA	mm [inch]
符号 Symbol	Z	Freq.	DCR	I _r	T
PZ4516U600-6R0TF	60 $\pm$ 25%	100	0.01	6000	1.6 $\pm$ 0.2 [.063 $\pm$.008]
PZ4516U720-6R0TF	72 $\pm$ 25%	100	0.01	6000	
PZ4516U181-3R0TF	180 $\pm$ 25%	100	0.025	3000	
PZ4516U471-2R0TF	470 $\pm$ 25%	100	0.05	2000	
PZ4516U102-1R5TF	1000 $\pm$ 25%	100	0.09	1500	

※：可根据客户需求提供其他电气特性产品，请联系您当地的销售人员。

※: Products with other Electrical Characteristics can be provided upon customer's request. Please contact your local sales.



电气特性

Typical Electrical Characteristics

D, E, U Material Comparison

额定电流 Rated Current




当工作温度超过 +85℃时，额定电流为 1000mA 及以上的片式铁氧体磁珠需要降额。请根据工作温度应用图表中所示的降额曲线。When operating temperatures exceed +85℃, derating of current is necessary for chip ferrite beads for which rated current is 1000mA and over. Please apply the derating curve shown in chart according to the operating temperature.



电气特性

Detail Electrical Characteristics








PZ0603 TYPE









电气特性

Detail Electrical Characteristics

PZ0603 TYPE







PZ1005 TYPE












电气特性

Detail Electrical Characteristics

PZ1005 TYPE










PZ1608 TYPE









电气特性

Detail Electrical Characteristics

PZ1608 TYPE












PZ2012 TYPE









电气特性

Detail Electrical Characteristics

PZ2012 TYPE





















PZ3216 TYPE



电气特性

Detail Electrical Characteristics










PZ3216 TYPE



电气特性

Detail Electrical Characteristics

PZ3216 TYPE



PZ4516 TYPE

